

Harvatek Surface Mount CSP LEDs Data Sheet SG060321NB-050048A3U1930

Official Product	HT Part No. SG060321NB-050048A3U1930			
Tentative Product	********			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		10/13/2023	Version 1.1	Page 1/13



DISCLAIMER	3
LIFE SUPPORT POLICY	3
PRODUCT SPECIFICATIONS	4
ATTENTION: ELECTROSTATIC DISCHARGE (ESD) PROTECTION	4
LABEL SPECIFICATIONS	5
SPECIFICATIONS RANGE	6
PRODUCT FEATURES	7
ELECTRO-OPTICAL CHARACTERISTICS	7
PACKAGE OUTLINE DIMENSION AND RECOMMENDED SOLDERING PATTERN FOR REFLOW SOLDERING	
ABSOLUTE MAXIMUM RATINGS	
CHARACTERISTICS OF SG060321NB	
PRECAUTION FOR USE	9
PACKAGING	10
Packing	11
DRY PACK	12
Storage	12
PRECAUTIONS	12
REFLOW SOLDERING	13
Reworking	13
CLEANING	13
CAUTIONS OF PICK AND PLACE	13
Revise History	14

Official Product	HT Part No. SG060321NB-050048A3U1930			
Tentative Product	*******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		10/13/2023	Version 1.1	Page 2/13



DISCLAIMER

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

Life Support Policy

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- 2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Official Product	HT Part No. SG060321NB-050048A3U1930			
Tentative Product	*******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		10/13/2023	Version 1.1	Page 3/13



Product Specifications

Item	Specification	Material	Quantity
Luminous	55-100 mcd		
Intensity(Iv)	@5 mA/ $T_S = 25$ °C; Tolerance: ± 10 %		
Chromaticity	As page 6 & 7		
Coordinate	@5 mA/ $T_S = 25$ °C; Tolerance: ± 0.007		
Vf	2.4-2.8 V		
	@5 mA/ $T_S = 25$ °C; Tolerance: ± 0.05 V		
Ir	< 10 μA @ V _R = 5 V		
Resin	Diffused	Silicon	
Carrier tape	EIA 481-1A specs	Conductive black tape	
Reel	EIA 481-1A specs	Conductive black	
Label	HT standard	Paper	
Packing bag	250x230mm	Aluminum laminated bag/ no-zipper	One reel per bag
Carton	HT standard	Paper	Non-specified

Others:

Each immediate box consists of 5 reels. The 5 reels may not necessarily have the same lot number or the same bin combinations of Iv, CIE and Vf. Each reel has a label identifying its specification; the immediate box consists of a product label as well.

Note: This is shipped test conditions

*Remarks: This product should be operated in forward bias. If a reverse voltage is continuously applied to the product, such operation can cause migration resulting in LED damage.

ATTENTION: Electrostatic Discharge (ESD) protection



The symbol to the left denotes that ESD precaution is needed. ESD protection for GaP and AlGaAs based chips is necessary even though they are relatively safe in the presence of low static-electric discharge. Parts built with AlGaInP, GaN, or/and InGaN based chips are **STATIC SENSITIVE devices**. ESD precaution must


be taken during design and assembly.

If manual work or processing is needed, please ensure the device is adequately protected from ESD during the process.

Official Product	HT Part No. SG060321NB-050048A3U1930			
Tentative Product	*******			
Specifications are subject notice. Proprietary data, dr	10/13/2023	Version 1.1	Page 4/13	



Label Specifications



Harvatek P/N:

S G 06032 1 NB- 05 0048 A3

Product	Product type	Package	Dice Q'ty	Color	Current	Series Number	Taping
CSP	Package type	0.6(L)x0.3(W)x0.2(H) mm	1:Single	Blue	5mA	X001~XZZZ	1.Taping style
							2. Q'ty

Lot No.:

1 2	3	4	5	6	7	8	9	10
E 1	A	1	Α	2	2	L	1	2
Code 12	Code 3	Code 4	Code 5	Code 6	Code 7	Code 8	Code 9	Code 10
	Mfg. Year	Mfg. Month	Mfg. Date	Consecuti	ve number		Special code	е
Internal Tracing Code	2020-L 2021-M 2022-P 2023-Q 2026-T 2027-V 2030-Y 2031-Z	1:Jan. 2:Feb. A:Oct. B:Nov. C:Dec.	1:A 2:B 3:C 26:Z 27:7 28:8 29:9 30:3 31:4	01-	-ZZ		000~ZZZ	

Official Product	HT Part No. SG060321NB-050048A3U1930			
Tentative Product	*******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		10/13/2023	Version 1.1	Page 5/13



Specifications Range

■Luminous Intensity (Iv) Bin:

Color	Bin Code	Spec. Range
NB-	BL3	55-75 mcd
ND-	BL4	75-100 mcd

Note: It maintains a tolerance of ±10% on Luminous Intensity

■Dominant Wavelength (Wd) Bin:

Color	Bin Code	Spec. Range
ND	BH1	464-469 nm
NB-	BH2	469-474 nm

Note: It maintains a tolerance of $\underline{+}$ 0.5nm on Wavelength Bin

■Forward Voltage (Vf) Bin:

Color	Bin Code	Spec. Range
	G1	2.4-2.5 V
NB-	G2	2.5-2.6 V
	G3	2.6-2.7 V
	G4	2.7-2.8 V

Note: It maintains a tolerance of ±0.05V on forward voltage measurements

Official Product	HT Part No. SG060321NB-050048A3U1930				
Tentative Product	*********	******			
	t to changes for improvement without advance rawings, company confidential all rights reserved.	10/13/2023	Version 1.1	Page 6/13	




Product Features

Electro-Optical Characteristics

($T_{Soldering}$, $25^\circ\mathtt{C}$							ldering , 25°C)		
Corios	Emitting Color	Motorial	V _F	(V)	Wav	elength λ	(nm)	I _V (mcd)	Viewing
Series Emi	Emitting Color	Material	min	max	λ_{D}	λ_{P}	Δλ	Typical	Angle $2\theta \frac{1}{2}$
SG060321	ND	InGaN	2.4	2.8	469	471	25	75	X : 140
39000321	NB-	iliGain	2. 4	2.0	409	4/1	25	73	Y: 140

Package Outline Dimension and Recommended Soldering Pattern for Reflow Soldering



Absolute Maximum Ratings

 $(T_{Soldering}, 25^{\circ}C)$


Series	P _D (mW)	I _F (mA)	I _{FP} (mA)*	T _{OP} (°C)	T _{ST} (℃)
Color	Dower Dissipation	Forward Current	Pulse Forward	Operating	Storage
Color	Power Dissipation	Forward Current	Current	Temperature	Temperature
NB-	56	20	50	-30~+85	-40~+85

 $^{^{\}star}$ Condition for I_{FP} is pulse of 1/10 duty and 0.1msec width

Official Product	HT Part No. SG060321NB-050048A3U1930			
Tentative Product	********	******		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		10/13/2023	Version 1.1	Page 7/13



Characteristics of SG060321NB-



Official Product	HT Part No. SG060321NB-050048A3U1930				
Tentative Product	********	*******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		10/13/2023	Version 1.1	Page 8/13	




Precaution for Use

- 1. The chips should not be used directly in any type of fluid such as water, oil, organic solvent, etc.
- 2. When the LEDs are illuminating, the maximum ambient temperature should be first considered before operation.
- 3. LEDs must be stored in a clean environment and a closed container with a nitrogen atmosphere is recommended. The storage period is one year after delivery.
- 4. The LEDs must be used within 168 hrs after unpacked. Unused products must be repacked in an anti-electrostatic package, folded to close any opening and then stored in a dry and cool space.
- 5. The appearance and specifications of the products may be modified for improvement without further notice.
- 6. The LEDs are sensitive to the static electricity and surge. It is strongly recommended to use a grounded wrist band and anti-electrostatic glove when handling the LEDs.If a voltage over the absolute maximum rating is applied to LEDs, it will damage LEDs.Damaged LEDs will show some abnormal characteristics such as remarkable increase of leak current, lower turn-on voltage and getting unlit at low current.
- 7. During processing, mechanical stress on the surface should be minimized as much as possible. Harvatek objects of all types should not be used to pierce the sealing compound.
- 8. Do not use tweezers to pick up or handle CSP LED. A vacuum pick up should only be used.
- 9. Silicone differs from materials conventionally used for the manufacturing of LEDs. These conditions must be considered during the handling of such devices. Compared to standard encapsulants, silicone is generally softer, and the surface is more likely to attract dust. As mentioned previously, the increased sensitivity to dust requires special care during processing. In cases where a minimal level of dirt and dust particles cannot be guaranteed, a suitable cleaning solution must be applied to the surface after the soldering of wire.
- 10. Harvatek suggests using isopropyl alcohol for cleaning. In case other solvents are used, it must be assured that these solvents do not dissolve the package or resin. Ultrasonic cleaning is not recommended. Ultrasonic cleaning may cause damage to the LED.
- 11. Please do not mold this product into another resin (epoxy, urethane, etc) and do not handle this product with acid or sulfur material in sealed space.
- 12. Avoid leaving fingerprints on silicone resin parts.

Official Product	HT Part No. SG060321NB-050048A3U1930			
Tentative Product	*********	******		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		10/13/2023	Version 1.1	Page 9/13




Packaging Tape Dimension



Notes:


- 1. All dimensions are in millimeters.
- 2. 7 inch reel-3000 pieces per reel.
- 3. Minimum packing quantity is 500 pieces for remainders.




Official Product	HT Part No. SG060321NB-050048A3U1930			
Tentative Product	********	******		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		10/13/2023	Version 1.1	Page 10/13



Reel Dimension



Packing



5 or 10 boxes per carton is available depending on shipment quantity.

Official Product	HT Part No. SG060321NB-050048A3U1930				
Tentative Product	********				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		10/13/2023	Version 1.1	Page 11/13	




Dry Pack

All SMD optical devices are **MOISTURE SENSITIVE**. Avoid exposure to moisture at all times during transportation or storage. Every reel is packaged in a moisture protected anti-static bag. Each bag is properly sealed prior to shipment.

A humidity indicator will be included in the moisture protected anti-static bag prior to shipment.

The packaging sequence is as follows:



Storage

It's recommended to store the products in the following conditions:

Humidity: 60 %RH Max.

Temperature: 5° C $\sim 30^{\circ}$ C $(41^{\circ}$ F $\sim 86^{\circ}$ F)

Precautions

- 1. Avoid exposure to moisture at all times during transportation or storage.
- 2. Anti-Static precaution must be taken when handling GaN, InGaN, and AlGaInP products.
- 3. It is suggested to connect the unit with a current limiting resistor of the proper size. Avoid applying a reverse voltage beyond the specified limit.
- 4. Avoid operation beyond the limits as specified by the absolute maximum ratings.
- 5. Avoid direct contact with the surface through which the LED emits light.
- 6. If possible, assemble the unit in a clean room or dust-free environment.

Official Product	HT Part No. SG060321NB-050048A3U1930				
Tentative Product	*******				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		10/13/2023	Version 1.1	Page 12/13	




Reflow Soldering

Recommend soldering paste specifications:

- Operating temp.: Above 217[°]C ,60~150sec
- 2. Peak temp.:260°C Max.,10sec Max.
- 3. Reflow soldering should not be done more than two times.
- 4. Never take next process until the component is cooled down to room temperature after reflow.
- 5. The recommended reflow soldering profile (measuring on the surface of the LED terminal) is as following:

Lead-free Solder Profile



Reworking

Rework should be completed within 5 seconds under 260°C.

Cleaning

Following are cleaning procedures after soldering:

An alcohol-based solvent such as isopropyl alcohol (IPA) is recommended.

Cautions of Pick and Place

- Avoid stress on the resin at elevated temperature.
- Avoid rubbing or scraping the resin by any object.
- Electric-static may cause damage to the component. Please ensure that the equipment is properly grounded. Use of an ionizer fan is recommended.

Official Product	HT Part No. SG060321NB-050048A3U1930			
Tentative Product	********	******		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		10/13/2023	Version 1.1	Page 13/13



Revise History

Rev.	Descriptions	Date	Page
-	New(Preliminary)	2022/12/26	-
1.0	Update Moisture Resistant Packing Materials	2023/04/10	7-13
1.1	Update Dominant Wavelength (nm) BIN	2023/08/24	7

Official Product	HT Part No. SG060321NB-050048A3U1930			
Tentative Product	********	******		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		10/13/2023	Version 1.1	Page 14/13