

Chandler, March 6th, 2023

## CHANGE NOTICE

Changes, solid and stranded Hook-up-Wire

CNC Tech is notifying that after the manufacturing location moved from China to Taiwan, some of the strand counts, Insulation thicknesses and overall diameters have changed in the listed UL Hook-up-Wire below. Those wires with red text in the "Before" columns have updated information in the "After" columns.

Specification sheets are listed on our web page: <u>www.cnctech.us</u>

H· Meyer CnC Tech

		CONDUCTOR STRANDED DIAMETER AWG TINNED COPPER (mm²)		CONDUCTOR OVERALL	INSULATION THICKNESS UL STANDARD	INSULATION THICKNESS		UL STANDARD O.D.	. STANDARD O.D.		OVERALL DIAMETER		
		AFTER	BEFORE	CNC TECH HOOK-up-WIRE	MINIMUM	CNC TECH HOOK-up-WIRE (mm)		MINIMUM	CNC TECH HOOK-up-WIRE (mm)			٥ ٥	
		14 144	200 0100	noon op when				India (discont)				ľ –	
UL WIRE	AWG	(mm²)	22/03	22/03	DIAMETER (mm)	AT ANY POINT (mm)	AFTER 22/03	BEFORE 22/03	AT ANY POINT (mm)	AFTER 22/03	TOLERANCE	BEFORE 22/03	TOLERANCE
1007	16		26/0.254		1.400	0.220	0.41		2.16	2.20			
1007	16 18	1.25 0.84	26/0.254 34/0.18	- X -	1.496	0.330	0.41	- x -	2.16	2.30	+/-0.10	- X -	- X -
	20	0.84	21/0.18	- X -	0.953	0.330	0.41	- x -	1.61	1.90	+/-0.10	- X -	- X -
	20	0.33	17/0.16	- X -	0.762	0.330	0.41	- x -	1.42	1.60	+/-0.10	- X -	- X -
	24	0.22	11/0.16	- X -	0.613	0.330	0.41	- X -	1.27	1.40	+/-0.10	- X -	- X -
	26	0.12	7/0.16	- X -	0.489	0.330	0.41	- X -	1.15	1.20	+/-0.10	- X -	- X -
1015	10	5.3	105/0.254	- X -	3.006	0.685	0.80	- X -	4.38	5.00	+/-0.10	- X -	- x -
	12	3.3	65/0.254	- X -	2.365	0.685	0.80	- x -	3.74	4.00	+/-0.10	- x -	- X -
	14	2.1	41/0.254	- X -	1.878	0.685	0.80	- X -	3.25	3.50	+/-0.10	- X -	- X -
	16	1.25	26/0.254	- x -	1.496	0.685	0.80	- x -	2.87	3.10	+/-0.10	- X -	- X -
	18	0.84	34/0.18	- X -	1.212	0.685	0.80	- X -	2.58	2.70	+/-0.10	- x -	- X -
	20	0.53	21/0.18	- X -	0.953	0.685	0.80	- X -	2.32	2.50	+/-0.10	- X -	- X -
	22	0.33	17/0.16	- X -	0.762	0.685	0.80	- X -	2.13	2.40	+/-0.10	- X -	- X -
	24	0.22	11/0.16	- X -	0.613	0.685	0.80	- X -	1.98	2.10	+/-0.10	- X -	- X -
	26	0.12	7/0.16	- X -	0.489	0.685	0.80	- X -	1.86	2.00	+/-0.10	- X -	- X -
1330	20	0.53	19/0.20	7/0.32	1.000	0.457	0.51	0.51	1.91	2.05	+/-0.10	2.05	+/-0.10
	22	0.33	19/0.16	7/0.254	0.800	0.457	0.51	0.51	1.71	1.80	+/-0.10	1.90	+/-0.10
	24	0.22	19/0.12	7/0.20	0.600	0.457	0.51	0.51	1.51	1.65	+/-0.10	1.70	+/-0.10
	26	0.12	7/0.16	7/0.16	0.480	0.457	0.51	0.51	1.39	1.55	+/-0.10	1.55	+/-0.10
1332	12	3.3	65/0.254	- X -	2.365	0.305	0.33	- X -	2.97	3.03	+/-0.10	- X -	- x -
	14	2.1	19/0.361	- X -	1.817	0.305	0.33	- X -	2.43	2.51	+/-0.10	- X -	- X -
	16	1.25	19/0.29	- X -	1.460	0.305	0.33	- X -	2.07	2.17	+/-0.10	- X -	- X -
	18	0.84	19/0.24	- X -	1.208	0.305	0.33	- X -	1.82	1.86	+/-0.10	- X -	- X -
	20	0.53	19/0.20	7/0.32	1.007	0.305	0.33	0.33	1.62	1.66	+/-0.10	1.65	+/-0.10
	22	0.33	19/0.16	7/0.254	0.806	0.305	0.33	0.33	1.42	1.46	+/-0.10	1.45	+/-0.10
	24 26	0.22	19/0.127 7/0.16	7/0.20	0.639 0.489	0.305	0.33	0.33	1.25	1.26	+/-0.10	1.30	+/-0.10
		0.12		- X -		0.000		- X -			+/-0.10	- X -	- X -
1430	16	1.25	26/0.254	26/0.254	1.496	0.330	0.41	0.38	2.16	2.40	+/-0.10	2.30	+/-0.15
	18	0.84	34/0.18	34/0.18	1.212	0.330	0.41	0.38	1.87	2.10	+/-0.10	2.05	+/-0.10
	20 22	0.53	21/0.18 17/0.16	21/0.18 17/0.16	0.953	0.330	0.41	0.38	1.61 1.42	1.76	+/-0.10	1.75	+/-0.10
<b>├</b> ──┤	22	0.33	1//0.16	1//0.16	0.762	0.330	0.41	0.38	1.42	1.55	+/-0.10	1.60 1.45	+/-0.10
	24	0.22	7/0.16	7/0.16	0.489	0.330	0.41	0.38	1.15	1.40	+/-0.10	1.45	+/-0.10
1500													
1569	16	1.25	26/0.254 34/0.18	26/0.254 34/0.18	1.496	0.330	0.38	0.38	2.16	2.40 2.10	+/-0.10	2.40 2.10	+/-0.15
	18 20	0.84	21/0.18	21/0.18	0.953	0.330	0.38	0.38	1.61	1.80	+/-0.10	1.85	+/-0.10
	20	0.53	17/0.16	17/0.16	0.953	0.330	0.38	0.38	1.42	1.60	+/-0.10	1.60	+/-0.10
	24	0.33	11/0.16	11/0.16	0.613	0.330	0.38	0.38	1.42	1.40	+/-0.10	1.45	+/-0.10

	26	0.12	7/0.16	- X -	0.489	0.330	0.38	- X -	1.15	1.30	+/-0.10	- X -	- X -
10064	22	0.33	7/0.254	- X -	0.776	0.051	0.12	- X -	0.88	1.20	+/-0.05	- X -	- x -
	24	0.22	7/0.20	- X -	0.611	0.051	0.12	- X -	0.71	0.80	+/-0.05	- X -	- X -
	26	0.12	7/0.16	- X -	0.489	0.051	0.12	- X -	0.59	0.70	+/-0.05	- X -	- x -
	28	0.08	7/0.12	7/0.12	0.367	0.051	0.12	0.15	0.47	0.60	+/-0.05	0.70	+/-0.05
	30	0.05	7/0.10	7/0.10	0.306	0.051	0.10	0.15	0.41	0.50	+/-0.05	0.60	+/-0.05
	32	0.032	7/0.08	7/0.08	0.244	0.051	0.07	0.15	0.35	0.38	+/-0.05	0.55	+/-0.05
	34	0.02	7/0.06	7/0.06	0.183	0.051	0.07	0.15	0.28	0.32	+/-0.05	0.50	+/-0.05
10368	26	0.12	7/0.16	7/0.16	0.489	0.203	0.27	0.23	0.90	1.02	+/-0.10	1.00	+/-0.10
	28	0.08	7/0.127	7/0.127	0.388	0.203	0.27	0.23	0.79	0.92	+/-0.05	0.90	+/-0.05
	30	0.05	7/0.102	7/0.10	0.306	0.203	0.27	0.23	0.71	0.84	+/-0.05	0.80	+/-0.05
11047	10	5.3	105/0.254	- X -	3.006	0.178/0.178	0.3/0.4	- X -	3.72	4.50	+/-0.15	- X -	- x -
	12	3.3	65/0.254	- X -	2.365	0.178/0.178	0.3/0.4	- X -	3.08	3.80	+/-0.15	- X -	- X -
	14	2.1	41/0.254	- X -	1.878	0.178/0.178	0.3/0.4	- X -	2.59	3.30	+/-0.15	- X -	- x -
	16	1.25	26/0.254	- x -	1.496	0.178/0.178	0.3/0.4	- X -	2.21	2.90	+/-0.15	- X -	- X -
	18	0.84	34/0.18	19/0.24	1.212	0.178/0.178	0.20/0.23	0.20/0.23	1.92	2.05	+/-0.10	2.05	+/-0.10
	20	0.53	21/0.18	7/0.32	0.953	0.178/0.178	0.20/0.23	0.20/0.23	1.66	1.80	+/-0.10	1.80	+/-0.10
	22	0.33	17/0.16	7/0.254	0.762	0.178/0.178	0.20/0.23	0.20/0.23	1.47	1.60	+/-0.10	1.60	+/-0.10
	24	0.22	11/0.16	7/0.16	0.613	0.178/0.178	0.20/0.23	0.20/0.23	1.32	1.46	+/-0.10	1.46	+/-0.10
	26	0.12	7/0.16	- X -	0.489	0.178/0.178	0.20/0.23	- X -	1.20	1.35	+/-0.10	- X -	- X -
21458	18	0.84	34/0.18	21/0.18	1.212	0.33	0.38	0.38	1.87	1.94*3.88	+/-0.10	1.94*3.88	+/-0.10
	20	0.53	21/0.18	21/0.18	0.953	0.33	0.38	0.38	1.61	1.8*3.6	+/-0.10	1.69*3.38	+/-0.10
	22	0.33	17/0.16	17/0.16	0.762	0.33	0.38	0.38	1.42	1.6*3.2	+/-0.10	1.50*3.00	+/-0.10
	24	0.22	11/0.16	11/0.16	0.613	0.33	0.38	0.38	1.27	1.45*2.9	+/-0.10	1.36*2.72	+/-0.10
	26	0.12	7/0.16	7/0.16	0.489	0.33	0.38	0.38	1.15	1.3*2.6	+/-0.10	1.24*2.47	+/-0.10
1672	18	0.84	34/0.18	34/0.18	1.212	0.127/0.127	0.4/0.5	0.4/0.5	1.72	3.10	+/-0.15	3.10	+/-0.15
	20	0.53	21/0.18	21/0.18	0.953	0.127/0.127	0.4/0.5	0.4/0.5	1.46	2.80	+/-0.15	2.80	+/-0.15
	22	0.33	17/0.16	17/0.16	0.762	0.127/0.127	0.4/0.5	0.4/0.5	1.27	2.50	+/-0.15	2.60	+/-0.15
	24	0.22	11/0.16	11/0.16	0.613	0.127/0.127	0.4/0.5	0.4/0.5	1.12	2.30	+/-0.15	2.40	+/-0.15
3132	16	1.25	26/0.254	26/0.254	1.496	0.33	0.40	0.39	2.16	2.30	+/-0.15	2.30	+/-0.15
	18	0.84	34/0.18	34/0.18	1.212	0.33	0.40	0.39	1.87	2.00	+/-0.15	2.00	+/-0.10
	20	0.53	21/0.18	21/0.18	0.953	0.33	0.40	0.39	1.61	1.80	+/-0.10	1.80	+/-0.10
	22	0.33	22/0.14	17/0.16	0.758	0.33	0.40	0.39	1.42	1.60	+/-0.10	1.60	+/-0.10
	24 26	0.22	11/0.16 7/0.16	11/0.16	0.613	0.33	0.40	0.39 - x -	1.27	1.45	+/-0.10	1.45 - x -	+/-0.10 - X -
0107		0.12		- X -							+/-0.10		
3135	16	1.25	26/0.254	26/0.254	1.496	0.686	0.76	0.76	2.87	3.02	+/-0.20	3.02	+/-0.20
	18	0.84	7/0.40	34/0.18	1.222	0.686	0.76	0.76	2.59	2.72	+/-0.20	2.72	+/-0.20
	20 22	0.53	7/0.32	- X -	0.978	0.686	0.76	- X -	2.35	2.52	+/-0.15	- x - 2.30	- X -
	22	0.33	11/0.16	17/0.16 - x -	0.762	0.686	0.76	0.76	2.13	2.30	+/-0.15	2.30 - x -	+/-0.15
	24	0.22	7/0.16	- X -	0.489	0.686	0.76	- X -	1.98	2.12	+/-0.15	- X -	- X -
2020													
3239	16	1.25	26/0.254	26/0.254	1.496	0.50	0.65	0.635	2.50	2.80	+/-0.15	2.80	+/-0.15
	18 20	0.84	34/0.18 21/0.18	34/0.18 21/0.18	1.212 0.953	0.50	0.65	0.635	2.21 1.95	2.50	+/-0.15	2.50	+/-0.10
	20	0.53	17/0.16	17/0.16	0.953	0.50	0.65	0.635	1.95	2.25	+/-0.15	2.25	+/-0.10
	22	0.33	11/0.16	11/0.16	0.613	0.50	0.65	0.635	1.61	1.90	+/-0.15	1.90	+/-0.10
3122	16	1.25	7/0.50	26/0.254	1.528	0.330	0.381/0.20	0.48/0.15	2.19	2.70	+/-0.13	2.70	+/-0.20
5144	10	0.84	7/0.40	34/0.18	1.222	0.330	0.381/0.20	0.48/0.15	1.88	2.40	+/-0.20	2.35	+/-0.20
	10	V.04	110.10	54/0.10	1.222	0.550	0.501/0.20	0.40/0.15	1.00	2.70	17-0.20	4.00	17-0.20

I I	20		7/0.22	21/0.19	0.017	0.220	0.201/0.20	0.49/0.15	1.50	2.10		0.15	<u> </u>
	20	0.53	7/0.32	21/0.18	0.917	0.330	0.381/0.20	0.48/0.15	1.58	2.10	+/-0.20	2.15	+/-0.20
	22	0.33	7/0.26	17/0.16	0.795	0.330	0.381/0.20	0.48/0.15	1.45	1.95	+/-0.20	2.00	+/-0.20
	24	0.22	7/0.20	- X -	0.611	0.330	0.381/0.20	- X -	1.27	1.80	+/-0.20	- X -	- X -
	26	0.12	7/0.16	- X -	0.489	0.330	0.381/0.20	- X -	1.15	1.70	+/-0.20	- X -	- X -
1426	10	5.26	105/0.254	- X -	3.006	0.127	0.85	- X -	3.26	4.70	+/-0.20	- X -	- X -
	12	3.31	65/0.254	- X -	2.365	0.127	0.85	- X -	2.62	4.10	+/-0.20	- X -	- X -
	14	2.08	41/0.254	- X -	1.878	0.127	0.85	- X -	2.13	3.60	+/-0.15	- X -	- X -
	16	1.31	26/0.254	- X -	1.496	0.127	0.85	- X -	1.75	3.20	+/-0.15	- X -	- X -
			DIAMETER A	OR SOLID AWG TINNED R (mm <sup>2</sup> ) BEFORE	CONDUCTOR OVERALL CNC TECH HOOK-up-WIRE	INSULATION THICKNESS UL STANDARD MINIMUM	INSULATION THICKNESS CNC TECH HOOK-up-WIRE (mm)		UL STANDARD O.D.	OVERALL DIAMETER			υ
UL WIRE	AWG	(mm²)	22/48	22/48	DIAMETER (mm)	AT ANY POINT (mm)	AFTER 22/48	BEFORE 22/48	AT ANY POINT (mm)	AFTER 22/48	TOLERANCE	BEFORE 22/48	TO FRANCE
10981	16	1.30	1/1.29	- X -	1.290	0.203	0.24	- X -	1.70	1.77	+/-0.10	- X -	- X -
10901	18	0.84	1/1.024	- X -	1.024	0.203	0.24	- x -	1.43	1.51	+/-0.10	- X -	- X -
	20	0.53	1/0.813	- X -	0.813	0.203	0.24	- x -	1.45	1.29	+/-0.10	- X -	- X -
	20	0.33	1/0.643	- X -	0.643	0.203	0.24	- x -	1.05	1.12	+/-0.10	- X -	- X -
	24	0.22	1/0.511	- X -	0.511	0.203	0.24	- x -	0.92	0.99	+/-0.10	- X -	- X -
	26	0.12	1/0.404	- X -	0.404	0.203	0.24	- X -	0.81	0.88	+/-0.10	- X -	- X -
	28	0.08	1/0.320	- X -	0.320	0.203	0.24	- X -	0.73	0.80	+/-0.10	- X -	- X -
	30	0.05	1/0.254	- X -	0.254	0.203	0.24	- X -	0.66	0.73	+/-0.10	- X -	- X -
10982	18	0.84	1/1.02	1/1.02	1.020	0.330	0.38	0.38	1.68	1.80	+/-0.10	1.70	+/-0.10
10702	20	0.53	1/0.813	1/0.813	0.813	0.330	0.38	0.38	1.47	1.60	+/-0.10	1.50	+/-0.10
	22	0.33	1/0.643	1/0.643	0.643	0.330	0.38	0.38	1.30	1.40	+/-0.10	1.40	+/-0.10
3132	18	0.84	1/1.02	1/1.02	1.020	0.330	0.40	0.39	1.68	1.80	+/-0.10	2.00	+/-0.10
5152	20	0.53	1/0.813	1/0.813	0.813	0.330	0.40	0.39	1.47	1.60	+/-0.10	1.70	+/-0.10
	20	0.33	1/0.643	1/0.643	0.643	0.330	0.40	0.39	1.30	1.50	+/-0.10	1.55	+/-0.10
1007	16	1.30	1/1.29	- X -	1.290	0.330	0.41	- X -	1.95	2.10	+/-0.10	- X -	- X -
1007	18	0.84	1/1.024	- x -	1.020	0.330	0.41	- x -	1.68	1.85	+/-0.10	- X -	- X -
	20	0.53	1/0.813	- X -	0.813	0.330	0.41	- X -	1.47	1.65	+/-0.10	- X -	- X -
	22	0.33	1/0.643	- X -	0.643	0.330	0.41	- X -	1.30	1.50	+/-0.10	- X -	- X -
	24	0.22	1/0.511	- X -	0.511	0.330	0.41	- X -	1.17	1.35	+/-0.10	- X -	- X -
	26	0.12	1/0.404	- X -	0.404	0.330	0.41	- X -	1.06	1.25	+/-0.10	- X -	- X -
1015	10	5.3	1/2.588	- X -	2.588	0.685	0.80	- X -	3.96	4.20	+/-0.10	- X -	- X -
1010	12	3.3	1/2.05	- X -	2.050	0.685	0.80	- X -	3.42	3.65	+/-0.10	- X -	- X -
	14	2.10	1/1.63	- X -	1.630	0.685	0.80	- X -	3.00	3.25	+/-0.10	- X -	- X -
	16	1.30	1/1.29	- X -	1.290	0.685	0.80	- X -	2.66	2.90	+/-0.10	- X -	- X -
	18	0.84	1/1.024	- X -	1.020	0.685	0.80	- X -	2.39	2.65	+/-0.10	- X -	- X -
	20	0.53	1/0.813	- X -	0.813	0.685	0.80	- X -	2.18	2.40	+/-0.10	- X -	- X -
	22	0.33	1/0.643	- X -	0.643	0.685	0.80	- X -	2.01	2.25	+/-0.10	- X -	- X -
	24	0.22	1/0.511	- X -	0.511	0.685	0.80	- X -	1.88	2.10	+/-0.10	- X -	- X -
	26	0.12	1/0.404	- X -	0.404	0.685	0.80	- X -	1.77	2.00	+/-0.10	- X -	- X -