

HRPS

Hall-Effect Rotary Position Sensor with integrated connector



KEY FEATURES



True, contactless operation

Without any gears or mechanical interfaces the sensor is easily assembled and calibrated and subject to limited wear and tear over lifetime.



360 degree absolute position feedback

Endless mechanical rotational angle without dead band, keeps the position on power loss with configurable electrical angles from 50 to 360 degrees.



Made for harsh environments

The rugged package protects the sensor from dust, moisture, vibration and extreme temperatures for usage in the most demanding environments.



Durable and robust design

The non-contacting design allows for an extra-long product lifetime of up to 50 million cycles.



Integrated shaft

The magnet is securely fastened to the shaft and acts as only moving component in the sensor.

DESCRIPTION

The HRPS Series of Hall-effect Rotary Position Sensors is a cost-effective, non-contacting position sensing solution for applications in harsh environments such as transportation, industrial and marine

This compact sensor with integrated AMP superseal connector uses a permanent magnet that is securely fastened to the shaft and acts as the only moving component in the sensor. Fully sealed and flanged mounted for easy positioning, the sensor is versatile with configurable angular ranges from 50 to 360 degrees, different pin-out options and support for low and high-voltage power supply.

APPLICATIONS

Industrial

- ► Autonomous warehouse robotics
- ▶ Robotics and automation feedback
- ► Robot arm position
- ► Valve monitoring
- ► Conveyor operation

Transportation

- ▶ Steering wheel angle
- ▶ Pedal Position
- ► Suspension/height detection
- ▶ Fork height and mast tilt
- ▶ Bucket position
- ► Hitch position
- ► Transmission gear shift

Marine

▶ Steering and shifter sensor

Home and Building Automation

► HVAC systems

HRPS

Hall-Effect Rotary Position Sensor with integrated connector

MECHANICAL SPECIFICATIO	AL SPECIFICATIONS		
	HRPS		
Rotational life	Up to 50 M cycles		
Mechanical range	360° (endless rotation)		
Mating connector	AMP Superseal 282087-1°		
Mounting screw sizes			
Sensor to mounting surface	non-magnetic, stainless steel M5 screws and 10 mm 0D washers		
Lever to mounting surface	non-magnetic stainless steel M6 screws		

ELECTRICAL SPECIFICATIONS

	HRPS	
Supply voltage	5V ±10%	7V to 32V
Supply current	12 mA	14 mA
Overvoltage protection	+10V	+36V
Reversevoltage protection	-10V	-36V
Output standard inverted		
Linearity ¹	± 1% (± 0.5 upon request)	
Resolution	Up to 12 bit	
Self-diagnostic features	yes	


 $^{^{1}}$ Ferromagnetic materials close to the sensor (i.e. shaft, mounting surface) may affect the sensor's linearity.

ENVIRONMENTAL SPECIFICATIONS

	HRPS
Operating temperature	-40° to +125°C
Shock	50g
Vibration	5-2000 Hz; 20g; Amax 0,75 mm
Sealing	IP69K


HRPS

Hall-Effect Rotary Position Sensor with integrated connector



CONNECTION SCHEME	ECTION SCHEME		
PIN	European Pinout	American Pinout	
1	Ground	Power supply	
2	Power Supply	Ground	
3	Signal output	Signal output	

OUTPUT FUNCTIONS



Custom output functions on request.









Please always use the latest updated datasheets and 3D models published on our website.

Disclaimer:

The product information in this catalog is for reference purposes. Please consult for the most up to date and accurate design information.

Piler Sensors & Controls S.A., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Piher"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product described herein or Piler disclaims any and all liability arising out of the use or application of any product described herein or behalf information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Piher's terms and conditions of sale, including but not limited to the warranty expressed therein, which apply to these products, product specifications do not expand or otherwise, to any intellectual property rights is granted by this document or by any conduct of Piher.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Piher for any damages arising or resulting from such use or sale. Please contact authorized Piher personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners. Information contained in this document complies with all relevant export control regulations. If you are in any doubt about the export control restrictions that apply to this information, please contact the sender immediately. For any Piher Exports, Note: All products / technologies are EAR99 Classified commodities. Exports from the United States are in accordance with the Export Administration Regulations. Diversion contrary to US law is prohibited.

CONTACT

Piher Sensing Systems Polígono Industrial Municipal Vial T2, Nº22 31500 Tudela Spain

sales@piher.net

+34 948 820 450 Europe: Americas: +1 636 251 0855 Asia Pacific: +65 9641 8886 +91 9538 686 586

Page 3 of 3

