

## SS32-ML THRU SS310-ML

### 3.0 AMPS. Surface Mount Schottky Barrier Rectifiers

Voltage Range  
20 to 100 Volts  
Current  
3.0 Amperes


#### Features

- ✧ For surface mounted application
- ✧ Metal to silicon rectifier, majority carrier conduction
- ✧ Low forward voltage drop
- ✧ Easy pick and place
- ✧ High surge current capability
- ✧ Plastic material used carriers Underwriters Laboratory Classification 94V-0
- ✧ Epitaxial construction
- ✧ High temperature soldering:  
260°C / 10 seconds at terminals

#### Mechanical Data

- ✧ Case: Molded plastic
- ✧ Terminals: Solder plated
- ✧ Polarity: Indicated by cathode band
- ✧ Packaging: 16mm tape per EIA STD RS-481
- ✧ Weight: 0.21 gram

#### SMC/DO-214AB



Dimensions in inches and (millimeters)

#### Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	SS 32	SS 33	SS 34	SS 35	SS 36	SS 39	SS 310	Units
Maximum Recurrent Peak Reverse Voltage	$V_{RRM}$	20	30	40	50	60	90	100	V
Maximum RMS Voltage	$V_{RMS}$	14	21	28	35	42	63	70	V
Maximum DC Blocking Voltage	$V_{DC}$	20	30	40	50	60	90	100	V
Maximum Average Forward Rectified Current at $T_A$ (See Fig. 1)	$I_{(AV)}$	3.0							A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	$I_{FSM}$	100							A
Maximum Instantaneous Forward Voltage (Note 1) @ 3.0A	$V_F$	0.5		0.75		0.85		V	
Maximum DC Reverse Current @ $T_A=25^\circ\text{C}$ at Rated DC Blocking Voltage @ $T_A=100^\circ\text{C}$	$I_R$	0.5					0.6		mA
		20		10.0		20			
Typical Thermal Resistance ( Note 2 )	$R_{\theta JL}$	17							$^\circ\text{C/W}$
	$R_{\theta JA}$	55							
Operating Temperature Range	$T_J$	-55 to +125			-55 to +150				$^\circ\text{C}$
Storage Temperature Range	$T_{STG}$	-55 to +150							

Notes: 1. Pulse Test with PW=300 usec, 1% Duty Cycle

2. Measured on P.C.Board with 0.6 x 0.6"(16 x 16mm) Copper Pad Areas.

## RATINGS AND CHARACTERISTIC CURVES (SS32-ML THRU SS310-ML)

FIG.1- MAXIMUM FORWARD CURRENT DERATING CURVE




FIG.2- MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG.3- TYPICAL FORWARD CHARACTERISTICS




FIG.4- TYPICAL REVERSE CHARACTERISTICS




FIG.5- TYPICAL JUNCTION CAPACITANCE





FIG.6- TYPICAL TRANSIENT THERMAL IMPEDANCE



**Disclaimer**

The information presented in this document is for reference only. MOSLEADER reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), MOSLEADER or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.