


Serrated Ring Terminals

Material: Tin Plated Brass

Temperature: 300°F

Maximum Electrical Rating: 22 - 3 Amps, 20 - 4 Amps, 18 - 7 Amps,
16 - 10 Amps, 14 - 15 Amps, 12 - 20 Amps,
10 - 24 Amps



HOFFMAN PART NO.	*CRIMP TYPE	WIRE SIZE	STUD SIZE	DIMENSION (INCHES)				UL	REEL QTY
				STUD DIAMETER D	TONGUE WIDTH W	STUD CLEARANCE E	LENGTH L		
2216M4SST	D	22-16	8	0.196	0.331	0.444	0.768	Y	5000
22164SST	D	22-16	8	0.169	0.331	0.444	0.752	N	5000
20189SST	D	20-18	3/8	0.433	0.630	0.422	1.055	N	5000
2016M3SST	D	20-16	6	0.142	0.295	0.386	0.630	Y	5000
20163SST	D	20-16	6	0.144	0.382	0.449	0.768	Y	5000
20164SST	D	20-16	8	0.169	0.394	0.504	0.827	Y	4000
20165SST	D	20-16	10	0.197	0.382	0.445	0.768	Y	5000
2016L5SST	D	20-16	10	0.207	0.449	0.457	0.768	Y	4000
20166SST	D	20-16	1/4	0.250	0.457	0.504	0.839	Y	4000
20169SST	D	20-16	3/8	0.433	0.630	0.386	1.055	N	3500
1814M4SST	D	18-14	8	0.173	0.295	0.421	0.732	N	3500
18144SST	D	18-14	8	0.173	0.331	0.441	0.760	N	3500


* D = Double Crimp

Spade Terminals

Material: Tin Plated Brass

Temperature: 300°F

Maximum Electrical Rating: 22 - 3 Amps, 20 - 4 Amps, 18 - 7 Amps, 16 - 10 Amps,
14 - 15 Amps, 12 - 20 Amps, 10 - 24 Amps



HOFFMAN PART NO.	WIRE SIZE	STUD SIZE	DIMENSION (INCHES)				UL	REEL QTY
			STUD DIAMETER D	TONGUE WIDTH W	STUD AREA LENGTH E	LENGTH L		
22162AST	22-16	4	0.128	0.300	0.288	0.688	Y	5000
22163AST	22-16	6	0.148	0.300	0.288	0.688	Y	5000
22164AST	22-16	8	0.172	0.300	0.288	0.688	Y	5000
20144AST	20-14	8	0.172	0.300	0.288	0.688	Y	5000
20143AST	20-14	6	0.148	0.232	0.288	0.696	Y	5000

