

# **Glass Passivated Bridge Rectifiers**

#### **FEATURES**

- Glass passivated junction
- Ideal for printed circuit board
- High case dielectric strength
- Typical IR less than 0.1µA
- High surge current capability
- UL Recognized File # E-326243
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21 definition

# MECHANICAL DATA

# Case: KBU

Molding compound, UL flammability classification rating 94V-0 Base P/N with suffix "G" on packing code - green compound (halogen-free) **Terminal:** Matte tin plated leads, solderable per JESD22-B102 Meet JESD 201 class 1A whisker test **Mounting torque:** 0.56 Nm max. **Weight:** 7.2 g (approximately)





Κ	в	U



DADAMETER		KBU	KBU	KBU	KBU	KBU	KBU	KBU	Unit
PARAMETER	SYMBOL	601G	602G	603G	604G	605G	606G	607G	
Maximum repetitive peak reverse voltage	V <sub>RRM</sub>	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V <sub>RMS</sub>	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V <sub>DC</sub>	50	100	200	400	600	800	1000	V
Maximum average forward rectified current	I <sub>F(AV)</sub>	6							Α
Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load	I <sub>FSM</sub>	175						Α	
Rating for fusing (t<8.3ms)	l <sup>2</sup> t				127				A <sup>2</sup> s
Maximum instantaneous forward voltage (Note 1) I <sub>F</sub> = 3 A I <sub>F</sub> = 6 A	V <sub>F</sub>				1.0 1.1				V
Maximum DC reverse current $T_J=25 \degree$ at rated DC blocking voltage $T_J=125\degree$	I <sub>R</sub>	5 500						μA	
Typical junction capacitance per leg	Cj				400				pF
Typical thermal resistance	R <sub>θJC</sub> R <sub>θJA</sub>	3.1 8.6						<sup>o</sup> C/W	
Operating junction temperature range	TJ	- 55 to +150						°C	
Storage temperature range	T <sub>STG</sub>	- 55 to +150					°C		

Note 1: Pulse Test with PW=300µs, 1% Duty Cycle

Note 2: Measured at 1MHz and applied Reverse Voltage of 4.0V D.C.



Taiwan Semiconductor


ORDERING INFORMATION							
PART NO.	PACKING CODE	PACKING CODE SUFFIX	PACKAGE	PACKING			
KBU60xG (Note 1)	то	G	KBU	500 / Tray			

Note 1: "x" defines voltage from 50V (KBU601G) to 1000V (KBU607G)

EXAMPLE							
PREFERRED P/N PART NO.		PACKING CODE	PACKING CODE SUFFIX	DESCRIPTION			
KBU607G T0	KBU607G	ТО					
KBU607G T0G	KBU607G	ТО	G	Green compound			


# **RATINGS AND CHARACTERISTICS CURVES**

(T<sub>A</sub>=25°C unless otherwise noted)






#### FIG. 5 TYPICAL JUNCTION CAPACITANCE



# PACKAGE OUTLINE DIMENSIONS KBU



DIM.	Unit	(mm)	Unit (inch)		
	Min	Max	Min	Max	
А	18.8	19.8	0.740	0.780	
В	4.6 5.6		0.181	0.220	
С	8.2 (	TYP.)	0.322 (TYP.)		
D	1.2	1.3	0.047	0.051	
E	20.0	-	0.787	-	
F	6.8	7.1	0.268	0.280	
G	22.7	23.7	0.894	0.933	
Н	4.6	5.0	0.181	0.197	

# MARKING DIAGRAM



- = Specific Device Code
- = Green Compound
- = Date Code
- = Factory Code



### Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or seling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.