




STATFREE® T2 PLUS DISSIPATIVE RUBBER



2-Layer

Grounding & Cleaning
If the material is used on top of an already properly grounded surface, [grounding hardware](#) may not be necessary. Where no properly grounded surface is available, [grounding hardware](#) is required to provide a path-to-ground. Rtg compliance verification measurements must be made as outlined in ESD TR53 with a [surface resistance meter](#).

See Tech Bulletin [IB-7000](#) for Restore® Surface & Mat Cleaner Application Instructions.

Limited Lifetime Warranty:
Desco warrants for one year that Statfree® matting products will be free of defects in materials and workmanship and will guarantee dissipative/conductive mat properties for the life of the mat. Damage to matting caused by misuse of any kind, including using inappropriate cleaners is not covered by [Desco Limited Warranty](#).

RoHS 3, REACH, and Conflict Minerals Statement
See the Desco Industries RoHS 3, REACH, and Conflict Minerals Statement:
<http://www.descoindustries.com/ROHS3.aspx>
See the Desco Limited Warranty:
<http://desco.descoindustries.com/Limited-Warranty.aspx>
See the Desco Disclaimer:
<http://desco.descoindustries.com/Disclaimer.aspx>

Specifications

Standard Document
ANSI/ESD S20.20

Electrical Properties
Dissipative Surface Layer
Rtt Resistance:
Rtg Resistance:

Ground Plane Layer
Rtt Resistance:

Meets Requirements of:
Worksurface

Test Procedures/Method

ANSI/ESD S4.1 and ESD TR53
ANSI/ESD S4.1 and ESD TR53
ANSI/ESD S4.1 and ESD TR53

Typical Values

1 x 10⁶ to < 1 x 10⁹ ohms
1 x 10⁶ to < 1 x 10⁸ ohms
< 1 x 10⁶ ohms

Physical Properties

Construction:
Thickness:
Color:²
Embossing:²
Weight:
Hardness:

Dual-layer rubber material¹
0.060" (1.5mm)
Blue (Top), Dark Blue (Top), Dark Grey (Top), Green (Top), Black (Bottom)
Slight Texture
0.43 lbs./sq. ft. (0.2g/cm2)
65 ± 5 Shore "A", per ASTM-D2240

Other Properties

Heat Resistance:
Chemical Resistance:
Oil Absorption Resistance:

Does not melt or burn when coming into contact with hot solder and soldering irons.
Resistance to degradation by inorganic acids, organic acids, reducing agents, aliphatic hydrocarbons, mineral oil, aldehydes, and amines.
Resists oil absorption to maintain physical and electrical properties.

¹Rubber material is vulcanized and may contain sulfur
²Color and texture may vary between lots and mills

Tolerances:

Width ± 0.250"
Length ± 0.250" every 1 linear foot of running material.
Thickness ±10%

Matting materials have a tendency to shrink slightly when first unrolled. In applications where length is critical, allow the material to condition for at least 4 hours before cutting to size. Always using care trim with a sharp knife or razor blade.

*Color and texture may vary between lots and mills.

For product listings, [Click Here](#)



Made in the
United States of America

**Tray liners have 3/4" radius corners and do not include grounding hardware.

Specifications and procedures subject to change without notice.



STATFREE® T2 PLUS DISSIPATIVE, RUBBER, 2-LAYER, 0.060" (1.5mm)

DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 WEB SITE: Desco.com

PHONE (909) 627-8178

DESCO EAST: ONE COLGATE WAY, CANTON, MA 02021-1407

PHONE (781) 821-8370

MATERIAL

STATFREE® T2 Plus
DRAWING PM-132

DATE:
March
2021