

CGD65A055S2 DATASHEET

650 V / 55 mΩ GaN HEMT with ICeGaN™ Gate and Current Sense

DECEMBER 2022






650 V / 55 mΩ GaN HEMT with ICeGaN™ Gate and Current Sense

Key features

- 650 V 27 A e-mode GaN power switch
- ICeGaN™ gate technology for high gate threshold and broad gate voltage window compatible with gate-drivers for Si MOSFETs
- Gate drive voltage 9 V to 20 V
- Current sense function
- $R_{DS(on)} = 55 \text{ m}\Omega$
- Suitable for very high switching frequency
- Kelvin Contact
- Small 8x8 mm² PCB footprint
- Bottom side cooled DFN package

Description

The CGD65A055S2 is an enhancement mode GaN-on-silicon power transistor, exploiting the unique material properties of GaN to deliver high current, high breakdown voltage and high switching frequency for a wide range of electronics applications. The CGD65A055S2 features CGD's ICeGaN™ gate technology enabling compatibility with virtually all gate drivers and controller chips available. The integrated current sense function eliminates a separate current sense resistor and the associated efficiency losses. Because no external sense resistor is needed, the device can be directly soldered to the large copper area of the ground plane, improving the thermal performance and simplifying the thermal design. It comes in a DFN 8x8 SMD package to support high frequency operation while ensuring the highest thermal performance.



Application & Topologies

PSUs, Industrial SMPS and inverters

- Server power and data centres
- Telecom rectifiers
- Gaming PSUs
- PC power
- LED drivers
- High power Class-D Audio
- General purpose SMPS
- PV inverters
- SMPS and converters in single-switch and halfbridge topologies with hard- or soft-switching
- AC/DC inverters
- Totem pole and single-switch PFC
- Forward, flyback and LLC converters at high frequency







Figure 1. Exemplary Application Circuit



PIN	NAME	DESCRIPTION
1-8	Drain	Power HEMT drain
9-12	Source	Power HEMT source, thermal pad
13	Kelvin Source	Kelvin source connection (internally tied to power HEMT source), reference
		potential for gate voltage.
14	Gate	Gate signal input.
		Recommended gate-drive voltage: V_{drive} (V_{GS} in on-state) = 9 V to V_{DD} .
15	Current Sense	Current sense output, relative to source, non-isolated.
16	V _{DD}	ICeGaN™ gate supply voltage (recommended at 12 V), relative to source.

Figure 2. Pin Configuration and Functions

Datasheet 1.0 – December 2022

Absolute Maximum Ratings

 T_{case} = 25 °C if not listed.

PARAMETER		VALUE	UNIT
Operating Junction Temperature	TJ	-55 to +150	°C
Storage Temperature Range	Ts	-55 to +150	°C
Drain-to-Source Voltage	V _{DS}	650	V
Drain-to-Source Voltage - transient ¹	V _{DS(transient)}	750	V
Gate-to-Source Voltage	V _{GS}	-1 to +20	V
		and V _{GS} ≤ V _{DD}	
Gate-to-Source Voltage - transient ²	V _{GS(transient)}	-1.5 to +21.5 and	V
		$V_{GS} \leq V_{DD} + 1.5$	
Current Sense Voltage	V _{CS}	-1.5 to 1.5	V
ICeGaN™ Gate Supply Voltage	V_{DD}	0 to +20	V
Continuous Drain Current (T _{case} = 25 °C)	I _D	27	Α

The recommended range of operation for V_{drive} (V_{GS} in on-state) and V_{DD} is 9 V to 20 V, enabling simple integration with a large variety of control chips and gate drivers.

Recommended maximum operating case temperature: T_{case} = 125 °C.

 $^{^{1}}$ Non-repetitive pulsed conditions, < 1 ms.

 $^{^{\}scriptscriptstyle 2}$ Non-repetitive pulsed conditions.

Electrical Characteristics

Values at $T_J = 25$ °C, $V_{DD} = 12$ V if not listed. To turn the device on the recommended gate voltage range is $V_{GS} = 9$ V to V_{DD} . To turn the device off set $V_{GS} = 0$ V. An integrated Miller Clamp eliminates the need for negative gate voltages.

STATIC CHARACTERISTICS

PARAMETER		CONDITIONS	MIN	TYP	MAX	UNIT
Drain-to-Source Blocking Voltage	BV _{DS}	$V_{GS} = 0 \text{ V}, I_{DSS} = 20 \mu\text{A}$	650			V
Drain-to-Source On Resistance	R _{DS(on)}	$V_{GS} = 12 \text{ V}, I_D = 2.2 \text{ A}$		55	77	mΩ
Drain-to-Source On Resistance	R _{DS(on)}	T _J = 150 °C		145		mΩ
		$V_{GS} = 12 \text{ V}, I_D = 2.2 \text{ A}$				
Source-to-Drain Voltage	V _{SD(on)}	$V_{GS} = 0 \text{ V}, I_D = 2.2 \text{ A}$		2.0	3.7	V
Gate-to-Source Threshold	V _{GS(th)}	$V_{DS} = 0.1 \text{ V}, I_{D} = 10 \text{ mA}$	2.2	2.9	4.2	V
Gate-to-Source Threshold	V _{GS(th)}	T _J = 150 °C		2.6		V
		$V_{DS} = 0.1 \text{ V}, I_{D} = 10 \text{ mA}$				
Gate-to-Source Current	I _{GS}	$V_{GS} = 12 \text{ V}, V_{DS} = 0 \text{ V}$		2.7	3.7	mA
Gate-to-Source Current	I _{GS}	T _J = 150 °C		2.5		mA
		$V_{GS} = 12 \text{ V}, V_{DS} = 0 \text{ V}$				
V _{DD} current	I _{VDD}	$V_{GS} = 12 \text{ V}, V_{DS} = 0 \text{ V}$		1.7	2.8	mA
V _{DD} current	I _{VDD}	T _J = 150 °C		1.0		mA
		$V_{GS} = 12 \text{ V}, V_{DS} = 0 \text{ V}$				
Drain-to-Source Leakage Current	I _{DSS}	$V_{GS} = 0 \text{ V}, V_{DS} = 650 \text{ V}$		0.7	20	μΑ
Drain-to-Source Leakage Current	I _{DSS}	T _J = 150 °C		30		μΑ
		$V_{GS} = 0 \text{ V}, V_{DS} = 650 \text{ V}$				

DYNAMIC CHARACTERISTICS

PARAMETER		CONDITIONS	MIN	TYP	MAX	UNIT
Output Capacitance	Coss	$V_{DS} = 400 \text{ V}, V_{GS} = 0 \text{ V}$		66		рF
		f = 100 kHz				
Output Charge	Qoss	$V_{DS} = 400 \text{ V}, V_{GS} = 0 \text{ V}$		63		nC
Total Gate Charge ³	Q_{G}	$V_{DS} = 400 \text{ V}, V_{GS} = 012 \text{ V}$		6.0		nC
		I _D = 10 A, I _G = 20 mA				
Reverse Recovery Charge	Q _{RR}	$I_S = 8 \text{ A}, V_{DS} = 400 \text{ V}$		0		nC
Turn-on delay time	t _{d(on)}	See Figure 17 and Figure 18		7		ns
Turn-off delay time	t _{d(off)}	See Figure 17 and Figure 18		23		ns
Rise time	t _r	See Figure 17 and Figure 18		7		ns
Fall time	t _f	See Figure 17 and Figure 18		7		ns

³ Turn-on gate charge value is listed. Turn-off gate charge value is lower, because ICeGaN™ gate discharges the gate internally.

_

Datasheet 1.0 – December 2022

CURRENT SENSING

Please refer to the application note CG-AN2206: Current Sensing with ICeGaN™. Please contact CGD for advice on the use of the current sense function.

ESD RATING

PARAMETER		CONDITIONS	MIN	TYP	MAX	UNIT
ESD withstand rating	НВМ	Human Body Model	2000			V
		(per JEDEC JS-001-2017)				

Thermal Characteristics

Typical values unless otherwise specified.

PARAMETER		CONDITIONS	VALUE	UNIT
Thermal resistance, junction to case	R _{th(JC)}		1.3	°C/W
Maximum reflow soldering temperature	T _{reflow}	MSL 3	260	°C



Figures

Figures at $T_J = 25$ °C, $V_{DD} = 12$ V if not specified.




Figure 3. Normalized thermal transient impedance ($Z_{th,JC}$) as a function of pulse width.




Figure 4. Safe Operating Area (SOA) based on thermal impedance $Z_{th,JC}$ at $T_{CASE} = 25$ °C.




Figure 5. Forward output characteristics at $T_J = 25$ °C.




Figure 6. Forward output characteristic at $T_J = 150$ °C.




Figure 7. Reverse output characteristics at $T_J = 25$ °C.




Figure 8. Reverse output characteristics at T_J = 150 °C.






Figure 9. Drain leakage current characteristics at T_J = 25 °C and T_J = 150 °C.




Figure 10. On-state resistance as a function of drain current at $T_J = 25$ °C.




Figure 11. On-state resistance as a function of junction temperature at $V_{GS} = 12 \text{ V}$.




Figure 12. Transfer characteristics at $V_{DS} = 0.1 \text{ V}$, $T_J = 25 \text{ }^{\circ}\text{C}$.





Figure 13. Transfer characteristics at $V_{DS} = 0.1 \text{ V}$, $T_J = 150 \text{ }^{\circ}\text{C}$.








Figure 14. Typical output capacitance C_{OSS} vs. V_{DS} at 100 kHz, $T_J = 25$ °C.

Figure 15. Typical output charge Q_{OSS} vs. V_{DS} at 100 kHz, $T_J = 25$ °C.




Figure 16. Typical C_{OSS} stored energy E_{OSS} vs. V_{DS} at $T_J = 25$ °C.




Figure 17. Inductive switching circuit. $I_D=10$ A, $R_{g(on)}=15$ Ω , $R_{g(off)}=2$ Ω , $V_{DD}=12$ V, $V_{DC}=400$ V, L=125 μH , diode = IDH04G65C5.




Figure 18. Switching waveform timing definitions.






Figure 19. Q_G gate charge characterization circuit. I_G =20 mA, V_{DC} = 400 V, V_{DD} =12V, L = 125 μ H, freewheeling diode = IDH04G65C5.




Figure 20. Q_G gate charge characterisation waveform at $I_G = 20$ mA and $V_{DD} = 12$ V. Time intervals t1 and t2 indicate the integration boundaries to calculate Q_G from I_G at turn-on and turn-off. Turn-off gate charge is lower than turn-on gate charge.




Packaging

DFN8x8 mm.

PIN NUMBER	NAME
1-8	Drain
9-12	Source
13	Kelvin Source
14	Gate
15	Current Sense
16	V _{DD}






Like any unwanted electronic device, CGD components should be recycled or otherwise disposed of in accordance with local laws and regulations.




Tape and Reel Information





Tape Trailer - a minimum length of 160mm empty cavities sealed with cover tape. Tape Leader - a minimum length of 400mm empty cavities sealed with cover tape.



Isometric View







Detail "A"

7 " Reel Dimensions (mm)					
	Min				
W1		22.2			
W2	16.6	17.1			
Α	178.5	181.5			
В	60				
С	20.2				
D	1.5	2.5			
E	12.8	13.5			

T

Version History

This version is 1.0

VERSION	DESCRIPTION	DATE	ВҮ
1.0	Initial Release	December 2022	MA, AB, JZ

Dare to innovate differently



Cambridge GaN Devices Limited
Jeffreys Building, Suite 8
St John's Innovation Park
Cambridge

CB4 0DS













Disclaimer

Information presented here by Cambridge GaN Devices Limited is believed to be correct and accurate. Cambridge GaN Devices Limited shall not be liable to any recipient or third part for any damages, including (but not limited to) personal injury, property damage, loss of profits, loss of business opportunity, loss of use, interruption of business, or indirect, special, incidental or consequential damages of any kind in connection with, or arising from, the use or performance of the data herein.

No obligation or liability to the recipient or third part shall arise from Cambridge GaN Devices Limited providing technical or other services. CGD reserves the right to modify the products and/or specifications described herein at any time and at Cambridge GaN Devices' sole discretion. All information in this document, including descriptions of product features or performance, is subject to change without notice.