

3-conductor ground terminal block; 2.5 mm<sup>2</sup>; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP<sup>®</sup>; 2,50 mm<sup>2</sup>; green-yellow



https://www.wago.com/2002-1307



Color: Margen-yellow



Similar to illustration

#### **Electrical data**

Ratings per	IEC/EN 60947-7-2		
Overvoltage category	III	Ш	Ш
Pollution degree	3	2	2
Nominal voltage	-	-	-
Rated surge voltage	-	-	-
Rated current	-	-	-

#### Ex information

Reference hazardous areas

See "Downloads – Documentation – Additional Information: Technical Section; Technical Explications"

#### **Connection data**

Connection points	3
Total number of potentials	1
Number of levels	1
Number of jumper slots	2

Connection 1	
Connection technology	Push-in CAGE CLAMP®
Actuation type	Operating tool
Connectable conductor materials	Copper
Nominal cross-section	2.5 mm²
Solid conductor	0.25 4 mm² / 22 12 AWG
Solid conductor; push-in termination	0.75 4 mm² / 18 12 AWG
Fine-stranded conductor	0.25 4 mm² / 22 12 AWG
Fine-stranded conductor; with insulated ferrule	0.25 2.5 mm² / 22 14 AWG

# Data Sheet | Item Number: 2002-1307 https://www.wago.com/2002-1307



Connection 1	
Connection 1	
Fine-stranded conductor; with ferrule; push-in termination	1 2.5 mm² / 18 14 AWG
Note (conductor cross-section)	Depending on the conductor characteri- stic, a conductor with a smaller cross- section can also be inserted via push-in termination.
Strip length	10 12 mm / 0.39 0.47 inches
Wiring direction	Front-entry wiring

Physical data	
Width	5.2 mm / 0.205 inches
Height	59.2 mm / 2.33 inches
Depth from upper-edge of DIN-rail	32.9 mm / 1.295 inches

Mechanical data	
Mounting type	DIN-35 rail
Marking level	Center/side marking

Information on material specifications can be found here
green-yellow
I
Polyamide (PA66)
VO
0.124 MJ
9.1 g

Environmental requirements	
Processing temperature	-35 +85 ℃
Continuous operating temperature	-60 +105 ℃

Commercial data	
Product Group	22 (TOPJOB S)
eCl@ss 10.0	27-14-11-41
eCl@ss 9.0	27-14-11-41
ETIM 8.0	EC000901
ETIM 7.0	EC000901
PU (SPU)	100 pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332999274
Customs tariff number	85369010000

https://www.wago.com/2002-1307

#### **Environmental Product Compliance**

**RoHS Compliance Status** 

# N/AGO

Compliant,No Exemption

#### Approvals / Certificates

#### **General approvals**



Approval	Standard	Certificate Name
CCA DEKRA Certification B.V.	EN 60947	NTR NL 7941
CSA DEKRA Certification B.V.	C22.2 No. 158	1536069
KEMA/KEUR DEKRA Certification B.V.	EN 60947	71-124163
UL Underwriters Laboratories Inc.	UL 1059	E45172

#### Declarations of conformity and manufacturer's declarations



Approval	Standard	Certificate Name
ATEX-Attestation of Con- formity WAGO GmbH & Co. KG	-	-
EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-
Railway WAGO GmbH & Co. KG	-	Railway Ready
UK-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-

#### Approvals for marine applications

.ABS.

BUREAU VERITAS		
Approval	Standard	Certificate Name
ABS American Bureau of Ship- ping	EN 60947	20-HG1941090-PDA
BV Bureau Veritas S.A.	EN 60947	38586/B0 BV
DNV GL Det Norske Veritas, Ger- manischer Lloyd	-	TAE00001V2

#### Approvals for hazardous areas

$\frac{AEx\text{ell}}{Ex\text{ell}} \left< Ex \right> EI$	RE Ex IECEX	
Approval	Standard	Certificate Name
AEx Underwriters Laboratories Inc.	UL 60079	E185892 (AEx eb IIC resp. Ex eb IIC)
ATEX Physikalisch Technische Bundesanstalt	EN 60079	PTB 03 ATEX 1162 U (II2G Ex eb IIC Gb, IM2 Ex eb IMb)
CCC CNEX	GB/T 3836.3	2020312313000238 (Ex eb IIC Gb, Ex eb I Mb)
EAC Brjansker Zertifizierungs- stelle	TP TC 012/2011	RU C-DE.AM02. B.00127/19 (Ex e IIC Gb U)
IECEx Physikalisch Technische Bundesanstalt	IEC 60079	IECEx PTB 03.0004U (Ex eb IIC Gb or Ex eb I Mb)
INMETRO TÜV Rheinland do Brasil Ltda.	IEC 60079	TÜV 12.1307 U

# Downloads Environmental Product Compliance Compliance Search

 $\downarrow$ 

Environmental Product Compliance 2002-1307




https://www.wago.com/2002-1307



Documentation						
Additional Information			Bid Text			
Technical Section	pdf 2240.62 KB	$\underline{\downarrow}$	2002-1307	29.04.2019	xml 3.80 KB	$\underline{\downarrow}$
			2002-1307	23.04.2019	docx 14.60 KB	$\underline{\downarrow}$

CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 2002-1307	EPLAN Data Portal 2002-1307
	WSCAD Universe 2002-1307
	ZUKEN Portal 2002-1307





#### Installation Notes

#### **Conductor termination**



All conductor types at a glance



Push-in termination of solid and ferruled conductors



Inserting a conductor via push-in termination:

Solid conductors with cross-sections from either one size above, or up to two sizes below, the rated cross-section can be simply pushed in – no tools needed.



Inserting a conductor via operating tool: Connecting fine-stranded conductors without ferrules, or small cross-sectional conductors that cannot be pushed in, is performed similarly to the original CAGE CLAMP® – just use an operating tool. Advantage:

To open the clamp, the operating tool is inserted vertically. The conductor entry is less than 15 degrees for easier wiring.

https://www.wago.com/2002-1307

#### **Conductor termination**





Conductor termination - insulation stop

#### Commoning





Insert push-in type jumper bar and push down until it hits backstop.

Removing a push-in type jumper bar: Insert the operating tool between the jumper and partition wall of the dual jumper slots, then lift up the jumper. Place the operating tool in the center of jumpers for up to five contacts (see above), or alternately on both sides for jumpers with more than five contacts.

#### Commoning







Removing a staggered jumper: Insert the operating tool between the staggered jumpers, then lift up the jumper.

#### Commoning



Continuous jumpers (2002 Series) readily connect an endless number of terminal blocks to each other via single jumper slot. Use the second jumper slot for additional commoning or testing.



Push down the wire jumper until fully inserted. Lift the jumper with an operating tool for rewiring.



The 1-to-3 adjacent jumper for continuous commoning enables every other terminal block to be commoned. For example, positive and negative potentials can be accommodated alongside each other.



This star point jumper has been specially developed to create a "star point" and is used on motor terminal boards equipped with Rail-Mount Terminal Blocks TOP-JOB® S.



This delta jumper has been specially developed to create a delta configuration and is used on motor terminal boards equipped with rail-mount terminal blocks TOPJOB® S.

https://www.wago.com/2002-1307







The modular TOPJOB® S connectors also connect conductors of the same size as the terminal blocks being used.



Test plug adapter (2009-174, CAT I) for 4 mm Ø plugs – compatible with 2000 to 2016 Series



TOPJOB® S Connectors with a 2 mm Ø test socket for testing voltage via 2-pole voltage tester



Testing tap (2009-182) for tool-free connection of test cables up to 2.5 mm<sup>2</sup> (12 AWG) – compatible with 2000 to 2016 Series



Rail-mount terminal block assembly for electric motor wiring



L-type test plug module – cross-sectional view of contacts





Snapping WMB Inline markers into marker slots.





TOPJOB® S 2009-193 Group Marker Carrier (equipped with a marking strip) for all 2001 to 2016 Series TOPJOB® S Rail-Mount Terminal Blocks Do not use on an end plate!



Using marker carriers for marking strips (2002-161) in jumper slots.

Subject to changes. Please also observe the further product documentation!