4-conductor ground terminal block;  $4 \text{ mm}^2$ ; suitable for Ex e II applications; side and center marking; for DIN-rail  $35 \times 15$  and  $35 \times 7.5$ ; Push-in CAGE CLAMP®;  $4,00 \text{ mm}^2$ ; green-yellow




https://www.wago.com/2004-1407





Color: green-yellow



Similar to illustration

#### Electrical data

Ex			

Reference hazardous areas See "Downloads – Documentation – Additional Information: Technical Section;

Technical Explications"

## Connection data Connection points 4 Total number of potentials 1 Number of levels 1 Number of jumper slots 2

Connection 1	
Connection technology	Push-in CAGE CLAMP®
Actuation type	Operating tool
Connectable conductor materials	Copper
Nominal cross-section	4 mm²
Solid conductor	0.5 6 mm² / 20 10 AWG
Solid conductor; push-in termination	1.5 6 mm² / 14 10 AWG
Fine-stranded conductor	0.5 6 mm² / 20 10 AWG
Fine-stranded conductor; with insulated ferrule	0.5 4 mm² / 20 12 AWG
Fine-stranded conductor; with ferrule; push-in termination	1.5 4 mm² / 18 12 AWG

https://www.wago.com/2004-1407



#### Connection 1

Note (conductor cross-section) Depending on the conductor characteri-

stic, a conductor with a smaller crosssection can also be inserted via push-in

termination.

Strip length 11 ... 13 mm / 0.43 ... 0.51 inches

Wiring direction Front-entry wiring

Physical data	
Width	6.2 mm / 0.244 inches
Height	78.7 mm / 3.098 inches
Depth from upper-edge of DIN-rail	32.9 mm / 1.295 inches

#### Mechanical data

Mounting type DIN-35 rail

Marking level Center/side marking

# Material dataNote (material data)Information on material specifications can be found hereColorgreen-yellowMaterial groupIInsulation materialPolyamide (PA66)Flammability class per UL94V0Fire load0.174 MJWeight16.7 g

Environmental requirements		
	Processing temperature	-35 +85 °C
	Continuous operating temperature	-60 +105 °C

Commercial data	
Product Group	22 (TOPJOB S)
eCl@ss 10.0	27-14-11-41
eCl@ss 9.0	27-14-11-41
ETIM 8.0	EC000901
ETIM 7.0	EC000901
PU (SPU)	50 pcs
Packaging type	Вох
Country of origin	DE
GTIN	4017332071833
Customs tariff number	85369010000



#### **Environmental Product Compliance**

RoHS Compliance Status Compliant, No Exemption

#### Approvals / Certificates

#### General approvals







Approval	Standard	Certificate Name
CCA DEKRA Certification B.V.	EN 60947	71-125978
CCA DEKRA Certification B.V.	EN 60947	NTR NL-7964
CSA DEKRA Certification B.V.	C22.2 No. 158	1645435
UL Underwriters Laboratories Inc.	UL 1059	E45172

#### Declarations of conformity and manufacturer's declarations



Approval	Standard	Certificate Name
ATEX-Attestation of Conformity WAGO GmbH & Co. KG	-	-
EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
Railway WAGO GmbH & Co. KG	-	Railway Ready
UK-Declaration of Conformity WAGO GmbH & Co. KG	-	-

#### Approvals for marine applications



Approval	Standard	Certificate Name
DNV GL Det Norske Veritas, Ger- manischer Lloyd	-	TAE00001V2

#### Approvals for hazardous areas





Approval	Standard	Certificate Name
AEx Underwriters Laboratories Inc.	EN 60079	E185892 (AEx eb IIC resp. Ex eb IIC)
ATEX Physikalisch Technische Bundesanstalt (PTB)	EN 60079	PTB 05 ATEX 1095 U (II 2 G Ex eb IIC Gb bzw. I M 2 Ex eb I Mb)
CCC CNEX	GB/T 3836.3	2020312313000160 (Ex eb IIC Gb, Ex eb I Mb)
EAC Brjansker Zertifizierungs- stelle	TP TC 012/2011	RU C-DE.AM02. B.00127/19 (Ex e IIC Gb U)
IECEx Physikalisch Technische Bundesanstalt (PTB)	IEC 60079	IECEx PTB 05.0033 U (Ex eb IIC Gb resp. Ex eb I Mb)
INMETRO TÜV Rheinland do Brasil Ltda.	IEC 60079	TÜV 12.1309 U

#### Downloads

#### **Environmental Product Compliance**

#### Compliance Search


**Environmental Product** Compliance 2004-1407





https://www.wago.com/2004-1407



#### 








#### **Conductor termination**







Push-in termination of solid and ferruled conductors



Inserting a conductor via push-in termination:

Solid conductors with cross-sections from either one size above, or up to two sizes below, the rated cross-section can be simply pushed in – no tools needed.



#### **Inserting a conductor via operating tool:**Connecting fine-stranded conductors wi-

thout ferrules, or small cross-sectional conductors that cannot be pushed in, is performed similarly to the original CAGE CLAMP® – just use an operating tool.

#### Advantage:

To open the clamp, the operating tool is inserted vertically. The conductor entry is less than 15 degrees for easier wiring.

### W/AGO

#### Conductor termination



Conductor termination – insulation stop

#### Commoning



Insert push-in type jumper bar and push down until it hits backstop.



Removing a push-in type jumper bar: Insert the operating tool between the jumper and partition wall of the dual jumper slots, then lift up the jumper. Place the operating tool in the center of jumpers for up to five contacts (see above), or alternately on both sides for jumpers with more than five contacts.


#### Commoning



This star point jumper has been specially developed to create a "star point" and is used on motor terminal boards equipped with Rail-Mount Terminal Blocks TOPJOB® S



This delta jumper has been specially developed to create a delta configuration and is used on motor terminal boards equipped with rail-mount terminal blocks TOPJOB® S.



Push down the wire jumper until fully inserted. Lift the jumper with an operating tool for rewiring.

#### **Testing**



The modular TOPJOB® S connectors also connect conductors of the same size as the terminal blocks being used.



TOPJOB® S Connectors with a 2 mm Ø test socket for testing voltage via 2-pole voltage tester



Rail-mount terminal block assembly for electric motor wiring



Test plug adapter (2009-174, CAT I) for 4 mm Ø plugs – compatible with 2000 to 2016 Series



Testing tap (2009-182) for tool-free connection of test cables up to 2.5 mm<sup>2</sup> (12 AWG) – compatible with 2000 to 2016 Series

https://www.wago.com/2004-1407



#### Marking









TOPJOB® S 2009-193 Group Marker Carrier (equipped with a marking strip) for all 2001 to 2016 Series TOPJOB® S Rail-Mount Terminal Blocks
Do not use on an end plate!

Subject to changes. Please also observe the further product documentation!