



Non-contact voltage testers



Order data

Order number	473010
GTIN	4045197554239
Item class	42I

Description

Version:

Compact two-component plastic casing with integral LED torch. Prods with visual indication of voltage by colour change (green to red) and additional acoustic signal. Easily transported, fits any pocket.

Function:

IP40: Protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away, and offers no protection against water.

Application:

For non-contact detection of live conductors, e.g. in cables, sockets, junction boxes etc.

Standard:

IEC/EN 61010-1.

Supplied with:

2 batteries No. 081551 size LR3.

IP Index of Protection: IP 40

Display range AC: 50 - 1000 V

Overvoltage category: CAT IV / 1000 V

Article no of the battery / rechargeable battery fitted: 081561 LR3

Technical description

Display range AC	50 - 1000 V
IP Index of Protection	IP 40
Overvoltage category	CAT IV / 1000 V
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081561 LR3

Power supply	Battery-powered
Type of product	Voltage tester

Accessories

Alkaline-manganese batteries International size LR3	081556 LR3
Alkaline-manganese batteries International size LR3	081561 LR3