RF Components

Balun transformers Wound SMD ATB series

ATB3225 type


FEATURES

- \bigcirc The ATB3225 case size is L3.2 \times W2.5 \times H2.3mm.
- The case size is smaller than conventional Baluns.
- The frequency band width for ATB3225-75011CT is 5 to 200MHz, for ATB3225-75032CT is 5 to 100MHz, for ATB3225-75034CT is 1 to 100MHz, and for ATB3225-50011CT is 1 to 100MHz.
- O Low insertion loss and good balance parameters.

APPLICATION

O Cable modem

PART NUMBER CONSTRUCTION



CHARACTERISTICS SPECIFICATION TABLE

DC resistance	Impedance ratio	Frequency range	Insertion loss	Return loss	Amplitude unbalance	Phase difference	Part No.
(Ω)max.		(MHz)	(dB)max.	(dB)min.	(dB)max.	(deg.)	
0.7	1:1 (75Ω:75Ω)	5 to 65	0.8	15	0.1	180±2	- <u>ATB3225-75011CT-T001</u>
		5 to 200	1.5	10	0.5	180±5	
0.7	3:2 (75Ω:50Ω)	5 to 100	2	5	1	180±10	ATB3225-75032CT-T001
0.7	3:4 (75Ω:100Ω)	1 to 100	2	5	0.1	180±10	ATB3225-75034CT-T000
0.7	1:1(50Ω: 50Ω)	1	0.8	15	0.1	180±2	- ATB3225-50011CT-T000
		100	1.5	10	0.5	180±5	

* Temperature derating was considered for the rated current.

Measurement equipment

Measurement item	Product No.	Manufacturer			
Insertion loss	E5071B	Keysight Technologies			
Return loss	E5071B	Keysight Technologies			
Amplitude unbalance	E5071B	Keysight Technologies			
Phase difference	E5071B	Keysight Technologies			

* Equivalent measurement equipment may be used.



. (1/5) 20190325






⊗TDK

ATB3225 type


FREQUENCY CHARACTERISTICS

ATB3225-75011CT-T001

INSERTION LOSS




AMPLITUDE UNBALANCE




ATB3225-75032CT-T001


INSERTION LOSS




AMPLITUDE BALANCE




RETURN LOSS




PHASE UNBALANCE



RETURN LOSS



PHASE BALANCE




ATB3225 type


FREQUENCY CHARACTERISTICS

ATB3225-75034CT-T000


□ INSERTION LOSS




AMPLITUDE IMBALANCE



RETURN LOSS




PHASE BALANCE




ATB3225-50011CT-T000


□ INSERTION LOSS




AMPLITUDE IMBALANCE



RETURN LOSS




PHASE BALANCE




Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use.
(3/5)
Please note that the contents may change without any prior notice due to reasons such as upgrading.
20190325

ATB3225 type

SHAPE & DIMENSIONS



RECOMMENDED LAND PATTERN



CIRCUIT DIAGRAM

Unbalance port

¹~____•

60

4

Ŷ

Balance port


GND

or Vcc

RECOMMENDED REFLOW PROFILE


03

PACKAGING STYLE





Dimensions in mm

TAPE DIMENSIONS



Dimensions in mm





Dimensions in mm

PACKAGE QUANTITY

Package quantity

TEMPERATURE RANGE, INDIVIDUAL WEIGHT

1000 pcs/reel

Operating temperature range	Storage temperature range*	Individual weight
–40 to +85°C	–40 to +85°C	75 mg

* The storage temperature range is for after the assembly.

Preheating Peak 230°C 150°C 60 to 120s Soldering Peak 245°C 230°C 5s max. 10 to 30s

Time

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.

RF Components

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

▲ REMINDERS ○ The storage period is within 6 months. Be sure to follow the storage conditions (temperature: 5 to 40°C, humidity: 10 to 75% RH or less). If the storage period elapses, the soldering of the terminal electrodes may deteriorate. O Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.). Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperature does not exceed 150°C. O Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur. O When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions. ○ Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design. Carefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference. ○ Use a wrist band to discharge static electricity in your body through the grounding wire. O Do not expose the products to magnets or magnetic fields. O Do not use for a purpose outside of the contents regulated in the delivery specifications. O The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition. The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property. If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions set forth in the each catalog, please contact us. (1) Aerospace/aviation equipment (8) Public information-processing equipment (2) Transportation equipment (cars, electric trains, ships, etc.) (9) Military equipment (3) Medical equipment (10) Electric heating apparatus, burning equipment (4) Power-generation control equipment (11) Disaster prevention/crime prevention equipment (12) Safety equipment (5) Atomic energy-related equipment (6) Seabed equipment (13) Other applications that are not considered general-purpose (7) Transportation control equipment applications When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (5/5)Please note that the contents may change without any prior notice due to reasons such as upgrading.