Specifications

Drawing No.	USY1N-H1-23097-00
Issued Date.	Sep,05.2023

Messrs: Kyocera AVX

Note: Part numbers may be revised in the event of any specifications change.

Product Type	Tuning Fork Crystal		
Series	DT3215DB		
Frequency	32.768kHz		
Customer Part Number	-		
Customer Specification Number	-		
KYOCERA Part Number	DT3215DB32768C0HPWAA		
Remarks Pb-Free, RoHS Compliant, MSL 1			

Customer Approval

pproved Date
Department
rson in charge

Seller

KYOCERA Corporation

Corporate Electronic Components Group Electronic Components Sales Division 6 Takeda Tobadono-cho, Fushimi-ku, Kyoto 612-8501 Japan TEL. No. 075-604-3500 FAX. No. 075-604-3501

Manufacturer

Corporate Electronic Components Group Electronic Devices Division Shiga Yohkaichi Plant 1166-6 Hebimizo-cho, Higashiomi, Shiga 527-8555 Japan TEL: 81-748-22-1550 FAX: 81-748-22-1590

Design Department	Quality Assurance	Approved by	Examined by	Written by
KYOCERA Corporation Corporate Electronic Components Group Electronic Devices Division	E.Kimura	A.Iwaguchi	K.Takahashi	H.Ebara

Drawing No. USY1N-H1-23097-00

Revision History

Rev.No.	Description of revise	Date	Approved by	Examined by	Written by
00	First Edition	Sep,05,2023	A.Iwaguchi	K.Takahashi	H.Ebara

1. APPLICATION

This specification sheet is applied to tuning fork crystal "DT3215DB".

2. KYOCERA PART NUMBER

DT3215DB32768C0HPWAA

3. RATINGS


Items	SYMB.	Rating	Unit
Operating Temperature	Topr	-40~+85	C°
Storage Temperature range	Tstg	-40~+85	С°

4. CHARACTERISTICS


4-1 ELECTRICAL CHARACTERISTICS

Itom	Sumbol	Electrical Specification				
Item	Symbol	Condition	Min	Тур.	Max	Unit
Nominal Frequency	fo	Ta = 25°C		32.768		kHz
Frequency Tolerance	df/fo	$Ta = 25^{\circ}C \pm 3^{\circ}C$	-20	-	20	ppm
Load Capacitance	CL		-	7.0	-	pF
Equivalent series resistance	R1		-	-	50	kΩ
Q-Value	Q		-	39000	-	
Motional capacitance	C1		-	3.6	-	fF
Shunt capacitance	Со		-	1.3	-	pF
Turning point	Тр		20	25	30	°C
Secondary temperature Coefficient	к		-	-	-0.04	10 ⁻⁶ /°C ²
Aging	df/F	Ta = 25°C	-3	-	3	ppm/year
Drive level	DL		-	0.2	1.0	μW
Insulation resistance (between electrodes)	IR	DC 100 ± 15V	500			MΩ

5. APPEARANCES, DIMENSION



CONNECTION (TOP VIEW)



UNIT : mm


MARKING

- (1.) Identification
- (2.) Date Code (3 Digits)
- (3.) Load Capacitance
- (4.) Manufacturing Location

K

igits) Last 1 digit of year and week Code. (Ex) 2023.Jan.1 \rightarrow 301 ce (Ex) 7.0pF \rightarrow C location Overseas \rightarrow C *The font of marking above is for reference purpose.

6. RECOMMENDED LAND PATTERN





7. TAPING


7.1 Specification

1. Material of the carrier tape is polystyrene and carbon.


- 2. Material of the cover tape is polyester.
- 3. The seal tape shall not cover the sprocket holes and not protrude from the carrier tape.
- 4. The alignment between centers of the cavities and sprocket holes is 0.05mm or less.
- 5. The orientation shall be checked from the top cover tape side.
- 6. Peeling force of the cover tape: 0.1 to 0.7N.








7-2 Emboss Taping specifications



symbol	А	В	С	D	E	F
Dimension	2.0±0.1	4.0±0.1	1.55±0.05	4.0±0.1	5.5±0.05	1.75±0.1
Symbol	G	Н	J	L	Ν	Т
Dimension	12.0±0.2	φ1.05±0.05	3.4 <u>±</u> 0.05	1.7±0.05	0.95±0.05	0.25±0.05

(Unit: mm)

7-3 Reel specifications



6180 Reel (3,000 pcs Max.)


Symbol	Р	Q	R
Dimension	ф180+0.0/-3.0	ф60 + 1.0/-0.0	φ13 ± 0.2
Symbol	S	U	W
Dimension	10.5±0.4	2.0±0.5	13.0±0.3
			(1 1-1

(Unit: mm)

Drawing No. USY1N-H1-23097-00


8.Enviromental requirements

8.1	Shock(Mounting Drop)	After the following test, parts shall conform specification table-1-B.		
			n 150cm heights to concrete. ered on substrate, fixed aluminum materials(about 100g) : FR-4, t=1.6mm : each 1time of 6directions	
8.2	Shock(Acceleration)	After the following test, parts	s shall conform specification table-1-B.	
		1000m/s2 by 6ms X,Y,Z ea	ch axis (6directions), 10cycles	
8.3	Vibration	After the following test, parts	s shall conform specification table-1-A	
		and no abnormal appearar	nce shall be observed.	
		(1)Frequency of Vibration :	10~2000Hz	
		(2)Amplitude total : sine wa	ves of 1.5mm (10~55Hz) and 200m/s2 (55~2000Hz)	
		(3)Vibration axis : X,Y,Z		
		(4)Vibration period : 2h for e	each axis	
		(5)Cycle : 20minAfter the To	est condition	
8.4	High Temperature	2h past at room temperatur	e after following test, parts shall conform specification	
		table-1-B. 240h +85±2°CTe	est condition	
8.5	Low Temperature	2h past at room temperatur	e after following test, parts shall conform specification	
		table-1-B. 240h -40±2°C		
8.6	Humidity	2h past at room temperate	ure after following test, parts shall conform	
		specification table-1-B. 24	0h +85±2°C, relative humidity 85±5%	
8.7	Temperature Cycle	2h past at room temperature after 200cycles of following test, parts shall conform specification table-1-B.		



8.8 Reflow condition

Reflow temp.profile




ts [°C]	150 to 200
ts time [s]	60 to 120
TL[°C]	217
t time [s]	60 to 150
Tp [°C]	Max. 260
Tp [s]	Max. 30

Reflow soldering shall be allowed only 3times.

48h past at room temperature from following test, parts shall conform specification table-1-B.

8.9 Bending Strength After the following test, parts shall conform specification table-1-A and no abnormality shall be observed in external appearance and sealing tightness and others shall be based on ET-7403 of EIAJ.
Solder this product onto the center of a 40mm × 100mm circuit board, and add a deflection of 3mm as shown below.



8.10 Specification

Table-1

	Frequency variation	Series resistance variation
А	±5 x 10 ⁻⁶	±10kΩ
В	±10 x 10 ⁻⁶	±10kΩ

9. Cautions for use

(1) Soldering

Characteristics may be affected when Solder paste or conductive glue comes in contact with product lid or surface. Please perform reflow temp. profile within 3 times.

(2) When using mounting machine

Crystal products are designed to be compatible with automatic mounting. Be sure to have a mounting test in advance by using the actual mounting machine and check that the characteristics of the products are not damaged by the automatic mounting. In the process where the board is warped, such as board separation process, be careful that the warping does not influence the characteristics and soldering of crystal products. Since mounting by Ultrasonic Welding and processing have a possibility of an excessive vibration spreading inside a tuning fork crystal resonator and becoming the cause of characteristic deterioration and not oscillating, it does not recommend.

(3) Conformity of a circuit

We strongly recommend to make sure that Negative resistance (Gain) of IC is designed to be 3 times the ESR (Equivalent Series Resistance) of Crystal unit.

(4) Washing

About use of the washing liquid of a basin system, an alcoholic system, and a chlorofluorocarbon-replacing material system, it is checking that it is satisfactory. However please consult in advance about other washing liquid. Tuning fork crystal resonators should not have ultrasonic washing because their frequency band is close to the washing frequency band of ultrasonic washing machines, very probably causing resonance destruction. To use ultrasonic washing to clean these resonators, tests must be performed in advance under actual application conditions.

(5) Drive Level

The piece of crystal it is processed very smaller than the conventional thing inside DT3215DB series crystal unit may be damaged, if crystal resonators are exposed to an excessively high drive level. Please use the products within the limits specified in the catalogs and specifications.

(6) Handling of a product

DT3215DB series has sufficient intensity to fall and vibration. However, if a crystal product is pressed hard, be sure to check for any damages before using. Crystal resonators should not have pattern to avoid causing base crack.

(7) Application instructions

This product is designed to be used for general electronic device and is not designed in the high reliability application listed below.

Please inform the department in charge when using the product for following applications.

Utility in nuclear power plant	Traffic signal control system
Utility in space	security and disaster-prevention
Aircraft	Transporter (car, train, ship, etc.)
under water or ground	Medical

other - applications requires same environmental status as above.

This product must not be used in every application which are primary - intended to damage human race or their property.

Arms (missile, bomb and other application to damage human)

Weapons (transports act for combat)

Controller with primary – intended to military use.

KYOCERA Corporation

10. Storage conditions

Please store product in below conditions, and use within 6 months. Temperature +40°C max., and Humidity of 80% in the packaging condition.

11. Quality Assurance

Location

KYOCERA Corporation Shiga Yohkaichi Plant: Quality Assurance Division

12. Quality guarantee

In the case when KYOCERA Corporation rooted failure occurred within 1year after its delivery, substitute product will be arranged based on discussion. Quality guarantee of product after 1year of its delivery is waivered.

13. Others

In case of any questions or opinions regarding the Specification, please have it in written manner within 45 days after issued date.