

Water Flow Sensor YF-B5

SKU 114991175





Water flow sensor consists of a copper body, a water rotor, and a hall-effect sensor. When water flows through the rotor, rotor rolls. Its speed changes with different rate of flow. The hall-effect sensor outputs the corresponding pulse signal. This one is suitable to detect flow in water dispenser or coffee machine.

Life is longer than plastic body.

Features

- Compact, Easy to Install
- High Sealing Performance
- High Quality Hall Effect Sensor
- RoHS Compliant

Technical Details

Dimensions	0mm x0mm x0mm			
Weight	G.W 131g			
Battery	Exclude			
Mini. Working Voltage	DC 4.5V			
Max. Working Current	15mA (DC 5V)			
Working Voltage	DC 5V~15V			
Flow Rate Range	1~30L/min			
Frequency	F=(6.6*Q) Q=L/MIN±3%			
Load Capacity	≤10mA (DC 5V)			
Operating Temperature	0 ~ 80°C			
Liquid Temperature	≤120°C			
Operating Humidity	35% ~ 90%RH			
Water Pressure	≤1.75MPa			
Storage Temperature	25 ~ + 80°C			
Storage Humidity	25% ~ 95%RH			
Interface Dimensions	G3/4Inch			
Error Range	(1~25L\MIN) ±3%			
Material Description	H57Copper+POM			
Output Pulse High Level	>DC 4.7V (Input Voltage DC5V)			
Output Pulse Low Level	<dc (input="" 0.5v="" dc5v)<="" td="" voltage=""></dc>			
Output Pulse Duty Cycle	50%±10%			

ECCN/HTS

HSCODE	9026100000			
USHSCODE	9026104000			
EUHSCODE	9013101000			
coo	CHINA			
CE	4			

CE	1
EU DoC	1
RoHS	1

Part List

1 x YF-B5 Water Flow Sensor

Туре	Dimensions	Working	Flow Rate	Length	Male & Female	Length of	Material
	(DN)	Voltage	Range			Thread	
YF-B1	DN15	5V~15V(DC)	1~25L/min	44mm	Double Male	10mm	Copper
YF-B2	DN15	5V~15V(DC)	1~25L/min	50mm	Male in Female	10mm	Copper
					out		
YF-B3	DN15	5V~15V(DC)	1~25L/min	66mm	Double Male	18mm	Copper
YF-B4	DN15	5V~15V(DC)	1~25L/min	66mm	Male in Female	10mm	Copper
					out		
YF-B5	DN20	5V~15V(DC)	1~30L/min	50mm	Double Male	10mm	Copper
YF-B6	DN20	5V~15V(DC)	1~30L/min	60mm	Double Male	11mm	Copper
YF-B7	DN15	5V~15V(DC)	1~25L/min	66mm	Double Male	10mm	Copper
G1&2	DN15	5V~24V(DC)	1~30L/min		Double Male		Plastic
G3&4	DN20	5V~24V(DC)	1~60L/min		Double Male		Plastic
G1&2	DN15	5V~24V(DC)	1~30L/min	60mm	Double Male	13mm	Plastic
G1&8	-	5V~24V(DC)	0.3~6L/min	-	-	-	Plastic
M11*1.25	-	5V~24V(DC)	0.3~6L/min	-	-	-	Plastic