

# SMD CRYSTAL UNITS



### • E3SB Series



## 3225 Seam Sealing Crystal

#### **FEATURES**


- Compact and thin (3.2X2.5X0.75mm.)
- Excellent electrical performance, ideal for OA (office automation),
  AV (audiovisual), Bluetooth and Wireless LAN applications
- Excellent heat resistance and shock resistance.
- Lead-free. Meets the requirements for re-flow profiling using lead -free solder


### **Electrical Specifications**


Item	Туре	E3SB					
Frequency Range	F0	8.0 to 9.999MHz	10 to 19.99MHz	20 to 23.999MHz	24 to 62.500MHz	60 to 114.285MHz	
Mode of Vibration		Fundamental 3RD					
Load Capacitance	CL	6 to 20pF					
Frequency Tolerance	△ F/F0	±10ppm,±15ppm,±30ppm(At 25°C)					
Equivalent Series Resistance	ESR	500Ω max.	150Ω max.	70 Ω max.	50 Ω max.	100 Ω max.	
Temperature Stability	TC	$\pm 30$ ppm(Refer to 25°C)	30ppm(Refer to 25°C) $\pm 10$ ppm, $\pm 15$ ppm, $\pm 30$ ppm(Refer to 25°C)				
Operating Temperature Range	Topr	-20~+70°C, -30~+85°C Option					
Storage Temperature Range	Tstg	-55∼+125°C					
Shunt Capacitance	C0	3pF max.					
Insulator Resistance	IR	500M Ω min. (At 100Vpc)					
Drive Level	DL	100μW <b>(</b> 200μW max. <b>)</b>					
Aging	Fa	±2ppm max. (At 25°C, First year)					
Packing Unit		3000pcs/reel					

<sup>\*\*</sup>Please contact us for inquiries regarding other Specifications

### **Mechanical Dimensions(mm)**







#### Recommended Solder Pattern

