

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER ORIGINAL

ADD NOTE 7 & 8

P.M. AUG. 13/2023

SPECIFICATION:

1- MATERIAL:

CONTACT: BRASS, GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING

HOUSING: PA9T, BLACK

MAGNET: N52 2- ELECTRICAL:

RATED VOLTAGE (PER CONTACT): 5V

RATED CURRENT (PER CONTACT): 2A

INSULATION RESISTANCE: 100MEGAOHMS MINIMUM.


DIELECTRIC WITHSTANDING VOLTAGE: 100V AT 60Hz.

CONTACT RESISTANCE: 30mOHMS MAX. BEFORE TEST AND 60mOHMS MAX. AFTER TEST

- 3- WORKING STROKE ON SINGLE PIN: PRESS STROKE 0.9mm (PER CONTACT) 30gf MAX.
- 4- LIFE CYCLE TEST: 10,000 TIMES MIN.
- 5- SALT SPRAY TEST: 5% SALT SPRAY CONCENTRATION, TEMPERATURE 35°C, TEST TIME 48 HOURS, NO CORROSION.
- 6- WORKING TEMPERATURE RANGE: -30~+85°C.

7- RECOMMENDED SOLDERING PROCESS ARE SELECTIVE SOLDERING OR MANUAL SOLDERING, OTHER FORMS OF SOLDERING SUCH AS WAVE SOLDER OR REFLOW SOLDER ARE NOT RECOMMENDED AND CAN POTENTIALLY CAUSE DEMAGNETIZATION OF MAGNET IN THE CONNECTOR

8- MATING WITH: 686J0521250124E, 686J0521350124E, 686J0521450110E, 686J0521350110E OR 686J0521250110E



RECOMMENDED PCB LAYOUT (T:1.6mm) TOLERANCE UNSPECIFIED ±0.05mm

## MAGNETIC SPRING LOADED CONNECTOR, 5POS, MALE

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.

XP.50

**WORKING STROKE 0.90** 

21.30

8.00

4.00

19.30

10.50

9.50

 $\mathbb{N}$ 

- Ø0.80

3.80

5 - Ø 0.60

2.50

3.80

9 50

5,



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

	ACAD REFERENCE NO.: 685J0521351110E		UNIT: MM
	DRAWN: J.L.	DATE: 8/13/2023	
	CHECKED: R.S.M	DATE: 8/13/2023	
	SCALE: (IN CAD 1:1)	SHEET 1 OF	1
	DDAWING NUMBER: 605 I05242544405		ICCLIE

DRAWING NUMBER: 685J0521351110E ISSUE PART NUMBER: 685J0521351110E