TOLERANCE UNLESS OTHERWISE SPECIFIED .X ±0.15

.XX ±0.10


THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.





ISSUE NUMBER ORIGINAL ADD NOTE 4 & 5


P.M. AUG. 10/2023 **DELETE DIM R2.25, R2.65** 

AUG. 18/2023









**PCB LAYOUT** LAYOUT TOLERANCE: ±0.05MM SPECIFICATION:

1- MATERIAL:

CONTACT: BRASS, GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING

HOUSING: LCP, WHITE

MAGNET: N52

2- ELECTRICAL:

RATED VOLTAGE (PER CONTACT): 5V RATED CURRENT (PER CONTACT): 2A

3- WORKING TEMPERATURE RANGE: -30~+85°C.

4- RECOMMENDED SOLDERING PROCESS ARE SELECTIVE SOLDERING OR MANUAL SOLDERING. OTHER FORMS OF SOLDERING SUCH AS WAVE SOLDER OR REFLOW SOLDER ARE NOT RECOMMENDED AND CAN POTENTIALLY CAUSE DEMAGNETIZATION OF MAGNET IN THE CONNECTOR

5- MATING WITH: 686B02C2P001B0E, 687B02C2A000J00 OR 685B0212P011B0E

## MAGNETIC SPRING LOADED CONNECTOR 1POS, FEMALE



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO.:	686B02222030B1E				UNIT: MM
DRAWN: J.L.		DATE: 8/23/2023			
CHECKED: R.S.M		DATE: 8/23/2023			
SCALE: (IN CAD 1:1)		SHEET	1	OF	: 1

DRAWING NUMBER: 686B02222030B1E ISSUE 3 PART NUMBER: 686B02222030B1E

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.

COMPLIANT