
6.60 ± 0.10  $3.60 \pm 0.05$ 中 15.80



8.60

b

D

+

5

d

Ħ

+ }

**TOLERANCE** UNLESS OTHERWISE SPECIFIED

.X ±0.15

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER **ORIGINAL** 

ADD NOTE 3 & 4

P.M. AUG. 13/2023

SPECIFICATION:

1- MATERIAL:

CONTACT: BRASS, GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING

HOUSING: PA9T, BLACK

MAGNET: N52, NICKEL 2000" MIN.

PROTECTIVE FILM: PC COLOR, BLACK

2- ELECTRICAL:

RATED VOLTAGE (PER CONTACT): 5V

RATED CURRENT (PER CONTACT): 2A


INSULATION RESISTANCE: 100MEGAOHMS MIN. DIELECTRIC WITHSTANDING VOLTAGE: 100V AT 60Hz.

CONTACT RESISTANCE: 30mOHMS MAX. BEFORE TEST AND 60mOHMS MAX.

AFTER TEST POGO PIN WORKING STROKE.

3- RECOMMENDED SOLDERING PROCESS ARE SELECTIVE SOLDERING OR MANUAL SOLDERING. OTHER FORMS OF SOLDERING SUCH AS WAVE SOLDER OR REFLOW SOLDER ARE NOT RECOMMENDED AND CAN POTENTIALLY CAUSE DEMAGNETIZATION OF MAGNET IN THE CONNECTOR

4- MATING WITH: 687G0524A50110E OR 685G0524P50110E



## MAGNETIC SPRING LOADED CONNECTOR, 5POS, FEMALE



0.15

**EDAC INC** TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

| ACAD REFERENCE NO.: 686G0 | 0524350125E     | UNIT: MM |
|---------------------------|-----------------|----------|
| DRAWN: J.L.               | DATE: 8/13/2023 | i        |
| CHECKED: R.S.M            | DATE: 8/13/2023 |          |
| SCALE: (IN CAD 1:1)       | SHEET 1 OF      | : 1      |
| DD AVAINO NII IMPED       |                 | 100115   |

**ISSUE** DRAWING NUMBER: 686G0524350125E 2 PART NUMBER: 686G0524350125E

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.

0.00

8 O

4.00

8

COMPLIANT