
Order Number 63828-1600





Application Tooling Specification

FEATURES


- A full cycle ratcheting hand tool ensures complete crimps
- Ergonomic soft grip handles for comfortable crimping
- A precision user-friendly terminal locator wire stop holds terminals in the proper crimping position
- Right- and left-handed applications
- This tool is IPC/WHMA-A-620 Class 2 compliant (see Page 2)
- This tool is RoHS compliant; however, RoHS compliance is not required

SCOPE

Products: Claspcon Socket Crimp Terminals, 24 AWG stranded wire.

Towningl	♦ Terminal	Wire Size		+	Stein Longth					
Terminal Series No.	v rerminar			IPC/WHMA-A-620 (1)		Terminal (2)		Strip Length		
Series No.	Loose Piece	Reel (3)	AWG	mm ²	mm	In.	mm	In.	mm	In.
1001 0	02-08-1102	02-08-1101	24	24 —	1.40-2.30	.055091	1.50-3.50	.059138	4.00-5.00	100 200
1881-2		02-08-5101	24							.100200
 ◆ Insulation Diameter Notes (1) Insulation diameter range for optimum IPC/WHMA-A-620 Class 2 insulation crimps. Use tool profile specified on Page 3. (2) Insulation diameter range for the terminal product design. ◆ Terminal Order No. Note										


DEFINITION OF TERMS



TERMINAL CUT-OFF SPECIFICATIONS

This hand tool operates best with loose-piece terminals. If reeled terminals are used, they must be cut from the carrier strip as specified below:

Terminal Series No.	Reeled Terminal	Cut-Off Dimension "X"				
	Order No.	mm	In.			
1001 0	02-08-1101	2 (1 0 00	142 002			
1881-2	02-08-5101	3.61±0.08	.142±.003			



1881-2 SERIES

After crimping, the crimped terminal should measure as follows:

Terminal			Crimp	Condu Height	uctor Crimp Wie	Pull Force Minimum		
Series No. AW		mm ²	mm	nm In. m		In.	N	Lb.
1881-2	24	-	1.21-1.27	.047050	1.80	.070	29.4	6.6

To achieve IPC/WHMA-A-620 Class 2 insulation crimps, use the appropriate tool profile for the insulation diameter:

Terminal Wire Size		UL Style	Insulation	Diameter	Insulation Crimp (Ref)				Tool					
Series No.	Wire Size		wire Size		(Ref)	e Range		Crimp Height		Crimp Width		Profile		е
AWG m		mm ²	(Rei)	mm	In.	mm	In.	mm	In.	Α	В	С		
					1061	1.05-1.15	.041045	2.00	.079	2.10	.083			Χ
1881-2	24	_	1007	1.40-1.50	.055059	2.30	.090	1.95	.077	Х				
			1015	2.20-2.30	.087090	2.60	.102	2.60	.102		Χ			

Crimp attribute specifications are as follows:

Terminal	Wire	Size	Bell M	louth	Bru	ısh	Bend Up	Bend Twist		Roll
Series No.	AWG	mm ²	mm	In.	mm	In.		Down		-
1881-2	24	_	0.20-0.50	.008020	0.50-1.00	.020040	3°	3°	4°	8°

Tool Qualification Notes

- 1. (Ref) means that the dimension provided is approximate because of the wide range of wires, conductor stranding, insulation diameter and insulation hardness.
- 2. An occasional conductor crimp height measurement should be performed. It must lie between the minimum and maximum crimp height specification.
- 3. Pull force should be measured with no influence from the insulation crimp. To ensure this, strip the wire long enough so the terminal insulation grips do not contact the wire insulation.

Notes

- 1. This tool should only be used for the terminals and wire gauges specified on this sheet.
- 2. Variations in tools, terminals, wire stranding and insulation types may affect crimp height.
- 3. This tool is intended for AWG conductor sizes. It may not give good insulation crimp support for insulation sizes outside of the specified range.
- 4. Molex does not repair hand tools. See warranty on page 6. The replacement parts listed are the only parts available for repair. If the handles or crimp tooling become damaged or worn, a new tool must be purchased.
- Conductor crimp height should be used as the final criterion for an acceptable crimp. Refer to Molex Quality Crimping Handbook 63800-0029 for additional information on crimping and crimp testing.
- 6. Molex does not certify crimp hand tools.

OPERATION

CAUTION: Crimp only the Molex terminals listed in the scope for this tool. Do not crimp hardened objects as damage can occur to the tool frame or crimp dies.

Open the tool by squeezing the handles together. At the end of the closing stroke, the ratchet mechanism will release the handles and the HANDLE WILL Nolex: hand tool will spring open. See Figure 1. SPRING OPEN **Crimping Terminals** 1. Select the desired terminal listed in the preceding charts. \mathfrak{D} SOUEEZE HANDLES 2. Make sure the center of the locator is in the down position. With TOGETHER the locator attached, push the locator button on the back of the hand tool to bring the locator forward through the tooling. See Figure 1 Figure 2. LOCATOR IN DOWN 3. While holding the locator button in, load the terminal into the proper POSTION nest opening in the locator based on the wire insulation diameter markings on the crimp jaws. See Figure 3. PUSH ON THE LOCATOR BUTTON Figure 2 RELEASE LOCATOR LOCATOR LOCATOR LOCATOR **PUSHED THROUGH** BUTTON TOOLING BUTTON PUSHED IN TERMINAL Figure 3 FERMINAL


4. Release the locator button, allowing the locator to return to the crimping position.

Hand Crimp Tool for Claspcon Socket Crimp Terminals

TOOLING 5. Close the tool handle until the first ratchet position engages. See PARTIALLY Figure 4. CLOSED 6. Insert the properly stripped wire through the terminal and against the wire stop. See Figure 5. PARTIALLY **CLOSE HANDLE** 7. Crimp the terminal by squeezing the tool handles until the ratchet mechanism cycle has been completed. Release the Molex handles to open the jaws. \sum WIRE STOP IS PART OF THE LOCATOR WIRE AGAINST OPEN THE WIRE STOP POSITION TERMINAL FIRST RATCHET POSITION WIRE Figure 4 TERMINAL Figure 5 **PRE-STRIPPED WIRE**

Note: The tamper-proof ratchet action will not release the tool until it has been fully closed.


- 8. Remove the crimped terminal from the terminal locator by pulling on the wire.
- 9. Visually inspect the crimped terminal for proper crimp location.
- 10. On some large O.D. wires, it may not be possible to insert the wire with the tool partially closed. Those wires should be inserted with the hand tool in the open position. Insert the wire above the terminal in the punch and against the wire stop then close the tool. See Figure 6.



Locator Replacement

See the parts list on the last page of this document for the proper locator order number. Follow the steps below to replace the locator:

- 1. Open the crimp hand tool.
- Gently squeeze on the lower area shown in Figure 7A with your thumb and index finger. The lower tabs of the locator should disengage from the hand tool.
- 3. Lift and pull away from the hand tool. The top locator hooks should slip out of the top slots easily. See Figure 7A.
- 4. To reinstall the new locator, make sure the hand tool is in the open position.
- 5. Press the center of the locator down as far as it will go as shown in Figure 7B.
- Holding onto the lower part of the locator with your thumb and index finger, insert the locator's top hooks into the hand tool's top slots.
- 7. Rotate the locator down, and press the lower tabs into the two bottom slots of the hand



Hand Crimp Tool for Claspcon Socket Crimp Terminals

tool. To secure the locator into place, the lower tabs must snap into place on the hand tool frame.

Right- or Left-Handed Operation

This hand tool has an added feature that can be converted from a right-handed application to a left-handed application. It is necessary to reverse the tooling if using the left-handed application along with the locator. Follow the steps below:

- 1. The locator must be removed before reversing the tooling.
- 2. Remove the M3 BHCS, which is holding the upper tooling.
- 3. Flip the upper tooling to the opposite side, and replace the M3 BHCS. Make sure the small markings on the front and back of the hand tool frame match up and are on the outside of the hand tool frame. See Figures 8 and 9.
- Do the same thing with the lower tooling, and tighten the M3 screws. Be sure the small markings line up.
- 5. Reinstall the locator by following the instructions in the locator replacement section.


63811-XXXX

(``

ΛΛΓ

0

FRONT



MAINTENANCE

It is recommended that each operator of the tool be made aware of and responsible for the following maintenance steps:

MATCH

Figure 9


C

BACK

1. Remove dust, moisture and other contaminants with a clean brush or a soft, lint-free cloth.

(D)

- 2. Do not use any abrasive materials that could damage the tool.
- 3. Make certain all pins, pivot points and bearing surfaces are protected with a thin coat of high-quality machine oil. Do not oil excessively. The tool was engineered for durability, but like any other equipment, it needs cleaning and lubrication for a maximum service life of trouble-free crimping. Light oil such as 30 weight automotive oil used at the oil points every 5,000 crimps or 3 months will significantly enhance the tool life.
- 4. Wipe excess oil from hand tool, particularly from the crimping area. Oil transferred from the crimping area onto certain terminations may affect the electrical characteristics of an application.
- 5. When the tool is not in use, keep the handles closed to prevent objects from becoming lodged in the crimping dies, and store the tool in a clean, dry area.



Miscrimps or Jams


Should this tool ever become stuck or jammed in a partially closed position, **Do Not** force the handles open or closed. The tool will open easily by pressing up on the ratchet release lever in the movable handle. See Figure 11.

How to Adjust Tool Preload (See Figure 12)

RATCHET RELEASE LEVER Figure 11

This hand tool is factory preset to 25-45 pounds handle preload. It may be necessary over the life of the tool to adjust tool handle preload force. Listed below are the steps required to adjust the crimping force of the hand tool to obtain proper crimp conditions:

- Hold the hand tool in the palm of your hand as shown in Figure 12. Using your index finger, squeeze the link toward the top of the hand tool frame. This will release the preload adjustment wheel.
- Rotate the setting wheel counterclockwise (CCW) to increase handle force. The numbers will display higher. To decrease handle force, rotate the setting wheel clockwise (CW).
- 3. Release the link to lock the setting wheel in place.
- Check the crimp specifications or conduct a pull test after tool handle preload force is adjusted.



Warranty

This tool is for electrical terminal crimping purposes only. This tool is made of the best quality materials. All vital components are long-life tested. All tools are warranted to be free of manufacturing defects for a period of 30 days. Should such a defect occur, Molex will repair or exchange the tool free of charge. This repair or exchange will not be applicable to altered, misused or damaged tools. This tool is designed for hand use only. Any clamping, fixturing or use of handle extensions voids this warranty.


CAUTION: Molex crimp specifications are valid only when used with Molex terminals and tooling.

CAUTIONS:

- 1. Manually powered hand tools are intended for low-volume use or field repair. This tool is NOT intended for production use. Repetitive use of this tool should be avoided.
- 2. Insulated rubber handles are not protection against electrical shock.
- 3. Wear eye protection at all times.
- 4. Use only the Molex terminals specified for crimping with this tool.

PARTS LIST

Item Number	Order Number	Description	Quantity
REF	63828-1600	Hand Crimp Tool	Figure 13
1	63828-1675	Locator Assembly	1
2	63810-0104	Spring, Return	1
3	63810-0105	Spring, Ratchet	1



Application Tooling Support

Phone: (402) 458-TOOL (8665) E-Mail: applicationtooling@molex.com Website: www.molex.com/applicationtooling

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

Doc. No: ATS-638281600 Revision: A Release Date: 10-30-19 Revision Date: 10-30-19 **UNCONTROLLED COPY**