



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-3 @20°C	0.350 ohms max.
D.C. RESISTANCE	6-4 @20°C	0.060 ohms max.
INDUCTANCE	1-3 10kHz, 100mVAC, Ls	700.00uH min.
LEAKAGE INDUCTANCE	1-3 tie(6+5+4), 1MHz, 100mVAC, Ls	1.8uH typ., 2.8uH max.
INTERWINDING CAPACITANCE	1-6 100kHz, 10mVAC, Cs	11.0pF typ., 16.0pF max.
DIELECTRIC	1-6 2500VAC, 1 second	2500VAC, 1 minute
TURNS RATIO	(1-3):(6-4)	5.33:1

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

CURRENT RATING: 1A on secondary side.

VOLTAGE-TIME: 25Vus for Unipolar operation
50Vus for Bipolar operation

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-1281 www.we-online.com/midcom
6A	6/23	SEE REVISION SHEET FOR REVISION LEVEL



Tolerances unless otherwise specified:
Angles: ±1°
Fractions: ±1/64
Decimals: ±.005 [.13]
Footprint: ±.005 [.13]

This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE TRANSFORMER	compliant RoHS
eiSos p/n: 750320325	

PART NO. 750320325
SPECIFICATION SHEET 1 OF 1