

Multilayer Ceramic Chip Capacitor

Part Number: 1806J0500224MXTE07

Description: 1806 50Vdc 220nF ±20% X7R (2R1)

A range of ceramic MLCC feedthrough 'C' filters with enhanced current carrying capabilities. Internal electrodes conduct signals through the MLCC body, with the capacitance formed to ground pads on the side of the chip, providing low inductance and high performance. Available with a variety of termination options including FlexiCapTM (on X7R), the world's first commercially available flexible termination.



Mechanical Specification			
Size Code	1806		
Length (L1) in mm (")	4.5 ± 0.35 (0.177 ± 0.014)		
Width (W) in mm (")	1.6 ± 0.20 (0.063 ± 0.008)		
Thickness (T) in mm (")	1.1 ± 0.2 (0.043 ± 0.008)		
Termination Bands (B2) in mm (")	0.50 ± 0.25 (0.02 ± 0.01)		
Center (Ground) Band (B1) in mm (")	1.4 ± 0.30 (0.055 ± 0.012)		
Termination Material	Nickel Barrier, Sn Plated Solder (RoHS compliant)		
Solderability	IEC-60068-2-58		
Packaging	7" Reel Horizontal Orientation, 2500 per reel		

General Electrical Specification				
Rated Voltage		50Vdc		
Rated DC Current		2A		
DC Resistance		0.06Ω		
Nominal Capacitance Value		220nF		
Capacitance Tolerance		±20%		
Tangent of Loss Angle (Tan δ)		≤0.025		
Capacitance and Tan δ Test Conditions		1.0Vrms @ 1kHz		
Voltage Proof (Voltage applied for 5 secs max. @ 50mA max. charge current)		125Vdc		
Min Insulation Resistance (IR)		4.55GOhm @ 50Vd	c	
Dielectric Classification		X7R (2R1)		
Rated Temperature Range		-55°C / +125°C		
Maximum Capacitance Change over Temperature Range		No DC Voltage ±15% Rated DC Voltage -		
Climatic Category (IEC)		55/125/56		
Ageing Characteristic		<2% per decade (no	ominal capacitance is 1000 hour value)	
Knowles Precision Devices - Sales	This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at http://www.knowlescapacitors.com or by contacting us.			
Europe: KPD-Europe-sales@knowles.com				
Asia: KPD-Asia-sales@knowles.com	© The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consent of Knowles and any customer mentioned within this specification.			
USA: KPD-NA-sales@knowles.com			Deter Tuesday, Japuary 16, 2024	
www.knowlescapacitors.com			Date. Tuesday, January 10, 2024	



Multilayer Ceramic Chip Capacitor

Part Number: 1806J0500224N	IXTE07	Description:	1806 50Vdc 220nF ±20% X7R (2R1)		
Environmental					
RoHS Compliant to 2011/65/EC as amend	ed by 2015/863/EU	Compliant			
REACH Compliant		235 compliant			
California Proposition 65		No exposure risk			
	Board	Layout			
Knowles' conventional 3-terminal chip cap mounted using the pad design supplied. It has been developed in conjunction with o the years and has been shown to yield s results. It incorporates factors that have reduce mechanical stress, such as reducin less than the chip width, but the position board should also be considered. Note that for optimum noise rejection the g be placed on the circuit board ground plan the ground plane by the shortest and wides	bacitors should be our customers over uccesful soldering e been shown to g the pad width to of the chip on the round pads should e, or connected to t route possible.		1806 A 1.20mm 0.047" B 1.40mm 0.055" C 0.80mm 0.031" D 1.40mm 0.055" E 1.00mm 0.039" F 0.70mm 0.028"		
	Pacl	caging			
Tape packaging information for tape-and-re Tape and reel packing of surface mounting for automatic placement are in accordance	eel parts: chip capacitors with IEC60286-3.		Product identifying label Plastic carrier tape Top tape 8 or 12mm 178mm (7") or nominal 330mm (13") dia. reel		
Soldering					
Reflow solder in accordance with IPC-A-610. Recommended reflow profile as laid down in IPC/JEDEC J- STD-020. Wave soldering is also possible, but care must be taken for case sizes 1210 and larger and component thickness >1.0mm. Trials are encouraged. T_{L}					
Hand soldering is not recommended and can lead to Time					
Application notes with mounting and handling guidance are available on request.					
Compex DLI	Johanson MFG	Novacap	Syfer Voltronics		
Knowles Precision Devices - Sales	This datasheet is for a s for this part may differ a	standard item and is confi nd is available at http://wv	rmed valid on the date generated, the latest published data ww.knowlescapacitors.com or by contacting us.		
Asia: KPD-Asia-sales@knowles.com	© The information cont	ained on this drawing is	Data is correct to the best of our knowledge, errors and omissions excented.		
USA: KPD-NA-sales@knowles.com www.knowlescapacitors.com	confidential and may not b any form or disclosed to a t of Knowles and any cust specification.	e copied in whole or part in hird party without the consent comer mentioned within this	Date: Tuesday, January 16, 2024 20240116 172434715UTC		