

Tel: 1-800-722-8197 1-631-595-2217 Fax: 1-631-667-5484 EMAIL: sales@challelec.com WEB: www.challengeelectronics.com ISO 9001/14001:2015 Certified

INDICATORS • SPEAKERS • SOUND TRANSDUCERS • ENCLOSURES • MICROPHONES • BATTERY ACCESSORIES

CS14-00P100-04-1

Rev. 1-2023 RoHS3 & REACH Planar Magnetic Speakers



Operating Characteristics ELECTRICAL Rated Power 0.005 W 123.0 Short Term Max Power 115.0 0.01 W 110.0 1Up.U $30 \Omega \pm 15 \%$ Impedance 100. 1000 Hz; 0.001 W 95.0 90.0 85. U ACOUSTIC: IEC-318 Artificial Ear 80. U 20u Pal 75.0 1000 Hz ± 15 % f٥ 70.0 0.001 W 85.0 Freq. Range 20 to 20000 Hz 6D. (5s.I 107 ± 2 dB 53.0 Rated SPL 1000 Hz; 45.0 AVG; 0.001 W; 40.0 op. o Distortion Max 1 % 30. (1000 Hz; 0.001 W 25 F 20.00


Physical Characteristics


MATERIALS


Housing	Stainless Steel
Cone	PET+PU
Magnet	NdFeB
Solder Pad	Tin Plated Copper

TEMPERATURE RANGES

Operating	-25 to +60 °C
Storage	-25 to +60 °C
Weight	2 g







General tolerance = ±0.2 mm and all measurements in mm unless otherwise noted.

Revision	Description	Ву	Date
0-2023	Original Specification.	SK	2023-08-17
1-2023	Updated Mechanical Drawing: overall diameter changed from 14.5 to 14.55mm, overall height changed from 4.9 to SK 4.88mm, and rear cover diameter changed from 8.5 to 8mm.		2023-11-10

Warranty: For a period of one (1) year from date of shipping under normal operations conditions. This warranty does not apply to products damaged through misuse, abuse, improper installation, alteration, rework, or attempt to repair.

The information contained herein is believed to be correct, but no guarantee or warranty, express or implied, with respect to accuracy, completeness or results is extended and no liability is assumed. Challenge Electronics reserves the right to make changes in any specification, data or material contained herein.