

LPS250 Series

250 Watts

Data Sheet

Total Power: 250 Watts **Input Voltage:** 85 - 264 Vac 120 - 300 Vdc

of Outputs: Single

SPECIAL FEATURES

- Active power factor correction
- IEC EN6100-3-2 compliance
- Remote sense & remote inhibit
- Power fail
- Single wire current sharing
- Built-in EMI filter
- 2:1 Wide range output voltage adjust
- 2 Supervisory outputs 5 V and 12 V
- Overvoltage protection
- Overload protection
- Thermal overload protection
- DC power good
- 120 kHz switching frequency
- RoHS compliant
- Cover -C
- Optional top with fan cover -CF
- Optional end fan cover -CEF

SAFETY

VDE 62368UL 62368CSA 62368NEMKO 62368

CB Certificate and report 2186

CE Mark (LVD)



Electrical Specifications					
Input					
Input range	85 - 264 Vac; 120 - 300 Vdc				
Frequency	47 - 440 Hz				
Inrush current	20 A max, cold start @ 25 °C				
Efficiency	75% typical at full load				
EMI filter	FCC Class B conducted and radiated CISPR 22 Class B conducted and radiated EN55022 Class B conducted and radiated VDE 0878 PT3 Class B conducted and radiated				
Safety ground leakage current	< 0.5 mA @ 50/60 Hz, 264 Vac input				
Output					
Maximum power	With cover: 250 W with 30 CFM forced air. (-C) (-CF) (CEF)				
Supervisory output	5 V @ 100 mA regulated; 12 V @ 500 mA				
Adjustment range	2:1 wide ratio				
Hold-up time	20 ms @ 250 W load, 115 VAC nominal line				
Overload protection	Short circuit protection on all outputs. Case overload protected @ 10 - 145% above peak rating				
Overvoltage protection	5 V output: 5.7 to 6.7 Vdc. Other models 10% to 25% above nominal output				
Logical Control					
Power failure	TTL Logic signal goes high 50 - 150 msec after 5 V output. It goes low at least 4 ms before loss of regulation				
Remote on/off	Requires an external contact (N.O or N.C) to inhibit outputs				
DC - OK	TTL logic goes high 50 - 150 msec after the output. It goes low when there is loss of regulation.				
Remote sense	Compensates for 0.5 V lead drop minimum, will operate without remote sense connected. Reverse connection protected				



Environmental Specifications				
Operating temperature	0° to 50 °C ambient; derate each output at 2.5% per degree from 50° to 70 °C			
Storage temperature	-40 °C to +85 °C			
Temperature coefficient	± 0.4% per °C			
Electromagnetic susceptibility	Designed to meet IEC 801, -2, -3, -4, -5, -6, Level 3			
Humidity	Operating; non-condensing 5% to 95%			
Vibration	Three orthogonal axes, sweep at 1 oct/min, 5 min. dwell at four major resonances 0.7 G peak 5 Hz to 500 Hz, operational			
MTBF demonstrated	> 550,000 hours at full load and 25 °C ambient conditions			


Ordering Information						
Model Number	Output Voltage	Minimum Load	Maximum Load with 30CFM Forced Air	Peak Load ¹	Regulation ²	Ripple P/P (PARD) ³
LPS252-C	5 V (3 - 6 V)	1.50 A	50 A	60 A	±2%	50 mV
LPS253-C	12 V (6 - 12 V)	0.63 A	21 A	25 A	±2%	120 mV
LPS254-C	15 (12 - 24 V)	0.50 A	16.7 A	20 A	±2%	150 mV
LPS255-C	24 V (24 - 48 V)	0.32 A	10.4 A	12.5 A	±2%	240 mV

- 1. Peak current lasting < 30 seconds with a maximum 10% duty cycle.
- 2. At 25 °C including initial tolerance, line voltage, load currents and output voltages adjusted to factory settings.
- 3. Peak-to-peak with 20 MHz bandwidth and 10 µF in parallel with a 0.1 µF capacitor at rated line voltage and load ranges.
- 4. If optional CF or CEF fans are not used, 30CFM forced air cooling needs to be provided and is required through the length of the power supply. Not convection rated.
- 5. Output voltage adjustment requires a minimum load.
- 6. Remote inhibit resets OVP latch
- 7. This product is a Component Power Supply and is only for inclusion by professional installers within other equipment and must not be operated as a standalone product. EMC compliance to appropriate standards must be verified at the system level. This product is for sale to OEMs and System Integrators, including through Distribution Channels. It is not intended for sale to End Users.

Note: -CF suffix added to the model number indicates cover with top fan. -CEF suffix added to the model number indicates cover with dual end mounted fan cover and AC inlet.



Mechanical Drawing



In the the

Pin Assignments				
Connector				
SK1	PIN 1	Neutral		
	PIN 2	Line		
	PIN 3	Ground		
SK3	PIN 1	+ Remote sense		
	PIN 2	- Remote sense		
	PIN 3	Remote inhibit (N.O.)		
	PIN 4	Remote inhibit (N.C.)		
	PIN 5	Common		
	PIN 6	Current sharing		
	PIN 7	Power fail		
	PIN 8	DC Power Good		
SK4	PIN 1	+ Fan's power source (12 V @ 500 mA)		
	PIN 2	- Fan's power source (12 V @ 500 mA)		
SK5	PIN 1	+ Supervisory output supply (5 V @ 100 mA)		
	PIN 2	- Supervisory output supply (5 V @ 100 mA)		
SK7	PIN 1	+ Fan's power source (12 V @ 500 mA)		
	PIN 2	- Fan's power source (12 V @ 500 mA)		

Mating Connectors		
SK3	Molex 22-01-1084 PINS:08-70-0057	
SK4	Molex 22-01-3027 PINS: 08-50-0114	
SK5	Molex 22-01-3027 PINS: 08-50-0114	
SK7	Molex 22-01-3027 PINS: 08-50-0114	
Artesyn Embedded Power Connector Kit #70-841-005, includes all of the above		

- 1. Specifications subject to change without notice.
- 2. All dimensions in inches (mm), tolerance is ± 0.02 "(± 0.5 mm)
- 3. Specifications are at factory settings.
- 4. To enable normally closed remote inhibit, cut jumper J1.
- 5. Mounting maximum insertion depth is 0.12".
- 6. Warranty: 2 year
- 7. Weight: 2.6 lb / 1.19 kg

WORLDWIDE OFFICES

Americas

2900 South Diablo Way Suite B100 Tempe, AZ 85282, USA +1 888 412 7832

Europe (UK)

Ground Floor Offices, Barberry House 4 Harbour Buildings, Waterfront West Brierley Hill, West Midlands DY5 1LN, UK +44 (0) 1384 842 211

Asia (HK)

14/F, Lu Plaza 2 Wing Yip Street Kwun Tong, Kowloon Hong Kong +852 2176 3333



www.artesyn.com

For more information: www.artesyn.com
For support: productsupport.ep@artesyn.com

Artesyn Embedded Technologies, Artesyn Embedded Power, Artesyn, and all Artesyn related logos are trademarks and service marks of Artesyn Embedded Technologies, Inc. All other names and logos referred to are trade names, trademarks, or registered trademarks of their respective owners. Specifications are subject to change without notice. © 2020 Artesyn Embedded Technologies, Inc. All rights reserved. For full legal terms and conditions, please visit www.artesyn.com/legal.