

**Industrial Ethernet
IE-C5DD4UG0100A20A20-E**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Assembled IE cables, PROFINET, Cat. 5, PUR, green, drag-chain compatible, RJ45

General ordering data

Type	IE-C5DD4UG0100A20A20-E
Order No.	1173030100
Version	Dragline cable, PROFINET, RJ45 IP 20, RJ45 IP 20, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PUR, 10 m
GTIN (EAN)	4032248985616
Qty.	1 pc(s).

**Industrial Ethernet
IE-C5DD4UG0100A20A20-E**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Length	10 m	Length (inches)	0.394 inch
Net weight	661 g	Insulation cross-section	1.5 mm

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	70 °C	Storage temperature, min.	-50 °C
Operating temperature	-40 °C...70 °C	Storage temperature	-50 °C...70 °C
Installation temperature	-20 °C...60 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Electrical properties

Insulation strength	500,000 Ω
---------------------	-----------

Standards

Connector standard	IEC 60603-7-51	Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)
Standard, wire material	DIN EN 13602 Cu-ETP-A	Standard, shielding material	DIN EN 13602 Cu-ETP-A..B
Certificate no. (cULus)	E316369		

Cable structure

Wire material	Stranded tin-plated copper wire	Standard designations	2YH(ST)C11Y 2x2x0,75/1,5-100 LI VZN GN FRNC
Strands	7	Cross-section	4*AWG 22/7 - 0.36 mm ²
Insulation	PE	Insulation cross-section	1.5 mm
Wire core insulation thickness	0.38 mm	No. of wires	4
Arrangement of wire cores	Star-quad	Colour sequence or wires - wire pairs	white, yellow, blue, orange
Diameter of inner sheathing	3.9 mm	Filler	As central element
Shielding	SF/UTP	Complete shielding	Aluminium foil, Shielding braid made from copper wiring
Shielding braid thickness	0.13 mm	Overlap of shielding braid	85 %
Material sheath	PUR	Sheath diameter, min.	6.3 mm
Sheath diameter, max.	6.7 mm	Sheathing material thickness	0.9 mm
Sheathing colour	green (RAL 6018)		

Electrical properties of cable

Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)	Operating voltage (UL rating)	600 V undefined
Test voltage: wire-wire-shield	2000 V _{eff} , 50 Hz, 1 min	Characteristic impedance	100 ± 15 Ω at 1-100 MHz
Loop resistance	120 Ω/km	Deviation	40 ns/100m
Resistance differential	3 %	Transfer impedance	20 mΩ/m at 10 MHz
Insulation strength	500,000 Ω	Capacity at 1 kHz	52 nF/km
Signal propagation time	5.3 ns/m	Speed	180 m/min

Creation date March 7, 2019 10:41:52 AM CET

Industrial Ethernet
IE-C5DD4UG0100A20A20-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Mechanical and material properties of cable**

Bending cycles	3 Mio	Min. bending radius, once only	5 x cable diameter
Min. bending radius, repetitive	7.5 x cable diameter	Pulling force	≤ 150 N
Speed	180 m/min	Acceleration	4 m/s ²
Abrasion resistance	very good	Resistance to spread of flame	in accordance with IEC 60332-1
Resistance to oils	in accordance with IEC 60811-2-1	UV-resistant	Yes
Silicone-free	Yes	Halogen	halogen-free, according to IEC 60754-2
Fire propagation	No		

plug

Connector left	RJ45 IP 20	Connector right	RJ45 IP 20
----------------	------------	-----------------	------------

Classifications

ETIM 6.0	EC002599	eClass 6.2	27-06-03-90
eClass 7.1	27-06-91-90	eClass 8.1	27-06-91-90
eClass 9.0	27-06-03-08	eClass 9.1	27-06-03-08

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 9 IETH 15/16 EN FL FIELDWIRING EN PI PROFINET CABLING EN
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN

Industrial Ethernet
IE-C5DD4UG0100A20A20-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Wiring

RJ45		RJ45
1	yellow	1
2	orange	2
3	white	3
6	blue	6

Industrial Ethernet
IE-C5DD4UG0100A20A20-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Accessories**Blank**

TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are five different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the SMark laser printer, PrintJet ADVANCED, plotter, MC-Mobilo or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
TM-I 12 MC	1718411044	TM-I, Insert markers, 12 x 4	4008190348977	320 pc(s).
NEWS		mm, white		

Industrial Ethernet
IE-C5DD4UG0100A20A20-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Accessories**Blank**

TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are five different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the SMark laser printer, PrintJet ADVANCED, plotter, MC-Mobilo or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
TM-I 18 MC	1718431044	TM-I, Insert markers, 18 x 4	4008190349011	320 pc(s).
NEWS		mm, white		