

**Mains Power Cord, UL Listed, IEC
60320 C14 to C13, 1 m, 3.3ft, 13A, 250
VAC, Black**

**RoHS
Compliant**

Stock No.: PE03902US-SJT-13

FEATURES

- C14 TO C13
- SJT
- 16 AWG




Product Description

The Universal Power Cords are a perfect replacement for your lost, damaged, or inadequate power cord. They are designed to work with most PCs, monitors, scanners, printers, and other devices that use the 3-pin C13 connector. This cable features a fully molded design that provides maximum durability and long-life.

General Specifications

| Attribute | Value |
|------------------------|----------------------|
| Connector to Connector | IEC 60320 C14 to C13 |
| Connector Type A | IEC 60320 C14 |
| Connector Type B | IEC 60320 C13 |
| Cable Length | 1m |
| Current Rating | 13A |
| Jacket Color | Black |

Product Drawing



| Plug Component | | | Plug Component (Dimension) | | |
|----------------|--|-----|----------------------------|-------|------------------|
| Colour | Component | Qty | Strip | ROJ | Colour |
| 35P (Black) | (IEC 60320, C14, 13A 250V) | 1 | 6 +1/-0 | 20 ±2 | Brown (L) |
| Nickel-plated | 2.0 × 4.0 (GEM 98672-1) (Computer Solid Blades, #16-#18) | 3 | 6 +1/-0 | 20 ±2 | Blue (N) |
| Black | (GS-009) (Computer 2 × 4 Serial Housing) | 1 | 6 +1/-0 | 20 ±2 | Green-Yellow (E) |

| Connector Component | | | Free End Terminal Style (Dimensions) | | |
|--|------|-----------------|--------------------------------------|---------|------------------|
| (Instruction) | Qty. | Colour | ROJ | Strip | Colour |
| (IEC 60320, C13, 13A 250V) | 1 | 35P (Black) | 16±1 | 5 +1/-0 | Brown (L) |
| 2.0 × 4.0 GEM 98740BS-0 (#16-18) (Receptacle Terminal) | 3 | (Brass-Natural) | 16±1 | 5 +1/-0 | Blue (N) |
| GA005-5 (2.0 × 4.0 Serial Housing) | 1 | (Off-White) | 16±1 | 5 +1/-0 | Green-Yellow (E) |

Dimensions: Millimeters (Inches)

Part Number Table

| Part Number | Description |
|------------------|--|
| PE03902US-SJT-13 | Mains Power Cord, UL Listed, IEC 60320 C14 to C13, 1 m, 3.3ft, 13A, 250 VAC, Black |

Important Notice: This data sheet and its contents (the "Information") belong to the members of the EASE group of companies (the "Group") or are licensed to it. No license is granted for the use of it other than for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate, but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. EASE is the registered trademark of Ease Electronics Co., Limited 2019.