DataSheet No.: E13010 Version: V0

Date: 2023/04/28



MMFR

Precision Metal Film Molded Resistor

Resistance $10\Omega-1M\Omega$

Tolerance ±0.05%

TCR ±5ppm/°C

Load Life ±0.05%

Applications

Precision Instrumentation

Better Solution for Sustainable High End Manufacturing

Unit: mm



Precision Metal Film Molded Resistor Tight Tolerance, Low TCR, High Load Life Stability



Introduction

MMFR series uses 96% alumina ceramic cores, combined with precision metal film deposition technology, to achieve the target resistance through laser trimming. The lowest TCR of MMFR series is $\pm 5 \text{ppm/}^{\circ}\text{C}$. Load life stability is significantly improved compared to general metal film resistor. At $+70^{\circ}\text{C}$ ambient temperature, the maximum resistance change after loading the rated power for 1000 hours is $\pm 0.05\%$, with strong moisture resistance. The pin structure is conducive to reducing the impact of PCB stress on resistor. Highly suitable for electronic circuits with high requirements of TCR and stability.





Electrical Parameters

Size	Rated Power (+70°C)	Max. Operating Voltage	Max. Overload Voltage	Operating Temperature	E-Series Value	TCR ppm/℃	$\begin{array}{c} \textbf{Resistance} \\ \Omega \end{array}$	Tolerance %
MMFR2568	0.25W	250V	500V	-50°C∼+125°C	E24, E96	±5	10≤R≤1M	±0.05, ±0.1, ±0.5, ±1.0
MMFR3710	0.5W	300V	600V	-50℃~+125℃	E24, E96	±5	10≤R≤1M	±0.05, ±0.1, ±0.5, ±1.0
MMFR5215	0.75W	350V	700V	-50℃~+125℃	E24, E96	±5	10≤R≤1M	±0.05, ±0.1, ±0.5, ±1.0
MMFR6518	1.0W	400V	800V	-50℃~+125℃	E24, E96	±5	10≤R≤1M	±0.05, ±0.1, ±0.5, ±1.0

Dimensions & Packaging




Size	L	D	d	Packaging	Quantity Per Bulk
2568	6.8±0.4	2.5±0.4	0.6±0.05	Bulk	200pcs
3710	10.0±0.4	3.7±0.4	0.6±0.05	Bulk	100pcs
5215	14.8±0.4	5.2±0.4	0.6±0.05	Bulk	100pcs
6518	18.3±0.4	6.5±0.4	0.8±0.05	Bulk	100pcs



Part Number Information

Example: MMFR3710B100RV9 (MMFR 3710 $\pm 0.1\%$ 100 Ω ± 5 ppm/°C Standard)




For more options of resistance, tolerance and TCR, please contact us.

Performance

Test	Test Method	Standards	Max.
Load Life	$70\pm2^{\circ}$ C, 1000h, RCWV or maximum operating voltage (the lower one)	IEC 60115-1 4.25	±0.05%+0.05Ω
TCR	+85°C, +25°C Ref.	IEC 60115-1 4.8	Within the nominal value range
Resistance to Solder Heat	+260±3°C, 10±1s, immersed 3±0.5mm of the body	IEC 60115-1 4.18	±0.05%+0.05Ω
Short-Time Overload	10x RCWV or 2x maximum operating voltage (the lower one) for 5s	IEC60115-1 4.13	±0.02% No visible damage
Resistance to Solvent	Immerse in IPA for 5 min with ultrasonic	IEC 60115-1 4.30	Clear marking No visible damage
Solderability	235±5°C, 3±0.5s	IEC 60115-1 4.17	95% coverage
Moisture Resistance	$40\pm2^{\circ}$ C, 90-95% RH for 56 days, 0.1xRCWV or the maximum operating voltage (the lower one)	IEC 60115-1, 4.24	±0.05%+0.05Ω
Dielectric Withstanding Voltage	Apply a AC voltage with an effective maximum overload voltage between the electrode and the substrate at a speed of approximately 100V/s, for 60s	IEC 60115-1 4.7	No breakdown or flashover
Insulation Resistance	Apply a DC voltage of 100V between the electrode and the substrate for 60s and measure the insulation resistance	IEC 600115-1 4.6	10000MΩ, minimum



Derating Curve



Marking

The first line: The first four digits represent brand and the second four digits represent resistance;
The second line: The first digit represents tolerance, the second and third digits represent TCR, and the last four digits represent date code.

Illustration



RESI (Brand) 、 10R0 (Resistance 10 Ω) 、 B (Tolerance ±0.1%) 、 T5 (TCR ±5ppm/°C) 2320 (Date Code. Week 20 of 2023)





Popular Part Numbers

Part Number	Size	Tolerance	Resistance	TCR	Power	Max. Operating Voltage
MMFR2568B10R0V9	2568	±0.1%	10Ω	±5ppm/°C	0.25W	250V
MMFR2568B20R0V9	2568	±0.1%	20Ω	±5ppm/°C	0.25W	250V
MMFR2568B50R0V9	2568	±0.1%	50Ω	±5ppm/°C	0.25W	250V
MMFR2568B100RV9	2568	±0.1%	100Ω	±5ppm/°C	0.25W	250V
MMFR2568B200RV9	2568	±0.1%	200Ω	±5ppm/°C	0.25W	250V
MMFR2568B250RV9	2568	±0.1%	250Ω	±5ppm/°C	0.25W	250V
MMFR2568B500RV9	2568	±0.1%	500Ω	±5ppm/°C	0.25W	250V
MMFR2568B1K00V9	2568	±0.1%	1ΚΩ	±5ppm/°C	0.25W	250V
MMFR2568B2K00V9	2568	±0.1%	2ΚΩ	±5ppm/°C	0.25W	250V
MMFR2568B5K00V9	2568	±0.1%	5ΚΩ	±5ppm/°C	0.25W	250V
MMFR2568B10K0V9	2568	±0.1%	10ΚΩ	±5ppm/°C	0.25W	250V
MMFR2568B20K0V9	2568	±0.1%	20ΚΩ	±5ppm/°C	0.25W	250V
MMFR2568B50K0V9	2568	±0.1%	50ΚΩ	±5ppm/°C	0.25W	250V
MMFR2568B100KV9	2568	±0.1%	100ΚΩ	±5ppm/°C	0.25W	250V
MMFR2568B200KV9	2568	±0.1%	200ΚΩ	±5ppm/°C	0.25W	250V
MMFR2568B500KV9	2568	±0.1%	500ΚΩ	±5ppm/°C	0.25W	250V
MMFR2568B1M00V9	2568	±0.1%	1ΜΩ	±5ppm/°C	0.25W	250V
MMFR3710B10R0V9	3710	±0.1%	10Ω	±5ppm/°C	0.5W	300V
MMFR3710B20R0V9	3710	±0.1%	20Ω	±5ppm/°C	0.5W	300V
MMFR3710B50R0V9	3710	±0.1%	50Ω	±5ppm/°C	0.5W	300V
MMFR3710B100RV9	3710	±0.1%	100Ω	±5ppm/°C	0.5W	300V
MMFR3710B200RV9	3710	±0.1%	200Ω	±5ppm/°C	0.5W	300V
MMFR3710B250RV9	3710	±0.1%	250Ω	±5ppm/°C	0.5W	300V
MMFR3710B500RV9	3710	±0.1%	500Ω	±5ppm/°C	0.5W	300V
MMFR3710B1K00V9	3710	±0.1%	1ΚΩ	±5ppm/°C	0.5W	300V
MMFR3710B2K00V9	3710	±0.1%	2ΚΩ	±5ppm/°C	0.5W	300V
MMFR3710B5K00V9	3710	±0.1%	5ΚΩ	±5ppm/°C	0.5W	300V
MMFR3710B10K0V9	3710	±0.1%	10ΚΩ	±5ppm/°C	0.5W	300V
MMFR3710B20K0V9	3710	±0.1%	20ΚΩ	±5ppm/°C	0.5W	300V
MMFR3710B50K0V9	3710	±0.1%	50ΚΩ	±5ppm/°C	0.5W	300V
MMFR3710B100KV9	3710	±0.1%	100ΚΩ	±5ppm/°C	0.5W	300V
MMFR3710B200KV9	3710	±0.1%	200ΚΩ	±5ppm/°C	0.5W	300V
MMFR3710B500KV9	3710	±0.1%	500ΚΩ	±5ppm/°C	0.5W	300V
MMFR3710B1M00V9	3710	±0.1%	1ΜΩ	±5ppm/°C	0.5W	300V
MMFR5215B10R0V9	5215	±0.1%	10Ω	±5ppm/°C	0.75W	350V
MMFR5215B20R0V9	5215	±0.1%	20Ω	±5ppm/°C	0.75W	350V
MMFR5215B50R0V9	5215	±0.1%	50Ω	±5ppm/°C	0.75W	350V
MMFR5215B100RV9	5215	±0.1%	100Ω	±5ppm/°C	0.75W	350V
MMFR5215B200RV9	5215	±0.1%	200Ω	±5ppm/°C	0.75W	350V
MMFR5215B250RV9	5215	±0.1%	250Ω	±5ppm/°C	0.75W	350V
MMFR5215B500RV9	5215	±0.1%	500Ω	±5ppm/°C	0.75W	350V
MMFR5215B1K00V9	5215	±0.1%	1ΚΩ	±5ppm/°C	0.75W	350V
MMFR5215B2K00V9	5215	±0.1%	2ΚΩ	±5ppm/°C	0.75W	350V 350V
MMFR5215B5K00V9	5215	±0.1%	5ΚΩ	±5ppm/°C	0.75W	350V 350V
				±5ppm/°C		
MMFR5215B10K0V9	5215	±0.1%	10ΚΩ	±5ppm/°C	0.75W	350V
MMFR5215B20K0V9	5215	±0.1%	20ΚΩ	±5ppm/°C	0.75W	350V
MMFR5215B50K0V9	5215	±0.1%	50ΚΩ	±5ppm/°C	0.75W	350V
MMFR5215B100KV9	5215	±0.1%	100ΚΩ		0.75W	350V
MMFR5215B200KV9	5215	±0.1%	200ΚΩ	±5ppm/°C	0.75W	350V



Popular Part Numbers

Part Number	Size	Tolerance	Resistance	TCR	Power	Max. Operating Voltage
MMFR5215B500KV9	5215	±0.1%	500ΚΩ	±5ppm/°C	0.75W	350V
MMFR5215B1M00V9	5215	±0.1%	1ΜΩ	±5ppm/°C	0.75W	350V
MMFR6518B10R0V9	6518	±0.1%	10Ω	±5ppm/°C	1.0W	400V
MMFR6518B20R0V9	6518	±0.1%	20Ω	±5ppm/°C	1.0W	400V
MMFR6518B50R0V9	6518	±0.1%	50Ω	±5ppm/°C	1.0W	400V
MMFR6518B100RV9	6518	±0.1%	100Ω	±5ppm/°C	1.0W	400V
MMFR6518B200RV9	6518	±0.1%	200Ω	±5ppm/°C	1.0W	400V
MMFR6518B250RV9	6518	±0.1%	250Ω	±5ppm/°C	1.0W	400V
MMFR6518B500RV9	6518	±0.1%	500Ω	±5ppm/°C	1.0W	400V
MMFR6518B1K00V9	6518	±0.1%	1ΚΩ	±5ppm/°C	1.0W	400V
MMFR6518B2K00V9	6518	±0.1%	2ΚΩ	±5ppm/°C	1.0W	400V
MMFR6518B5K00V9	6518	±0.1%	5ΚΩ	±5ppm/°C	1.0W	400V
MMFR6518B10K0V9	6518	±0.1%	10ΚΩ	±5ppm/°C	1.0W	400V
MMFR6518B20K0V9	6518	±0.1%	20ΚΩ	±5ppm/°C	1.0W	400V
MMFR6518B50K0V9	6518	±0.1%	50ΚΩ	±5ppm/°C	1.0W	400V
MMFR6518B100KV9	6518	±0.1%	100ΚΩ	±5ppm/°C	1.0W	400V
MMFR6518B200KV9	6518	±0.1%	200ΚΩ	±5ppm/°C	1.0W	400V
MMFR6518B500KV9	6518	±0.1%	500ΚΩ	±5ppm/°C	1.0W	400V
MMFR6518B1M00V9	6518	±0.1%	1ΜΩ	±5ppm/°C	1.0W	400V

Revision

Version	Revised Content	Date	Approver
V0	Initial Issue	2023/4/28	LFY



MMFR

Precision Metal Film Molded Resistor

Disclaimer

All products, datasheets and data can be changed without prior notice.

C&B Electronics Shenzhen CO., LTD., its affiliates, distributors, employees, and any other person acting on its behalf (collectively referred to as "C&B Electronics") shall not bear any legal responsibility for any errors, inaccuracies, or incompleteness of information related to the product disclosed under this agreement or other disclosures.

Product datasheet does not constitute an extension or revision of the purchase terms and conditions in C&B Electronics, including but not limited to the warranties under this agreement.

Unless specified in the purchase terms and conditions, C&B Electronics makes no guarantees, representations or warranties.

To the maximum extent permitted by applicable laws, C&B Electronics hereby makes the following disclaimer:

- (1) All liabilities arising from the use of the product;
- (2) Including but not limited to all liabilities arising from special, indirect or incidental damages;
- (3) All implied warranties, including warranties of suitability for special purposes, non infringement possibility, and marketability.

The information provided in the datasheet and parameter tables may vary in different applications, and the performance of the product may change over time. The recommended application instructions for the product are based on C&B Electronics' understanding and experience of typical requirements. Customers are obligated to verify whether the product is suitable for a specific application based on the parameters provided in the datasheet. Before officially installing or using the product, you should ensure that you have obtained the latest version of relevant information, which can be obtained through the website: resistor.today.

The signing of this agreement does not constitute an express, implied or other form of license related to all intellectual property rights of C&B Electronic Products.

Unless explicitly stated, the products listed in this agreement are not applicable to lifesaving or life sustaining products. In the absence of a clear indication, the customer shall bear all risks caused by unauthorized use of the above products and agree to fully compensate C&B Electronics for all losses caused by such sales or use. For written product terms for such special applications, please contact authorized personnel from C&B Electronics to obtain.

The names and markings on the listed products may be trademarks owned by others.