

**W-Series
WAP WTL6/1 EN**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

Type	WAP WTL6/1 EN
Order No.	1957710000
Version	W-Series, End plate
GTIN (EAN)	4032248654024
Qty.	20 pc(s).

W-Series
WAP WTL6/1 EN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	1.5 mm	Width (inches)	0.059 inch
Height	65 mm	Height (inches)	2.559 inch
Depth	34.5 mm	Depth (inches)	1.358 inch
Net weight	3.935 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	Wemid	Colour code	dark beige
UL 94 flammability rating	V-0		

System specifications

Version	End plate
---------	-----------

Additional technical data

Installation advice	Feed-through (bushing), Direct mounting
---------------------	--

Classifications

ETIM 3.0	EC000886	ETIM 4.0	EC000886
ETIM 5.0	EC000886	ETIM 6.0	EC000886
UNSPSC	30-21-18-27	eClass 5.1	27-14-11-33
eClass 6.2	27-14-11-33	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.1	27-14-11-33

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP