
# AN110204-01S

Rev. 001



824 MHz / 960 MHz / 1710 MHz / 2170 MHz PCB Antenna (5G, LTE, IoT, UMTS, WCDMA)



#### **General information**

This small antenna is intended to be soldered to the main PCB of the mobile devices, routers or gateways. On request, the antenna geometry can be optimized for customer's housing design and material properties.

#### **Typical applications**

5G NR, LTE, GSM, CDMA, DCS, PCS, WCDMA, UMTS, HSPDA, EDGE, IMT, IoT

Electrical data		
Antenna type	Embedded / internal antenna soldered on the main PCB	
5G bands	1, 2, 3, 5, 8, 18, 25, 26, 34, 39, 65, 66, 70, 80 - 82, 84, 86, 89, 95, 98	
4G bands	1 - 6, 8 -10, 18 - 20, 23, 25 - 27, 33 - 37, 39, 65, 66, 70	
Frequency range [MHz]	824960	17102170
Return loss [dB] 1)	-8	-10
Peak gain [dBi]	1.7	3.6
Radiation efficiency [%]	78	69
Nominal input impedance [Ohm]	50	
Polarization	linear	
Radiation pattern	omnidirectional	
Maximum input power [W]	5	

Mechanical data		
Antenna PCB dimensions [mm]	47.7 x 21.4 x 1.6	
PCB material	FR4	
Weight [g]	3	

Environmental data		
Operating temperature [°C]	-40+85	
Storage temperature [°C]	-40+85	
Ambient relative humidity [%]	095	
RoHS / REACH compliant	yes / yes	

#### Additional information

All electrical data have been obtained in free space on the reference board (not included) with the following dimensions:125mm x 60mm x 0.8mm. Please note that the performance in the lower frequency bands is dependent on the ground plane length and may degrade in case of reducing the board size.

Other mechanical designs, materials or frequency bands are possible on request.

Further customization, electromagnetic simulations and measurements can be offered on request.


All information (including technical data and pictures) presented in this document is typical and subject to change without notice. Sevskiy is a registered trade mark of Sevskiy GmbH. Copyright © 2009 - 2023 Sevskiy GmbH. All rights reserved. No warranties.


## AN110204-01S

Rev. 001



824 MHz / 960 MHz / 1710 MHz / 2170 MHz PCB Antenna (5G, LTE, IoT, UMTS, WCDMA)






All information (including technical data and pictures) presented in this document is typical and subject to change without notice. Sevskiy is a registered trade mark of Sevskiy GmbH. Copyright © 2009 - 2023 Sevskiy GmbH. All rights reserved. No warranties.

Tel.: +49 89 38-90-7229 Fax: +49 89 38-90-7230

Sevskiy<sup>®</sup> RF & Antenna Development

824 MHz / 960 MHz / 1710 MHz / 2170 MHz PCB Antenna (5G, LTE, IoT, UMTS, WCDMA)



All information (including technical data and pictures) presented in this document is typical and subject to change without notice. Sevskiy is a registered trade mark of Sevskiy GmbH. Copyright © 2009 - 2023 Sevskiy GmbH. All rights reserved. No warranties.

Tel.: +49 89 38-90-7229 Fax: +49 89 38-90-7230

### AN110204-01S

Rev. 001

824 MHz / 960 MHz / 1710 MHz / 2170 MHz PCB Antenna (5G, LTE, IoT, UMTS, WCDMA)


Product dimensions and recommended layout



47.7 1.6 0  $\triangleleft$ 00 2 Top layer Bottom layer 60 53 45.9 0 Ċ Ċ Ċ R1.6 (12X) 50 Ohm feed line Matching circuit pads -R0.85 (12X)  $\sim$ (empty typical) Matching circuit pads (zero Ohm typical)  $\sim$ 1.7 M Unit: mm Plated through holes (3X) 0.85 Copper 3 3.4 Free solder mask area 3.8 All information (including technical data and pictures) presented in this document is typical and subject to change without notice. Sevskiy is a registered trade mark of Sevskiy GmbH. Copyright © 2009 - 2023 Sevskiy GmbH. All rights reserved. No warranties. Rev. 001



824 MHz / 960 MHz / 1710 MHz / 2170 MHz PCB Antenna (5G, LTE, IoT, UMTS, WCDMA)



All information (including technical data and pictures) presented in this document is typical and subject to change without notice. Sevskiy is a registered trade mark of Sevskiy GmbH. Copyright © 2009 - 2023 Sevskiy GmbH. All rights reserved. No warranties.