


868 MHz / 915 MHz / 2.45 GHz / 5.5 GHz PCB Antenna (ISM, IoT, RFID, Bluetooth, Wi-Fi, 5G NR, LTE)



General information

This small antenna is intended to be used within a plastic housing of a mobile device, a terminal or a router. On request, the antenna geometry can be optimized for customer's housing design or other requirements.

Typical applications

ISM, RFID, IoT (Sigfox, LoRa, NB-IoT), LP-WAN, Smart meters, 5G NR, LTE

Electrical data

Antenna type	Embedded / internal PCB antenna						
5G bands	1, 2, 3, 5, 8, 14, 18, 20, 25, 26, 34, 39, 47, 65, 66, 70, 80 - 82, 84, 86, 89, 95, 98						
4G bands	1 - 6, 8-10, 14, 18 - 20, 22, 23, 25 - 27, 33 - 37, 39, 42, 47, 65, 66, 70						
Other frequency bands	SRD860 (EU), ISM915 (US), ISM5800,						
Frequency range [MHz]	758... 928	791... 862	862... 870	1593... 2200	1695... 2170	3400... 3600	5725... 5925
Return loss [dB]	-5	-10	-9	-5	-10	-5	-6
Peak gain [dBi]	-1	-0.2	-0.1	0.8	0.9	4.2	4.6
Radiation efficiency [%]	85	84	84	67	66	85	81
Nominal input impedance [Ohm]	50						
Polarization	linear						
Radiation pattern	omnidirectional						
Maximum input power [W]	10						

Mechanical data

Antenna PCB dimensions [mm]	70 x 19 x 0.8
Connector type ¹⁾	IPEX MHF1 / Hirose U.FL (UMCC) compatible ¹⁾
Cable type and thickness ²⁾ [mm]	micro coax 1.13 ²⁾
Cable length ³⁾ [mm]	160 ³⁾
PCB material	FR4

Environmental data

Operating temperature [°C]	-40...+85
Storage temperature [°C]	-40...+85
Ambient relative humidity [%]	0...95
RoHS / REACH compliant	yes / yes

Additional information

¹⁾ Other connector types can be offered on request.

²⁾ Following cable thicknesses can be used with MHF1 connector: 0.81 mm, 1.13 mm, 1.32 mm, 1.37 mm.

³⁾ Other cable lengths can be provided.

Antenna performance was measured using the specified cable length in free space.


Further customization, electromagnetic simulations and measurements can be offered on request.

The antenna can be additionally equipped with adhesive tape and mounting holes.


All information (including technical data and pictures) presented in this document is typical and subject to change without notice. Sevskiy is a registered trade mark of Sevskiy GmbH. Copyright © 2009 - 2023 Sevskiy GmbH. All rights reserved. No warranties.

868 MHz / 915 MHz / 2.45 GHz / 5.5 GHz PCB Antenna (ISM, IoT, RFID, Bluetooth, Wi-Fi, 5G NR, LTE)

Product dimensions



Measured input impedance matching



All information (including technical data and pictures) presented in this document is typical and subject to change without notice. Sevskiy is a registered trade mark of Sevskiy GmbH. Copyright © 2009 - 2023 Sevskiy GmbH. All rights reserved. No warranties.