Rev. 004



868 MHz / 915 MHz / 2.45 GHz / 5.8 GHz PCB Antenna (ISM, IoT, RFID, Bluetooth, Wi-Fi, 5G NR, LTE)



General information

This small antenna is intended to be used within a plastic housing of a mobile device, a terminal or a router. On request, the antenna geometry can be optimized for customer's housing design or other requirements.

Typical applications

ISM, RFID, IoT (Sigfox, LoRa, NB-IoT), LP-WAN, Smart meters, Bluetooth, Wi-Fi 2.4 GHz, 5G NR, LTE

Electrical data								
Antenna type	Embedded / internal PCB antenna							
5G bands	5, 7, 18, 20, 26, 30, 38, 40, 41, 47, 53, 81, 82, 89, 90, 96, 97							
4G bands	5, 6, 7, 18, 19, 20, 22, 26, 27, 30, 38, 40, 41, 42, 47, 53, 69							
Other frequency bands	SRD860 (EU), ISM915 (US), ISM2400, ISM5800							
Frequency range [MHz]	791	807	824	2300	2400	2496	3400	5855
	928	890	870	2360	2495	2620	3600	5925
Return loss [dB]	-6	-10	-15	-10	-15	-9	-5	-5
Peak gain [dBi]	1.6	1.4	1.4	4	4.2	4.8	7	6.2
Radiation efficiency [%]	80	82	85	77	71	85	87	90
Nominal input impedance [Ohm]	50							
Polarization	linear							
Radiation pattern	omnidirectional							
Maximum input power [W]	10							

Mechanical data					
Antenna PCB dimensions [mm]	38 x 17 x 1				
Connector type 1)	IPEX MHF1 / Hirose U.FL (UMCC) compatible 1)				
Cable type and thickness ²⁾ [mm]	micro coax 1.13 ²⁾				
Cable length ³⁾ [mm]	180 ³⁾				
PCB material	FR4				

Environmental data					
Operating temperature [°C]	-40+85				
Storage temperature [°C]	-40+85				
Ambient relative humidity [%]	095				
RoHS / REACH compliant	yes / yes				

Additional information

- 1) Other connector types can be offered on request.
- ²⁾ Following cable thicknesses can be used with MHF1 connector: 0.81 mm, 1.13 mm, 1.32 mm, 1.37 mm.
- 3) Recommended length. Cable is not included, but can be customized and provided separately.

Antenna performance was measured using the recommended cable length in free space.

Further customization, electromagnetic simulations and measurements can be offered on request.

The antenna can be additionally equipped with adhesive tape and mounting holes.

All information (including technical data and pictures) presented in this document is typical and subject to change without notice. Sevskiy is a registered trade mark of Sevskiy GmbH. Copyright © 2009 - 2023 Sevskiy GmbH. All rights reserved. No warranties.

Tel.: +49 89 38-90-7229

Fax: +49 89 38-90-7230


E-Mail: sergey@sevskiy.de

Internet: www.sevskiy.com

Rev. 004



868 MHz / 915 MHz / 2.45 GHz / 5.8 GHz PCB Antenna (ISM, IoT, RFID, Bluetooth, Wi-Fi, 5G NR, LTE)



Tel.: +49 89 38-90-7229

Fax: +49 89 38-90-7230

E-Mail: sergey@sevskiy.de

Internet: www.sevskiy.com