

## KN 19 - Short-travel main switch, 2-pole

## 1.12.000.501/0000

For keycaps, refer to RK 90 system design.

Positive opening contacts to IEC 947-5-1.

1-LED spot-illumination (max. 3 mm) possible.



General information		
Recommended key grid	19.05 x 38.1 mm	
<b>D</b> '		
Dimensions		
Length	37.8 mm	
Width	18.8 mm	
Overall height	9.7 mm	
Mechanical design		
Mounting	on PCB	
Terminals	THT solder terminals	
Contact system	snap-action bridge contact	
Contact arrangement	2 NC / 2 NO	
Contact materials	Ag	
Illumination	1 LED (max. 3 mm) possible	
Degree of protection	IP40 (DIN EN 60529)	
Hot wire ignition acc. to IEC 60695-2-1	850 °C	
Mechanical characteristics		
Operating force max.	9 <sup>±3</sup> N	
Operating travel	0.55 <sup>±0.15</sup> mm	
Robustness max.	100 N	
Electrical characteristics		
Rated voltage AC min.	12 V	
Rated voltage DC min.	12 V	
Rated voltage AC max.	250 V	
Rated voltage DC max.	50 V	
Ohmic load DC max.	10 A	
Ohmic load DC min.	0.1 A	
Ohmic load AC	6 A	
Contact resistance when new max.	50 mΩ	
	100 A	
Capacity input current AC max.	100 A	
Capacity input current AC max. Rated motor current AC	4 A	

Technical data are approximate and intended solely for general orientation in the selection of a product. Subject to modifications and errors. Images and other graphics may only be similar. For more information, refer to www.rafi.de chapter Imprint / Data Protection. 22.11.2017





Deuneine	time a maay		
Bouncina	time max.		

Other specifications	
Ambient temp. operating min.	-25 °C
Ambient temp. operating max.	+70 °C
Environmental restistance	acc. to IEC 60068-2-14, -30, -33 and -78
Operating life AC	AC 250 V: 200.000 /2A; 100.000 /6A
Operating life DC	50,000(10 A / 50 V=)
Soldering time max.	3 s
Soldering temperature max.	<u>350 °C</u>
Flame class acc. to UL 94	UL 94 VO
ROHS compliant	yes
REACH compliant	ves

10 ms

## PCB footprint





## 2 NC / 2 NO



Technical data are approximate and intended solely for general orientation in the selection of a product. Subject to modifications and errors. Images and other graphics may only be similar. For more information, refer to www.rafi.de chapter Imprint / Data Protection.