ThingMagic® M7E-TERA UHF RAIN® RFID Module



46 mm L x 26 mm W x 4.0 mm H

Features & Benefits:

- Small Form Factor Coupled with Powerful Performance
- RF Power Output of +31.5 dBm* Results in Tag Read Distance Over 12 Meters*
- Features the Impinj E710 RAIN RFID Reader Chip
- Support for EPCglobal Gen2 (ISO 18000-63) Protocol Meets Industry Tag Standards
- Reads up to 800* Tags/ Second to Support Fast Moving Tags and Large Tag Populations
- Configured for Multiple Regions, such as FCC / ISED (North & South America), ETSI (European Union), and other Regions Including India, China, Korea, Australia and Japan
- Module Size and Feature Set comparable to ThingMagic M6e

High Performance, Multi-Protocol, 4-Port, Embedded UHF RAIN[®] RFID Module

ThingMagic M7E-TERA is a 4-port module that meets or exceeds the performance requirements of the most demanding fixed position multi-antenna reader applications. The M7E-TERA's high read rate and RF power, coupled with its form factor and time-to-market advantages, make it the ideal solution for Original Equipment Manufacturer (OEM) applications. Transmitting up to +31.5 dBm* and reading more than 800* tags/second, ThingMagic's M7E-TERA performance is outstanding in challenging applications.

The four RF connections to antennas can be made via edge pads or U.FL connectors

ThingMagic M7E-TERA is supported by ThingMagic API.

Applications:

- OEM
- Value-Added Reseller
- Solution Providers
- Medical Cabinets
- Race Timing
- Portals with Long Cable Runs
- Inventory Tracking.
- Conveyors Requiring Multiple Antenn







Ordering Information	
Module	M7E-TERA
Module on Carrier Board	M7E-TERA-CB
Development Kit	M7E-TERA-DEVKIT
Physical	
Dimensions	46 mm L x 26 mm W x 4.0 mm H (1.8 in L x 1.0 in W x 0.16 in H)
Tag / Transponder Protocols	
RFID Protocol Support	EPCglobal Gen 2 (ISO 18000-63) with DRM
RF Interface	
RF Transceiver	Impinj E710
Antenna Connector	Four 50 Ω connections (board-edge or U.FL)
RF Power Output	Separate read and write levels, command-adjustable from +5 dBm to +31.5 * in 0.5 dB steps, accurate to +/- 1 dBm
Regulatory	Pre-configured for the following regions: FCC (NA, SA) 902-928MHz; ETSI (EU) 865.6-867.6 MHz; TRAI (India) 865-867 MHz; KCC (Korea) 917- 923.5 MHz; ACMA (Australia) 920-926 MHz; SRRC-MII (P.R. China) 920.1-924.9 MHz; MIC (Japan) 916.8-922.2 MHz; 'Open' (Customizable channel plan; 860-930 MHz)
Data/Control Interface	
Physical	38 board-edge connections providing DC power, communication, control and GPIO signals
Control/Data Interfaces	UART; 3.3V logic levels from 9.6 to 921.6 kbps
GPIO Sensors and Indicators	Four 3.3V bidirectional ports configurable as input (sensor) ports or output (indicator) ports
API support	C#/.NET, Java, C
Power	
DC Power Required	DC Voltage: 3.3 to 5V DC power consumption when reading: TBD @ +31.5 dBm; TBD @ power levels under +17 dBm
Power Saving Options	Ready: TBD Sleep: TBD Shutdown: TBD
Environment	
Certification	USA (FCC 47 CFR Ch. 1 Part 15); Canada (Industry Canada RSS-247); EU (ETSI EN 302 208 v3.1.1, RED 2014/53/EU); JAPAN (MIC Article 38 Section 24)**
Operating Temp.	-40°C to +60°C (case temperature)
Storage Temp.	-40°C to +85°C
Shock and Vibration	Survives 1 meter drop during handling
Performance	
Max Read Rate	Up to 800* tags/second using high-performance settings
Max Tag Read Distance	Over 12 meters (36 feet) with 6 dBi antenna (36 dBm EIRP)*
Specifications subject to change with * Actual Max Performance is TBD **Japan Certification is pending	

ABOUT JADAK:

JADAK, a business unit of Novanta, is a market leader in machine vision, RFID, barcode, printing, and color and light measurement products and services for original equipment manufacturers. The business designs and manufactures custom embedded detection and analysis solutions that help customers solve unique inspection, tracking, scanning and documenting challenges. JADAK is based in Syracuse, New York, with sales and technical locations across the globe. For more information, visit <u>www.jadaktech.com</u>. ThingMagic is JADAK's RFID line of products.

Novanta is a trusted technology partner to OEMs in the medical and advanced industrial technology markets, with deep proprietary expertise in photonics, vision and precision motion technologies. For more information, visit <u>www.novanta.com</u>.



USA Office phone:+1 315.701.0678 email: info@jadaktech.com web: jadaktech.com

European Office

phone:+49 89 31 707 100 email: info@jadaktech.com Asia Pacific Office

phone: +86 512.6283.7080 email: info@jadaktech.com

© 2023 Novanta Inc. and its affiliated companies. All rights reserved. Rev 06262023

