# <u>TOSHIBA</u>

Unit: mm


TOSHIBA LED Lamps

# TLBD1100B(T11), TLEGD1100B(T11)

#### Panel Circuit Indicators


- Surface-mount devices
- 3.2 (L) mm  $\times$  2.8 (W) mm  $\times$  1.9 (H) mm
- Flat-top type
- InGaN LEDs
- High luminous intensity
- Low drive current, high-intensity light emission
- Colors Blue: λd = 470 nm (typ.) Green: λd = 528 nm(typ.)
- Applications: backlighting, pilot lamp etc.
- Standard embossed tape packing: T11 (2000 pcs / reel)

8-mm tape reel



### **Color and Material**

Part Number	Color	Material
TLBD1100B	Blue	InGaN
TLEGD1100B	Green	Indaly




# Absolute Maximum Ratings (Ta = 25°C)

Part Number	Forward Current I <sub>F</sub> (mA) See Note 1	Reverse Voltage V <sub>R</sub> (V)	Power Dissipation PD (mW)	Operation Temperature T <sub>opr</sub> (°C)	Storage Temperature T <sub>stg</sub> (°C)
TLBD1100B	30		120	-40 to 100	-40 to 100
TLEGD1100B	30	$\mathcal{D}$		-40 10 100	-40 10 100

Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings.

Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc).

Note 1: Forward current derating



### **Electrical Characteristics (Ta = 25°C)**

Part Number	F	Forward \	Reverse Current I <sub>R</sub>			
	Min	Тур.	Max	١ <sub>F</sub>	Max	VR
TLBD1100B	2.7	3.3	4.0	20	10	4
TLEGD1100B	2.7	3.3	4.0	20	10	7
Unit	V			mA	μA	V

# **Optical Characteristics-1 (Ta = 25°C)**

Part Number	L	uminous	Intensity	Available I <sub>V</sub> rank (Note 2)	
Fait Number	Min	Тур.	Max	١ <sub>F</sub>	
TLBD1100B	40	70	200	20	PA / QA / RA
TLEGD1100B	100	200	500	20	RA / SA / TA
Unit		mcd		mA	$\overline{7}$

#### Note 2: The specification as following table is used for Iv classification of LEDs in Toshiba facility. Each reel includes the same rank LEDs. Let the delivery ratio of each rank be unquestioned.

I <sub>V</sub> rank						
Rank symbol	Min	Max				
PA	40	80				
QA	63	125				
RA	100	200				
SA	160	320				
TA	250	500				
Unit	mcd	mçd				

# Optical Characteristics-2 (Ta = 25°C)

	$\langle \langle \rangle$			Emission	Spectrum	$\mathcal{D}$		
Part Number		ak Emiss avelength		Δλ	Domina	nt Wavele	ength $\lambda_d$	IF
$\sim$	∕∕Min	Тур.	Max	Тур.	Min	Тур.	Max	.1
TLBD1100B 🗸	$\searrow$	468	$- \land$	22	463	470	477	20
TLEGD1100B		518	$\swarrow$	35	518	528	538	20
Unit (	))	nm		nm		nm		mA

#### Note 3: Caution


ESD withstand voltage according to MIL STD 883D, Method 3015.7 : ≥1000 V

When handling this LED, take the following measures to prevent the LED from being damaged or otherwise adversely affected.


- 1) Use a conductive tablemat and conductive floor mat, and ground the workbench and floor.
- 2) Operators handling laser diodes must be grounded via a high resistance (about 1 MΩ). A conductive strap is good for this purpose.
- 3) Ground all tools including soldering irons.

This product is designed as a general display light source usage, and it has applied the measurement standard that matched with the sensitivity of human's eyes. Therefore, it is not intended for usage of functional application (ex. Light source for sensor, optical communication and etc) except general display light source.

# TLBD1100B



# TLEGD1100B



# Packaging

These LED devices are packed in an aluminum envelope with a silica gel and a moisture indicator to avoid moisture absorption. The optical characteristics of the devices may be affected by exposure to moisture in the air before soldering and they should therefore be stored under the following conditions:

- This moisture proof bag may be stored unopened within 12 months at the following conditions. Temperature: 5°C to 30°C Humidity: 90% (max)
- 2. After opening the moisture proof bag, the devices should be assembled within 168 hours in an environment of 5°C to 30°C/60% RH or below.
- 3. If upon opening, the moisture indicator card shows humidity 30% or above (Color of indication changes to pink) or the expiration date has passed, the devices should be baked in taping with reel. After baking, use the baked devices within 72 hours, but perform baking only once. Baking conditions: 60±5°C, for 12 to 24 hours.

Expiration date: 12 months from sealing date, which is imprinted on the same side as this label affixed. 4. Repeated baking can cause the peeling strength of the taping to change, then leads to trouble in mounting.


- Furthermore, prevent the devices from being destructed against static electricity for baking of it.
- 5. If the packing material of laminate would be broken, the hermeticity would deteriorate. Therefore, do not throw or drop the packed devices.

# **Mounting Method**

### Soldering

- Reflow soldering (example)
  - Temperature profile for Pb soldering (example)


Temperature profile for Pb-free soldering (example)



- The products are evaluated using above reflow soldering conditions. No additional test is performed exceed the condition (i.e. the condition more than (\*)MAX values) as a evaluation. Please perform reflow soldering under the above conditions.
- Please perform the first reflow soldering with reference to the above temperature profile and within 168 h of opening the package.
- Second reflow soldering In case of second reflow soldering should be performed within 168 h of the first reflow under the above conditions. Storage conditions before the second reflow soldering: 30°C, 60% RH (max)
- Make any necessary soldering corrections manually. (only once at each soldering point) Soldering iron: 25 W Temperature: 300°C or less
  - Time: within 3 s
- If the product needs to be performed by other soldering method (ex. wave soldering), please contact Toshiba sales representative.

#### Land pattern dimensions for reference only

Unit: mm



I Init: mm

#### Cleaning

TOSHIBA

When cleaning is required after soldering, Toshiba recommends the following cleaning solvents. It is confirmed that these solvents have no effect on semiconductor devices in our dipping test (under the recommended conditions). In selecting the one for your actual usage, please perform sufficient review on washing condition, using condition and etc.

ASAHI CLEAN AK-225AES: KAO CLEAN THROUGH 750H: PINE ALPHA ST-100S: (made by ASAHI GLASS) (made by KAO) (made by ARAKAWA CHEMICAL)

#### **Precautions When Mounting**

Do not apply force to the plastic part of the LED under high-temperature conditions. To avoid damaging the LED plastic, do not apply friction using a hard material. When installing the PCB in a product, ensure that the device does not come into contact with other emponents.

### **Tape Specifications**


#### 1. Product Number Format

The type of package used for shipment is denoted by a symbol suffix after the product number. The method of classification is as below. (this method, however does not apply to products whose electrical characteristics differ from standard Toshiba specifications)

- (1) Tape Type: T14 (4-mm pitch)
- (2) Example

#### 2. Tape Dimensions


		$\sim$	_	7/	$\langle \rangle$	Unit. min
Symbol	Dimension	Tolerance		Symbol	Dimension	Tolerance
D	(1.5)	+0.1/-0	$\langle$	$(P_2)$	2.0	±0.05
E	1.75	±0.1		W	8.0	±0.3
P <sub>0</sub>	4.0	±0.1		P	4.0	±0.1
t 🔨	0.3	±0.05		A <sub>0</sub>	2.9	±0.1
F	3,5	±0.05		∼ во	3.7	±0.1
D <sub>1</sub>	1.5	±0.1		K <sub>0</sub>	2.3	±0.1
~ []						



<u>TOSHIBA</u>

### 3. Reel Dimensions

Unit: mm



Note 1: Empty trailer section Note 2: Empty leader section

### 5. Packing Display


(1) Packing quantity

Reel	2,000 pcs
Carton	10,000 pcs

(2) Packing form: Each reel is sealed in an aluminum pack with silica gel.

#### 6. Label Format

(1) Example: TLBD1100B (T11)



# **RESTRICTIONS ON PRODUCT USE**

- Toshiba Corporation, and its subsidiaries and affiliates (collectively "TOSHIBA"), reserve the right to make changes to the information in this document, and related hardware, software and systems (collectively "Product") without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample applications. TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.
- Product is intended for use in general electronics applications (e.g., computers, personal equipment, office equipment, measuring equipment, industrial robots and home electronics applications or for specific applications as expressly stated in this document. Product is neither intended nor warranted for use in equipment or systems that require extraordinarily high levels of quality and/or reliability and/or a malfunction or failure of which may cause loss of human life, bodily injury, serious property damage or serious public impact ("Unintended Use"). Unintended Use includes, without limitation, equipment used in nuclear facilities) equipment used in the aerospace industry, medical equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions, safety devices, elevators and escalators, devices related to electric power, and equipment used in finance-related fields. Do not use Product for Unintended Use unless specifically permitted in this document.
- · Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your POSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. TOSHIBA assumes no liability for damages or losses occurring as a result of noncompliance with applicable laws and regulations.