

Antenna YB0014AA Datasheet

Antenna Services

Version: 3.2

Date: 2021-12-08

Status: Released







At Quectel, our aim is to provide timely and comprehensive services to our customers. If you require any assistance, please contact our headquarters:

Quectel Wireless Solutions Co., Ltd.

Building 5, Shanghai Business Park Phase III (Area B), No.1016 Tianlin Road, Minhang District, Shanghai 200233, China Tel: +86 21 5108 6236 Email: info@guectel.com

Or our local offices. For more information, please visit: http://www.quectel.com/support/sales.htm.

For technical support, or to report documentation errors, please visit: http://www.quectel.com/support/technical.htm. Or email us at: support@quectel.com.

Legal Notices

We offer information as a service to you. The provided information is based on your requirements and we make every effort to ensure its quality. You agree that you are responsible for using independent analysis and evaluation in designing intended products, and we provide reference designs for illustrative purposes only. Before using any hardware, software or service guided by this document, please read this notice carefully. Even though we employ commercially reasonable efforts to provide the best possible experience, you hereby acknowledge and agree that this document and related services hereunder are provided to you on an "as available" basis. We may revise or restate this document from time to time at our sole discretion without any prior notice to you.

Use and Disclosure Restrictions

License Agreements

Documents and information provided by us shall be kept confidential, unless specific permission is granted. They shall not be accessed or used for any purpose except as expressly provided herein.

Copyright

Our and third-party products hereunder may contain copyrighted material. Such copyrighted material shall not be copied, reproduced, distributed, merged, published, translated, or modified without prior written consent. We and the third party have exclusive rights over copyrighted material. No license shall be granted or conveyed under any patents, copyrights, trademarks, or service mark rights. To avoid ambiguities, purchasing in any form cannot be deemed as granting a license other than the normal non-exclusive, royalty-free license to use the material. We reserve the right to take legal action for noncompliance with abovementioned requirements, unauthorized use, or other illegal or malicious use of the material.



Trademarks

Except as otherwise set forth herein, nothing in this document shall be construed as conferring any rights to use any trademark, trade name or name, abbreviation, or counterfeit product thereof owned by Quectel or any third party in advertising, publicity, or other aspects.

Third-Party Rights

This document may refer to hardware, software and/or documentation owned by one or more third parties ("third-party materials"). Use of such third-party materials shall be governed by all restrictions and obligations applicable thereto.

We make no warranty or representation, either express or implied, regarding the third-party materials, including but not limited to any implied or statutory, warranties of merchantability or fitness for a particular purpose, quiet enjoyment, system integration, information accuracy, and non-infringement of any third-party intellectual property rights with regard to the licensed technology or use thereof. Nothing herein constitutes a representation or warranty by us to either develop, enhance, modify, distribute, market, sell, offer for sale, or otherwise maintain production of any our products or any other hardware, software, device, tool, information, or product. We moreover disclaim any and all warranties arising from the course of dealing or usage of trade.

Privacy Policy

To implement module functionality, certain device data are uploaded to Quectel's or third-party's servers, including carriers, chipset suppliers or customer-designated servers. Quectel, strictly abiding by the relevant laws and regulations, shall retain, use, disclose or otherwise process relevant data for the purpose of performing the service only or as permitted by applicable laws. Before data interaction with third parties, please be informed of their privacy and data security policy.

Disclaimer

- a) We acknowledge no liability for any injury or damage arising from the reliance upon the information.
- b) We shall bear no liability resulting from any inaccuracies or omissions, or from the use of the information contained herein.
- c) While we have made every effort to ensure that the functions and features under development are free from errors, it is possible that they could contain errors, inaccuracies, and omissions. Unless otherwise provided by valid agreement, we make no warranties of any kind, either implied or express, and exclude all liability for any loss or damage suffered in connection with the use of features and functions under development, to the maximum extent permitted by law, regardless of whether such loss or damage may have been foreseeable.
- d) We are not responsible for the accessibility, safety, accuracy, availability, legality, or completeness of information, advertising, commercial offers, products, services, and materials on third-party websites and third-party resources.

Copyright © Quectel Wireless Solutions Co., Ltd. 2021. All rights reserved.

About the Document

Revision History

Version	Date	Author	Note
-	2020-09-11	Kenny YIN	Creation of the document
1.0	2020-09-11	Kenny YIN	First official release
1.1	2021-01-18	Kenny YIN	Updated the antenna image in Chapter 2.
2.0	2021-04-02	Kenny YIN	Updated the data in Product Specifications and the test data in the datasheets.
3.0	2021-07-25	Kenny YIN	Updated all test data in this datasheet.
3.1	2021-12-03	Kenny YIN	Updated the product description in Chapter 1.
3.2	2021-12-08	Aria CHU	Updated the data for product specifications (Chapter 3).

Contents

		cument	
1	Product	Description	5
2	Product	Features	5
3	Product	Specifications	6
4	Overall P	Performance	7
		st Environment	
		WR (Data of 1 Meter Cable)	
	4.2.1	4G	8
	4.2.2	4G DIV	9
	4.2.3	GNSS	10
	4.3. Eff	iciency (Data of 1 Meter Cable)	11
	4.3.1	. 4G	11
	4.3.2	4G DIV	12
	4.4. Ga	ain (Data of 1 Meter Cable)	13
	4.4.1	. 4G	13
	4.4.2	4G DIV	14
	4.4.3	. GNSS	15
	4.5. Ra	diation Patterns (Data of 1 Meter Cable)	16
	4.5.1	. 4G	17
	4.5.2	4G DIV	21
5	Product	Size	25

1 Product Description

To meet customers' requirements for the high performance, high integration, and integrated appearance of their products, Quectel provides a combined antenna box series. The antenna box can integrate a variety of antennas, such as 5G, 4G, GNSS, Wi-Fi antennas, to achieve communication functions of 5G MIMO, 4G, GNSS, and Wi-Fi. These antenna boxes can be mounted on the surface of devices via screw, adhesive or other methods, supports multiple connector types and cable lengths. It is a more flexible and reliable high-performance antenna solution for outdoor applications.

2 Product Features

- Cellular LTE + GNSS
- High efficiency
- Excellent performance



3 Product Specifications

Passive Electrical Specifications	
Frequency Range	4G: 698–1000 MHz; 1700–2700 MHz 4G DIV: 698–1000 MHz; 1700–2700 MHz GNSS: 1561.098 MHz ±3 MHz; 1575.42 ±3 MHz
Input Impendence	50 Ω
VSWR (Data of 1 Meter Cable)	4G: ≤ 3.0 4G DIV: ≤ 4.0
Gain (Data of 1 Meter Cable)	LNA (28 ±2 dB) 4G: ≤ 2 dBi 4G DIV: ≤ 2 dBi
Polarization Type	Linear (4G MAIN) Circular (GNSS)
Mechanical Specifications	
Antenna Size	81 mm × 14.5 mm RG174 Cable Length = 3000 mm
Casing	ABS + PC
Connector Type	SMA Male (with center pin)
Working Temperature	-40 °C to +85 °C
Radome Color	Black
IP Rating	IP66
Mounting Type	Screw

4 Overall Performance


4.1. Test Environment

- KEYSIGHT VNA Network Analyzer E5063A 100 kHz 8.5 GHz
- RayZone[®]2800 Chamber 5G (FR1) SISO/MIMO, 400 MHz 8.0 GHz



4.2. VSWR (Data of 1 Meter Cable)


4.2.1. 4G



Frequency (MHz)	700	824	960	1710	1990	2170	2450	2570	2690
VSWR	2.23	1.75	2.25	1.46	1.31	1.4	1.18	1.29	1.44


4.2.2. 4G DIV

QUECTEL






4.2.3 GNSS



Frequency (MHz)	1561	1575
VSWR	1.95	1.55


4.3. Efficiency (Data of 1 Meter Cable)

4.3.1. 4G




QUECTEL

4.3.2. 4G DIV




4.4. Gain (Data of 1 Meter Cable)

4.4.1. 4G




QUECTEL

4.4.2. 4G DIV




4.4.3. GNSS




Frequency (MHz)	1561	1575	1602	1606
Gain (dB)	28.82	28.34	27.74	27.69

4.5. Radiation Patterns (Data of 1 Meter Cable)





Note: Z is directed towards reflector antenna; Y is directed towards sky; X is directed towards OTA chamber door.

4.5.1. 4G




700.000MHz E1








820.000MHz




820.000MHz E1












850.000MHz








240


210



960.000MHz


150

120




180


960.000MHz H




,330

960.000MHz E1











1000.000MHz H 5.00 30 330 0.00 68 300 10.00 15.00 90 270 240 120 210 150 180


1000.000MHz E1





1700.000MHz





1700.000MHz E1













2200.000MHz





2200.000MHz H

30

.00

0.00

5.00

10.00

i sti

180

,330


210


300


270


40

2700.000MHz















4.5.2. 4G DIV










820.000MHz







820.000MHz E1 5.00 0.00













850.000MHz E1 0.0030







960.000MHz










960.000MHz E1 960.000MHz E2 5.00 30 30 330 0.00 5.00 60/ 60 300 90 270 90 240 120 120 210 150 150 180 180







1700.000MHz E1 5.00









-3.6 90 -5.6 -7.6 120 150 180

60

2200.000MHz H

5.00

0.00

5.00

0.00

,330

210


300

270

248

2200.000MHz E1


2700.000MHz





2200.000MHz E2 5.0030. 330 9.88 5.00 60 300 10.00 15.00 270 90 248 120 210 150 190

-12 -22 -3.7 -5.2 -7.2 -9.2 -11.2

2700.000MHz H









5 Product Size

