SiSA88DN

RoHS COMPLIANT

HALOGEN

FREE

www.vishay.com

Vishay Siliconix



PRODUCT SUMMARY V_{DS} (V) 30 $R_{DS(on)}$ max. (Ω) at V_{GS} = 10 V 0.0067 $R_{DS(on)}$ max. (Ω) at $V_{GS} = 4.5$ V 0.0100 Q_g typ. (nC) 8.3 40.5 I_D (A) Configuration Single


FEATURES

N-Channel 30 V (D-S) MOSFET

- TrenchFET[®] Gen IV power MOSFET
- 100 % R_g and UIS tested
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- DC/DC conversion
- Battery protection
- Load switching
- DC/AC inverters



ORDERING INFORMATION	
Package	PowerPAK 1212-8
Lead (Pb)-free and halogen-free	SiSA88DN-T1-GE3

PARAMETER		SYMBOL	LIMIT	UNIT	
Drain-source voltage		V _{DS}	30		
Gate-source voltage		V _{GS}	+20, -16	- V	
Continuous drain current (T _J = 150 °C)	T _C = 25 °C		40.5	_	
	T _C = 70 °C		32.4		
	T _A = 25 °C	ID	16.2 ^{b, c}		
	T _A = 70 °C		12.8 ^{b, c}		
Pulsed drain current (t = 300 µs)		I _{DM}	100	- A	
Continuous source-drain diode current	T _C = 25 °C		18		
	T _A = 25 °C	I _S	2.9 ^{b, c}	1	
Single pulse avalanche current		I _{AS}	10		
Single pulse avalanche energy	L = 0.1 mH	E _{AS}	5	mJ	
Maximum power dissipation	T _C = 25 °C		19.8	w	
	T _C = 70 °C		12.7		
	T _A = 25 °C	P _D	3.2 ^{b, c}		
	T _A = 70 °C		2 ^b ,c	1	
Operating junction and storage temperature range		T _J , T _{stg}	-55 to +150	°C	
Soldering recommendations (peak temperature) d, e			260		

THERMAL RESISTANCE RATINGS						
PARAMETER		SYMBOL	TYPICAL	MAXIMUM	UNIT	
Maximum junction-to-ambient b, f	t ≤ 10 s	R _{thJA}	31	39	°C/W	
Maximum junction-to-case (drain)	Steady state	R _{thJC}	5	6.3	C/W	

Notes

a. Based on $T_C = 25 \ ^\circ C$ b. Surface mounted on 1" x 1" FR4 board

t = 10 s c.

See solder profile (www.vishay.com/doc?73257). The PowerPAK 1212-8 is a leadless package. The end of the lead terminal is exposed copper (not plated) as a result of the singulation process in manufacturing. A solder fillet at the exposed copper tip cannot be guaranteed and is not required to ensure adequate bottom side solder interconnection Rework conditions: manual soldering with a soldering iron is not recommended for leadless components Maximum under steady state conditions is 81 °C/W d.

f.

S17-1504-Rev. A, 02-Oct-17

1

SiSA88DN

PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNIT	
Static	<u> </u>						
Drain-source breakdown voltage	V _{DS}	$V_{GS} = 0 V, I_D = 250 \mu A$	30	-	-		
Drain-source breakdown voltage (transient) ^c	V _{DSt}	$V_{GS} = 0 \text{ V}, \text{ I}_{D(aval)} = 10 \text{ A}, t_{transcient} \leq 50 \text{ ns}$	36	-	-	V	
V _{DS} temperature coefficient	$\Delta V_{DS}/T_J$	1 050	-	15.5	-	mV/°C	
V _{GS(th)} temperature coefficient	$\Delta V_{GS(th)}/T_J$	I _D = 250 μA	-	-4.7	-		
Gate-source threshold voltage	V _{GS(th)}	$V_{DS} = V_{GS}, I_D = 250 \ \mu A$	1.1	-	2.4	V	
Gate-source leakage	I _{GSS}	$V_{DS} = 0 V, V_{GS} = +20, -16 V$	-	-	± 100	nA	
Zero gate voltage drain current		$V_{DS} = 30 \text{ V}, \text{ V}_{GS} = 0 \text{ V}$	-	-	1		
	I _{DSS}	V _{DS} = 30 V, V _{GS} = 0 V, T _J = 55 °C	-	-	10	μA	
On-state drain current ^a	I _{D(on)}	$V_{DS} \ge 5 \text{ V}, \text{ V}_{GS} = 10 \text{ V}$	30	-	-	А	
Drain-source on-state resistance ^a	D	V _{GS} = 10 V, I _D = 10 A	-	0.0054	0.0067	Ω	
	R _{DS(on)}	V _{GS} = 4.5 V, I _D = 8 A	-	0.0078	0.0100		
Forward transconductance ^a	g _{fs}	V _{DS} = 10 V, I _D = 10 A	-	47	-	S	
Dynamic ^{b, d}	•	·					
Input capacitance	C _{iss}		-	985	-	рF	
Input capacitance	Coss		-	305	-		
Output capacitance	C _{rss}	$V_{DS} = 15 V, V_{GS} = 0 V, f = 1 MHz$	-	38	-		
Reverse transfer capacitance			-	0.039	0.078		
C _{rss} /C _{iss} ratio		$V_{DS} = 15 \text{ V}, \text{ V}_{GS} = 10 \text{ V}, \text{ I}_{D} = 10 \text{ A}$	-	16.8	25.5		
	Qg		-	8.3	12.5	nC	
Total gate charge	Q _{gs}	V _{DS} = 15 V, V _{GS} = 4.5 V, I _D = 10 A	-	2.1	-		
Gate-source charge	Q _{qd}		-	2.8	-		
Gate-drain charge	Q _{oss}	$V_{DS} = 15 \text{ V}, \text{ V}_{GS} = 0 \text{ V}$	-	8.7	-		
Output charge	Ra	f = 1 MHz	0.8	1.7	3.1	Ω	
Gate resistance	t _{d(on)}		-	7	14		
Turn-on delay time	tr	$V_{DD} = 15 \text{ V}, \text{ R}_{L} = 1.5 \Omega$	-	28	56	-	
Rise time	t _{d(off)}	$I_D \cong 10 \text{ A}, V_{GEN} = 10 \text{ V}, R_g = 1 \Omega$	-	14	28		
Turn-off delay time	t _f		-	8	16		
Fall time	t _{d(on)}		-	11	22	ns	
Turn-on delay time	tr	V_{DD} = 15 V, R _L = 1.5 Ω	-	47	94	-	
Rise time	t _{d(off)}	$I_D \cong 10 \text{ A}, V_{GEN} = 4.5 \text{ V}, R_g = 1 \Omega$	_	18	36		
Turn-off delay time	t _f	1 1	-	18	36		
Drain-Source Body Diode Characterist	ics			1		1	
Continuous source-drain diode current	Is	T _C = 25 °C	-	-	18		
Pulse diode forward current ^a	I _{SM}	~ ~	-	-	100	- A	
Body diode voltage	V _{SD}	I _S = 5 A	-	0.77	1.1	V	
	00	C C		1			

Notes

a. Pulse test; pulse width $\leq 300~\mu\text{s},~\text{duty}~\text{cycle} \leq 2~\%$

Body diode reverse recovery charge

Reverse recovery fall time

Reverse recovery rise time

b. Guaranteed by design, not subject to production testing

www.vishay.com

c. T_C = 25 °C; expected voltage stress during 100 % UIS test. Production data log is not available

Q_{rr}

ta

tb

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

 $I_F = 10 \text{ A}, \text{ di/dt} = 100 \text{ A/}\mu\text{s},$

 $T_J = 25 \ ^\circ C$

72

40

8

-

_


140

nC


ns




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Output Characteristics




On-Resistance vs. Drain Current




Gate Charge



Transfer Characteristics



Capacitance



On-Resistance vs. Junction Temperature

S17-1504-Rev. A, 02-Oct-17


3

Document Number: 76062


For technical questions, contact: <u>pmostechsupport@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Source-Drain Diode Forward Voltage




Threshold Voltage



On-Resistance vs. Gate-to-Source Voltage



Single Pulse Power, Junction-to-Ambient




Safe Operating Area


4

For technical questions, contact: <u>pmostechsupport@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Current Derating ^a



Note


a. The power dissipation P_D is based on T_J max. = 150 °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit




SiSA88DN

Vishay Siliconix

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Case

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?76062.



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.