



THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER **ORIGINAL** 

ADD NOTE 3 & 4

P.M. AUG. 12/2023

SPECIFICATION:

CONTACT: BRASS, GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING

HOUSING: PA9T, BLACK MAGNET: N52 PULL3-3.5N

ELECTRICAL:

RATED VOLTAGE (PER CONTACT): 5V RATED CURRENT (PER CONTACT): 2A


INSULATION RESISTANCE: 100MEGAOHMS MINIMUM. DIELECTRIC WITHSTANDING VOLTAGE: 100V AT 60Hz.


CONTACT RESISTANCE: 30mOHMS MAX. BEFORE TEST AND 60mOHMS MAX.

AFTER TEST POGO PIN WORKING STROKE.

RECOMMENDED SOLDERING PROCESS ARE SELECTIVE SOLDERING OR MANUAL SOLDERING. OTHER FORMS OF SOLDERING SUCH AS WAVE SOLDER OR REFLOW SOLDER ARE NOT RECOMMENDED AND CAN POTENTIALLY CAUSE DEMAGNETIZATION OF MAGNET IN THE CONNECTOR

MATING WITH: 686F0321250110E, 686F0321350120E, 686F0321350124E, 686F0321250124E OR 686F0321450110E





## MAGNETIC SPRING LOADED CONNECTOR, 3POS, MALE



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO.: 685F0321451110E UNIT: MM		UNIT: MM
DRAWN: J.L.	DATE: 8/12/2023	
CHECKED: R.S.M	DATE: 8/12/2023	3
SCALE: (IN CAD 1:1)	SHEET 1 OF	- 1
DRAWING NUMBER: 685E0321451110E		ISSUE

DRAWING NUMBER: 685F0321451110E ISSUE PART NUMBER: 685F0321451110E

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.