#### DATASHEET


## NI 9411 Datasheet

6 DI, ±5 V to 24 V, Differential/Single-Ended, 500 ns



- DSUB connectivity
- CompactDAQ counter compatibility
- 60 VDC, CAT I, channel-to-earth isolation

The NI 9411 works with industrial logic levels and signals for direct connection to a wide array of industrial switches, transducers, and devices. The NI 9411 is a correlated digital module, so it can perform correlated measurements, triggering, and synchronization when installed in a CompactDAQ chassis.





	С	SERIES DIGITAL INPU	T MODULE (	COMPARISO	N	
Product Name	Signal Levels	Direction	Channels	Update Rate	Isolation	Connectivity
NI 9411	±5 V, 24 V	Sinking/Sourcing Diff/ SE Input	6	500 ns	60 VDC Ch-Earth	15-Pin DSUB
NI 9421	12 V, 24 V	Sinking Input	8	100 μs	60 VDC Ch-Earth	Screw Terminal, 25-Pin DSUB
NI 9422	24 V, 48 V, 60 V	Sinking/ Sourcing Input	8	250 μs	250 Vrms Ch-Ch	Screw Terminal
NI 9423	12 V, 24 V	Sinking Input	8	1 μs	60 VDC Ch-Earth	Screw Terminal
NI 9425	12 V, 24 V	Sinking Input	32	7 µs	60 VDC Ch-Earth	37-Pin DSUB
NI 9426	24 V	Sourcing Input	32	7 µs	60 VDC Ch-Earth	37-Pin DSUB
NI 9435	250 VDC/ VAC	Sinking/ Sourcing Input	4	3 ms	250 Vrms Ch-Earth	Screw Terminal
NI 9437	24 V to 250 V	Sinking Input	8	1 µs	300 Vrms Ch-Earth	Screw Terminal

#### NI C Series Overview



NI provides more than 100 C Series modules for measurement, control, and communication applications. C Series modules can connect to any sensor or bus and allow for high-accuracy measurements that meet the demands of advanced data acquisition and control applications.

- Measurement-specific signal conditioning that connects to an array of sensors and signals
- Isolation options such as bank-to-bank, channel-to-channel, and channel-to-earth ground
- -40 °C to 70 °C temperature range to meet a variety of application and environmental needs
- Hot-swappable

The majority of C Series modules are supported in both CompactRIO and CompactDAQ platforms and you can move modules from one platform to the other with no modification.

### CompactRIO



CompactRIO combines an open-embedded architecture with small size, extreme ruggedness, and C Series modules in a platform powered by the NI LabVIEW reconfigurable I/O (RIO) architecture. Each system contains an FPGA for custom timing, triggering, and processing with a wide array of available modular I/O to meet any embedded application requirement.

### CompactDAQ

CompactDAQ is a portable, rugged data acquisition platform that integrates connectivity, data acquisition, and signal conditioning into modular I/O for directly interfacing to any sensor or signal. Using CompactDAQ with LabVIEW, you can easily customize how you acquire, analyze, visualize, and manage your measurement data.



#### Software

#### **LabVIEW Professional Development System for Windows**



- Use advanced software tools for large project development
- Generate code automatically using DAQ Assistant and Instrument I/O Assistant
- Use advanced measurement analysis and digital signal processing
- Take advantage of open connectivity with DLLs, ActiveX, and .NET objects
- Build DLLs, executables, and MSI installers

#### NI LabVIEW FPGA Module



- Design FPGA applications for NI RIO hardware
- Program with the same graphical environment used for desktop and real-time applications
- Execute control algorithms with loop rates up to 300 MHz
- Implement custom timing and triggering logic, digital protocols, and DSP algorithms
- Incorporate existing HDL code and third-party IP including Xilinx IP generator functions
- Purchase as part of the LabVIEW Embedded Control and Monitoring Suite

#### NI LabVIEW Real-Time Module




- Design deterministic real-time applications with LabVIEW graphical programming
- Download to dedicated NI or third-party hardware for reliable execution and a wide selection of I/O
- Take advantage of built-in PID control, signal processing, and analysis functions
- Automatically take advantage of multicore CPUs or set processor affinity manually
- Take advantage of real-time OS, development and debugging support, and board support
- Purchase individually or as part of a LabVIEW suite

### Input Circuitry

The NI 9411 channels share a common ground isolated from other modules in the system.

Figure 1. NI 9411 Input Circuitry



### NI 9411 Specifications

The following specifications are typical for the range -40 °C to 70 °C unless otherwise noted. All voltages are relative to COM unless otherwise noted.



**Caution** Do not operate the NI 9411 in a manner not specified in this document. Product misuse can result in a hazard. You can compromise the safety protection built into the product if the product is damaged in any way. If the product is damaged, return it to NI for repair.

### Input Characteristics

Number of channels	6 digital input channels
Input type	Differential or single-ended

Digital	0010	0370	ı
Digital	טוצטו	ICVC.	ιo

Digital logic levels	
Differential (DIa and DIb)	
Input high range	300 mV to 24 V
Input low range	-300 mV to -24 V
Common-mode voltage	-7 V to 12 V
Single-ended	
Input high range	2 V to 24 V
Input low range	0 V to 0.8 V
Input current	
At 5 V	±1 mA per channel
At 24 V	±4 mA per channel
Input impedance	8.4 kΩ
I/O protection	
Input voltage (channel-to-COM)	30 V maximum
Input current	±4 mA, internally limited
Input delay time	500 ns maximum
MTBF	800,319 hours at 25 °C; Bellcore Issue 2, Method 1, Case 3, Limited Part Stress Method
Power Requirements	
Power consumption from chassis	
Active mode	340 mW maximum
Sleep mode	1.1 mW maximum
Thermal dissipation (at 70 °C)	
Active mode	1.4 W maximum
Sleep mode	1.1 W maximum
External Power Supply	
Input voltage range (Vsup)	5 VDC to 30 VDC maximum

#### 5 V regulated output

Voltage tolerance	$5 \text{ V} \pm 3\%, \text{ Vsup} \ge 6 \text{ V}$
Current	200 mA
Short-circuit protection	400 mA



Note The NI 9411 does not provide overvoltage protection for the external power supply.

### **Physical Characteristics**

If you need to clean the module, wipe it with a dry towel.



**Tip** For two-dimensional drawings and three-dimensional models of the C Series module and connectors, visit *ni.com/dimensions* and search by module number.

Screw-terminal wiring	
Gauge	0.05 mm <sup>2</sup> to 1.5 mm <sup>2</sup> (30 AWG to 14 AWG) copper conductor wire
Wire strip length	6 mm (0.24 in.) of insulation stripped from the end
Temperature rating	90 °C minimum
Torque for screw terminals	0.22 N · m to 0.25 N · m (1.95 lb · in. to 2.21 lb · in.)
Wires per screw terminal	One wire per screw terminal; two wires per screw terminal using a 2-wire ferrule
Ferrules	0.25 mm <sup>2</sup> to 1.5 mm <sup>2</sup>
Connector securement	
Securement type	Screw flanges provided
Torque for screw flanges	0.2 N · m (1.80 lb · in.)
Weight	136 g (4.8 oz)

### Safety Voltages

Connect only voltages that are within the following limits.

Channel-to-COM or Vsup-to-COM	30 V maximum, Measurement Category I
Isolation	
Channel-to-channel	None

#### Channel-to-earth ground

Continuous	30 Vrms, 42.4 Vpk, 60 VDC
Withstand	400 Vrms, verified by a 5 s dielectric
	withstand test

Measurement Category I is for measurements performed on circuits not directly connected to the electrical distribution system referred to as MAINS voltage. MAINS is a hazardous live electrical supply system that powers equipment. This category is for measurements of voltages from specially protected secondary circuits. Such voltage measurements include signal levels, special equipment, limited-energy parts of equipment, circuits powered by regulated lowvoltage sources, and electronics.



**Caution** Do not connect the NI 9411 to signals or use for measurements within Measurement Categories II, III, or IV.



**Note** Measurement Categories CAT I and CAT O are equivalent. These test and measurement circuits are not intended for direct connection to the MAINS building installations of Measurement Categories CAT II, CAT III, or CAT IV.

#### **Hazardous Locations**

U.S. (UL)	Class I, Division 2, Groups A, B, C, D, T4; Class I, Zone 2, AEx nA IIC T4
Canada (C-UL)	Class I, Division 2, Groups A, B, C, D, T4; Class I, Zone 2, Ex nA IIC T4
Europe (ATEX) and International (IECEx)	Ex nA IIC T4 Gc

### Safety and Hazardous Locations Standards

This product is designed to meet the requirements of the following electrical equipment safety standards for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA 61010-1
- EN 60079-0:2012, EN 60079-15:2010
- IEC 60079-0: Ed 6, IEC 60079-15; Ed 4
- UL 60079-0; Ed 5, UL 60079-15; Ed 3
- CSA 60079-0:2011, CSA 60079-15:2012



**Note** For UL and other safety certifications, refer to the product label or the *Online* Product Certification section.

### Electromagnetic Compatibility

This product meets the requirements of the following EMC standards for sensitive electrical equipment for measurement, control, and laboratory use:

- EN 61326 (IEC 61326): Class A emissions; Industrial immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- AS/NZS CISPR 11: Group 1, Class A emissions
- FCC 47 CFR Part 15B: Class A emissions
- ICES-001: Class A emissions



**Note** For EMC declarations and certifications, and additional information, refer to the *Online Product Certification* section.



**Note** For EMC compliance, operate this device with shielded cables.

# CE Compliance ( €

This product meets the essential requirements of applicable European Directives, as follows:

- 2014/35/EU; Low-Voltage Directive (safety)
- 2014/30/EU; Electromagnetic Compatibility Directive (EMC)
- 94/9/EC; Potentially Explosive Atmospheres (ATEX)

#### Online Product Certification

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for this product, visit *ni.com/certification*, search by model number or product line, and click the appropriate link in the Certification column.

#### Shock and Vibration

To meet these specifications, you must panel mount the system.

Operating vibration	
Random (IEC 60068-2-64)	$5 g_{rms}$ , $10 Hz$ to $500 Hz$
Sinusoidal (IEC 60068-2-6)	5 g, 10 Hz to 500 Hz
Operating shock (IEC 60068-2-27)	30 g, 11 ms half sine; 50 g, 3 ms half sine; 18 shocks at 6 orientations

#### Environmental

Refer to the manual for the chassis you are using for more information about meeting these specifications.

Operating temperature (IEC 60068-2-1, IEC 60068-2-2)	-40 °C to 70 °C
Storage temperature (IEC 60068-2-1, IEC 60068-2-2)	-40 °C to 85 °C
Ingress protection	IP40
Operating humidity (IEC 60068-2-78)	10% RH to 90% RH, noncondensing
Storage humidity (IEC 60068-2-78)	5% RH to 95% RH, noncondensing
Pollution Degree	2
Maximum altitude	2,000 m

Indoor use only.

### **Environmental Management**

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the Minimize Our Environmental Impact web page at *ni.com/environment*. This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document

### Waste Electrical and Electronic Equipment (WEEE)



**EU Customers** At the end of the product life cycle, all NI products must be disposed of according to local laws and regulations. For more information about how to recycle NI products in your region, visit ni.com/environment/weee.

### 电子信息产品污染控制管理办法(中国 RoHS)

(A) 中国客户 National Instruments 符合中国电子信息产品中限制使用某些有害物 质指令(RoHS)。关于 National Instruments 中国 RoHS 合规性信息,请登录 ni.com/environment/rohs china。 (For information about China RoHS compliance, go to ni.com/environment/rohs china.)

Refer to the *NI Trademarks and Logo Guidelines* at ni.com/trademarks for information on NI trademarks. Other product and company names mentioned herein are trademarks or trade names of their respective companies. For patents covering NI products/technology, refer to the appropriate location: Help»Patents in your software, the patents.txt file on your media, or the *National Instruments Patent Notice* at ni.com/patents. You can find information about end-user license agreements (EULAs) and third-party legal notices in the readme file for your NI product. Refer to the *Export Compliance Information* at ni.com/legal/export-compliance for the NI global trade compliance policy and how to obtain relevant HTS codes, ECCNs, and other import/export data. NI MAKES NO EXPRESS OR IMPLIED WARRANTIES AS TO THE ACCURACY OF THE INFORMATION CONTAINED HEREIN AND SHALL NOT BE LIABLE FOR ANY ERRORS. U.S. Government Customers: The data contained in this manual was developed at private expense and is subject to the applicable limited rights and restricted data rights as set forth in FAR 52.227-14, DFAR 252.227-7014, and DFAR 252.227-7015.