


THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER **ORIGINAL**


ADD NOTE 4 & 5

P.M. AUG. 12/2023



SPECIFICATION:

- 1- MATERIAL:
 - CONTACT: BRASS GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING HOUSING: PA, BLACK
- 2- ELECTRICAL:
 - RATED VOLTAGE (PER CONTACT): 24V RATED CURRENT (PER CONTACT): 3A
 - INSULATION RESISTANCE: 100MEGAOHMS MINIMUM CONTACT RESISTANCE: 25mOHMS MAXIMUM
- 3- WORKING TEMPERATURE RANGE: -30°C~+85°C
- 4- RECOMMENDED SOLDERING PROCESS ARE SELECTIVE SOLDERING OR MANUAL SOLDERING. OTHER FORMS OF SOLDERING SUCH AS WAVE SOLDER OR REFLOW SOLDER ARE NOT RECOMMENDED AND CAN POTENTIALLY CAUSE DEMAGNETIZATION OF MAGNET IN THE CONNECTOR
- 5- MATING WITH: 685A2131260111E



2.00

MAGNETIC SPRING LOADED CONNECTOR, 21POS, FEMALE

YOUR CONNECTION TO QUALITY & SERVICE

Ø0.7

EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

	ACAD REFERENCE NO.: 686A2131260114E		UNIT: MM
	DRAWN: J.L.	DATE: 8/12/2023	
	CHECKED: R.S.M	DATE: 8/12/2023	
	SCALE: (IN CAD 1:1)	SHEET 1 OF	= 1
	DRAWING NUMBER: 686A2131260114E		ISSUE

686A213126U114E 2 PART NUMBER: 686A2131260114E

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.