


HC Series Chevron Inserts




Straight hole flanged / headed

HC Series Inserts offer the same benefits as the C Series plus a flanged head. This insert offers a large contact area for electrical connections and greater pull-out strengths for reverse entry applications.

Recommended Hole Size – See chart for installation hole size. Additional information can be found on page 5, Design Guidelines.





| INCH | | METRIC | | Α | В | С | D | Hole H | Min. |
|----------------|----------------|----------------|---------------------------|-------|-------|-------|---------------------|----------|------|
| Thread Size | Part Number | Thread Size | Part Number | ±.004 | ±.004 | ±.004 | Flange Thickness | +.003000 | Boss |
| 2-56 | H256 x 157C | M2.0 x 0.4 | HM20 x 157C | .188 | .157 | .123 | .018 | .126 | .252 |
| 4-40 | H440 x 226C | M2.5 x 0.45 | HM25 x 226C | .218 | .226 | .154 | .021 | .157 | .314 |
| | | M3.0 x 0.5 | HM30 x 226C | .218 | .226 | .154 | .021 | .157 | .314 |
| 6-32 | H632 x 180C | M3.5 x 0.6 | HM35 x 180C [†] | .250 | .180 | .185 | .027 | .188 | .376 |
| | H632 x 281C | | HM35 x 281C | .250 | .281 | .185 | .027 | .188 | .376 |
| 8-32 | H832 x 185C | M4.0 x 0.7 | HM40 x 185C | .281 | .185 | .218 | .033 | .221 | .442 |
| | H832 x 250C | | HM40 x 250C | .281 | .250 | .218 | .033 | .221 | .442 |
| | H832 x 321C | | HM40 x 321C | .281 | .321 | .218 | .033 | .221 | .442 |
| 10-24 | H1024 x 225C | M5.0 x 0.8 | HM50 x 225C [†] | .312 | .225 | .249 | .040 | .252 | .504 |
| | H1024 x 250C | | HM50 x 250C | .312 | .250 | .249 | .040 | .252 | .504 |
| | H1024 x 375C | | HM50 x 375C | .312 | .375 | .249 | .040 | .252 | .504 |
| 10-32 | H1032 x 225C | | | .312 | .225 | .249 | .040 | .252 | .504 |
| | H1032 x 250C | | | .312 | .250 | .249 | .040 | .252 | .504 |
| | H1032 x 375C | | | .312 | .375 | .249 | .040 | .252 | .504 |
| 1/4-20 | H2520 x 300C | M6.0 x 1.0 | HM60 x 300C | .375 | .300 | .312 | .050 | .315 | .630 |
| | H2520 x 500C | | HM60 x 500C | .375 | .500 | .312 | .050 | .315 | .630 |
| 1/4-28 | H2528 x 300C | | | .375 | .300 | .312 | .050 | .315 | .630 |
| | H2528 x 500C | | | .375 | .500 | .312 | .050 | .315 | .630 |
| 5/16-18 | H3118 x 500C | M8.0 x 1.25 | HM80 x 500C | .437 | .500 | .374 | .050 | .377 | .754 |
| 5/16-24 | H3124 x 500C | | | .437 | .500 | .374 | .050 | .377 | .754 |
| 3/8-16 | H3816 x 500C | M10.0 x 1.5 | HM100 x 500C [†] | .550 | .500 | .465 | .065 | .468 | .936 |
| 3/8-24 | H3824 x 500C | | | .550 | .500 | .465 | .065 | .468 | .936 |

Stainless Steel Inserts – Class 3A/4H screw must pass with finger torque, standard class go gage may stop on last thread. • Part numbers for Stainless Steel Inserts are the same as listed in the chart, but ending with -SS.

[†] Non-Stocking Item - Minimum Order May Apply