**TOLERANCE** UNLESS OTHERWISE SPECIFIED .XX ±0.10

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER **ORIGINAL** 

ADD NOTE 3 & 4

P.M. AUG. 13/2023

.X ±0.15

SPECIFICATION: 1- MATERIAL:

CONTACT: BRASS, GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING

HOUSING: PA9T, BLACK

MAGNET: N52, NICKEL PLATING

2- ELECTRICAL:

VOLTAGE RATING (PER CONTACT): 5V CURRENT RATING (PER CONTACT): 2A


INSULATION RESISTANCE: 100MEGAOHMS MINIMUM. DIELECTRIC WITHSTANDING VOLTAGE: 100V AT 60Hz.


CONTACT RESISTANCE: 30mOHMS MAX. BEFORE TEST AND 60mOHMS MAX.


AFTER TEST POGO PIN WORKING STROKE.

3- RECOMMENDED SOLDERING PROCESS ARE SELECTIVE SOLDERING OR MANUAL SOLDERING. OTHER FORMS OF SOLDERING SUCH AS WAVE SOLDER OR REFLOW SOLDER ARE NOT RECOMMENDED AND CAN POTENTIALLY CAUSE DEMAGNETIZATION OF MAGNET IN THE CONNECTOR

4- MATING WITH: 687B0611050110E OR 685B0621250124E







## MAGNETIC SPRING LOADED CONNECTOR, 6POS, FEMALE



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO.: 686B0621250124E UNIT: MM	
DRAWN: J.L.	DATE: 8/13/2023
CHECKED: R.S.M	DATE: 8/13/2023
SCALE: (IN CAD 1:1)	SHEET 1 OF 1
DRAWING NUMBER: 696B06212E0124E	

DRAWING NUMBER: 686B0621250124E ISSUE 2 PART NUMBER: 686B0621250124E

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.