

UNLESS O	TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.15	
.XX	±0.10	

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.





ISSUE NUMBER	
ORIGINAL	1
ADD NOTE 3 & 4	

AUG. 11/2023

686D0432210123E

6.70	
7.70	7.55





SPECIFICATION:

1- MATERIAL:

CONTACT: BRASS GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING

MAGNET: N52 HOUSING: PA9T

2- ELECTRICAL:

RATED VOLTAGE PIN 1 AND PIN 4 (PER CONTACT): 20V RATED CURRENT 1st AND 4th PIN (PER CONTACT): 3A INSULATION RESISTANCE: 100MEGAOHMS MINIMUM DIELECTRIC WITHSTANDING VOLTAGE: 100V AT 60Hz

CONTACT RESISTANCE: 30mOHMS MAXIMUM BEFORE TEST AND 60mOHMS MAXIMUM AFTER TEST

3- RECOMMENDED SOLDERING PROCESS ARE SELECTIVE SOLDERING OR MANUAL SOLDERING. OTHER FORMS OF SOLDERING SUCH AS WAVE SOLDER OR REFLOW SOLDER ARE NOT RECOMMENDED AND CAN POTENTIALLY CAUSE DEMAGNETIZATION OF MAGNET IN THE CONNECTOR

4- MATING WITH: 685D0432210123E

WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO.: 686D0432210123E UNIT: MM MAGNETIC SPRING LOADED CONNECTOR, DRAWN: DATE: 8/11/2023 4POS, FEMALE CHECKED: R.S.M DATE: 8/11/2023 THESE DRAWINGS AND SPECIFICATIONS SCALE: (IN CAD 1:1) SHEET 1 OF EDAC INC ARE THE PROPERTY OF EDAC INC..AND TORONTO, ONTARIO SHALL NOT BE REPRODUCED, OR COPIED DRAWING NUMBER: 686D0432210123E ISSUE OR USED AS THE BASIS FOR THE CANADA MANUFACTURE OR SALE OF APPARATUS YOUR CONNECTION TO QUALITY & SERVICE PART NUMBER:



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.