
TOLERANCE UNLESS OTHERWISE SPECIFIED .X ±0.15 .XX ±0.10 THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.




ISSUE NUMBER ORIGINAL

ADD NOTE 4 & 5

P.M. AUG. 13/2023



19.3 50 6 5-Ø0.60



SPECIFICATION:

1- MATERIAL:

CONTACT: BRASS, GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING

HOUSING: PA9T, BLACK

MAGNET: N52 2- ELECTRICAL:

RATED VOLTAGE (PER CONTACT): 5V RATED CURRENT (PER CONTACT): 2A

INSULATION RESISTANCE: 100MEGAOHMS MIN. DIELECTRIC WITHSTANDING VOLTAGE: 100V AT 60Hz.


CONTACT RESISTANCE: 30mOHMS MAX. BEFORE TEST AND 60mOHMS MAX. AFTER TEST


3- SALT SPRAY TEST: 5% SALT SPRAY CONCENTRATION, TEMPERATURE 35°C, TEST TIME 48 HOURS, NO CORROSION.

WORKING TEMPERATURE RANGE: -30°C~+85°C.

4- RECOMMENDED SOLDERING PROCESS ARE SELECTIVE SOLDERING OR MANUAL SOLDERING. OTHER FORMS OF SOLDERING SUCH AS WAVE SOLDER OR REFLOW SOLDER ARE NOT RECOMMENDED AND CAN POTENTIALLY CAUSE DEMAGNETIZATION OF MAGNET IN THE CONNECTOR

5- MATING WITH: 687J0522A51110E, 685J0521451110E, 685J0521251110E, 685J0521351110E, 685J0521351114E OR 685J0521251114E





RECOMMENDED P.C.B. LAYOUT (T=1.6mm) TOLERANCE UNSPECIFIED ±0.05mm

MAGNETIC SPRING LOADED CONNECTOR, 5POS, FEMALE



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

| ACAD REFERENCE NO.: 686J0521350110E UNIT: MN | | JNIT: MM |
|--|-----------------|----------|
| DRAWN: J.L. | DATE: 8/13/2023 | |
| CHECKED: R.S.M | DATE: 8/13/2023 | |
| SCALE: (IN CAD 1:1) | SHEET 1 OF | 1 |
| DRAWING NUMBER: 696 I05212501105 | | ISSLIE |

DRAWING NUMBER: 686J0521350110E ISSUE PART NUMBER: 686J0521350110E



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.