TOLERANCE UNLESS OTHERWISE SPECIFIED ±0.20 .X ±0.15 .XX ±0.10


THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.





ISSUE NUMBER ORIGINAL


ADD NOTE 5 & 6

P.M. AUG. 13/2023









SPECIFICATION:

CONTACT: BRASS GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING

HOUSING: PA9T, BLACK MAGNET: N52

2- ELECTRICAL:

RATED VOLTAGE (PER CONTACT): 5V RATED CURRENT (PER CONTACT): 1A CONTACT RESISTANCE: 30mOHMS MAXIMUM

3- SALT SPRAY TEST: 48 HOURS, MIN.

4- WORKING TEMPERATURE RANGE: -40~+85° C

5- RECOMMENDED SOLDERING PROCESS ARE SELECTIVE SOLDERING OR MANUAL SOLDERING. OTHER FORMS OF SOLDERING SUCH AS WAVE SOLDER OR REFLOW SOLDER ARE NOT RECOMMENDED AND CAN POTENTIALLY CAUSE DEMAGNETIZATION OF MAGNET IN THE CONNECTOR

6- MATING WITH: 687K0412A501100

MAGNETIC SPRING LOADED CONNECTOR, 4POS, FEMALE



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

	ACAD REFERENCE NO.: 686K0412P50125E		UNIT: MM
	DRAWN: J.L.	DATE: 8/15/2023	
	CHECKED: R.S.M	DATE: 8/15/2023	
	SCALE: (IN CAD 1:1)	SHEET 1 O	F 1
	DRAWING NUMBER: 686K0412P50125E		ISSUE

ISSUE 2 PART NUMBER: 686K0412P50125E

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY. COMPLIANT