

Rotary Position Sensor Series 525

Features

- Field proven (over 13 million units delivered)
- Leak-proof rotor and cover seals
- Suitable for Harsh environment such as Engine compartment
- Mates with Metri-Pack® 150 Series PS2 connector
- Spring loaded "Tang Drive"
- No electromagnetic interference issues

Applications

- Industrial
- Off Road
- Harsh Environments
- Agriculture

Description

This Rotary Position Sensor (RPS) works on the potentiometer principle. The Rotary shaft position determines the contact location of the metal arm on the patented polymer film. Based on the contact position, the effective resistance and output voltage are calculated. Our 525 RPS design is optimized for accuracy, durability and low noise while reducing the negative effects of Axial rotor movement and electromagnetic interference. 525 RPS sensors feature a low-cost, robust design that benefits from patented technology and its small hermetically sealed package which eliminates the potential for moisture and debris penetration. With a temperature range of -40° to 150°C and IP6K9K rating, our 525 RPS is versatile to be used in in-cabin application or engine under-hood applications. Please contact CTS if you are interested in using our RPS to determine linear movement position using Kinematic mechanism principle.

Electrical Specifications

Parameter	Unit			
Total Resistance	> 3k Ω			
Linearity	± 2.0% standard			
Rotation Maximum	119º mechanical 97º typical electrical			
Hysteresis	< 1.0% applied voltage			
Electrical Limit Maximum	16 VDC			
Typical Voltage	5.0 — 10.0 VDC			
Maximum Power Rating	0.08 watts			

www.ctscorp.com

RevA_0922 Page 1 of 3

©2023 CTS Corporation. Information/product(s) subject to change. No warranty that product(s) will meet the stated specifications for customer specific applications or test

equipment. Visit www.ctscorp.com for list of applicable patent(s), more information, or to request a quote.



Mechanical Specifications

Parameter	Value				
Torque	15 Nmm at any position between 0° and 100° rotation				
Mounting Bolt Torque	2 N (18 in. lbs., typical drive)				
Rotor	9.47 mm diameter				
Shaft Recommended	See recommended mounting				


IMPORTANT: exceeding the absolute maximum ratings may cause permanent damage to the sensor module. Exposure to absolute maximum-rated conditions for extended periods of time may affect sensor module reliability.


Durability and Environmental Specifications

Parameter	Unit				
Electrical Life	Full Strokes: >1 Million Cycles -25°C to 135°C				
Electrical Life	Dither Strokes: 10 Million Cycles -25°C to 135°C				
Vibration	16 – 22 G rms Random for 20hrs each plane				
Vibration	-40°C to 150°C temperature cycling				
Thermal Shock	500 cycles: -40°C to 135°C				
Temperature Range	-40°C to 150°C				
Salt Spray	96 hrs., 5% solution				
Leak Test	150°C immersion into 25°C water for 5 min				
Fuel Vapor	48 hrs. each in 15% methanol, 15% ethanol and indolene HO.				
Ozone	72 hrs. at 38°C, 100 ppm ozone				
Dust	48 km/hr. blowing course dust 9 hrs. at 80°C				

Operating conditions VDD = $5V\pm10\%$, unless otherwise specified.

0º incline connector version – Dimension Details





Page 2 of 3





0º incline connector version - Partnumbers

CTS Part No	Index Volt at "A"	"B"	Angle from Axis 0 to Mech stop "C"	Nom. Slope/Deg.	Rotation	Rotor	Cover	Config.
525-99-011	12% at 6° ±2°	85° ±2°	10.53°, 6.5% at 0°	0.91765% of input	CW	Black	Black	Non Adj.
525-99-018	0.37% at -8°±2°	97° ±2°	10.53°, 7.2% at 0°	0.8536% of input	CW	Black	Black	Non Adj.
525-99-019*	12% at 6° ±2°	85° ±2°	10.53°, 6.5% at 0°	0.91765% of input	CCW	Gray	Gray	Non Adj.

Note: * Part 525-99-019 has a 3 month lead time for component procurement

15º incline connector version – Dimension Details





15º incline connector version - Partnumbers

CTS Part No	Index Volt at "A"	"B"	Angle from Axis 0 to Mech stop "C"	Nom. Slope/Deg.	Rotation	Rotor	Cover	Config.
525-99-009	12% at 8° ±2°	84° ±2°	10.32°, 4.6% at 0°	0.92857% of input	CCW	Gray	Gray	Non Adj.
525-99-015	12% at 8° ±2°	84° ±2°	10.53°, 4.6% at 0°	0.92857% of input	CW	Black	Black	Non Adj.
525-99-020*	12% at 8° ±2°	94° ±3°	10.53°, 5.4% at 0°	0.82979% of input	CW	Black	Black	Non Adj.

Note: * Part 525-99-020 has a 3 month lead time for component procurement