Data Sheet No: E16013 Version: V2

Date: 2023/11/16



PEWK3920

High-Precision Low-Inductance Alloy Current Sensing Resistor

Resistance $2m\Omega \sim 5m\Omega$

Tolerance ±0.5%

TCR ±50ppm/℃

Rated Current 24A~54A

Applications

Automotive Electronics

Precision Power Supply

Instrumentation

Testing & Measurement Equipment

Medical Equipment

Better Solution for Sustainable High End Manufacturing




High-Precision Low-Inductance Alloy Current Sensing Resistor

Low-Inductance Alloy Current Sensing Resistor "Trimming Free" Technology, High Precision, Reliability

Introduction











"Trimming Free" technology avoids the loss of rated current caused by trimming and also avoids current accumulation hotspots caused by trimmed notch, greatly improving the reliability of the product. Meanwhile, due to the improvement of welding quality, thermal EMF of the product is significantly reduced, improving its long-term stability.

PEWK3920 series, from raw materials, core equipment, to core processes, achieves independent and controllable production, stable quality, and timely delivery. If the standard specifications cannot meet your needs, please contact our sales for consultation. Resi is committed to providing the best precision resistor solutions to meet the needs of customers in instrumentation, medical equipment, automotive electronics, precision power supplies, formation & sorting of battery testing and measurement equipment and other fields.

Electrical Parameters

Size	Resistance	Rated Power (+70°C)	Max. Operating Current	Operating Temperature ℃	TCR ppm/°C(+20°CRef)	Thermal Resistance* °C/W	Tolerance %
PEWK3920	2mΩ	6W	54A	-55~+170	±50 (-55°C∼+170°C)	15.4	±0.5 ±1.0 ±5.0
PEWK3920	3mΩ	5W	40A	-55~+170	±50 (-55°C∼+170°C)	23.1	±0.5 ±1.0 ±5.0
PEWK3920	4mΩ	4W	30A	-55~+170	±50 (-55°C∼+170°C)	28.9	±0.5 ±1.0 ±5.0
PEWK3920	5mΩ	3W	24A	-55~+170	±50 (-55°C∼+170°C)	36.5	±0.5 ±1.0 ±5.0

^{*} Thermal Resistance: Refer to the internal thermal resistance between the center of the resistive alloy and the copper electrode.

As the heat dissipation efficiency is influenced by operating environment, copper bus bars, PCB design, etc., this parameter is only for reference.


Applications

 $Inductance\ of\ PEWK3920\ current\ sensing\ resistors\ is\ less\ than\ 3nH,\ suitable\ for\ AC,\ DC\ low\ and\ high\ frequency\ sampling\ circuits.$




DimensionsUnit: mm

Resistor








Resistance	L	W	Α	Т	D	a	b	c	Packaging	Quantity Per Reel	Net Weight
2mΩ	10.0±0.3	5.2±0.3	2.0±0.3	0.6±0.2	0.5±0.2	5.6±0.1	6.2±0.2	2.7±0.2	Tape&Reel	2000pcs	0.27±0.1
3mΩ	10.0±0.3	5.2±0.3	2.0±0.3	0.4±0.2	0.5±0.2	5.6±0.1	6.2±0.2	2.7±0.2	Tape&Reel	2000pcs	0.18±0.1
4mΩ	10.0±0.3	5.2±0.3	2.0±0.3	0.33±0.15	0.5±0.2	5.6±0.1	6.2±0.2	2.7±0.2	Tape&Reel	2000pcs	0.15±0.1
5mΩ	10.0±0.3	5.2±0.3	2.0±0.3	0.25±0.15	0.5±0.2	5.6±0.1	6.2±0.2	2.7±0.2	Tape&Reel	2000pcs	0.11±0.1

Part Number Information

Example: PEWK3920F2L00Q9 (PEWK 3920 $\pm 1.0\%$ 2.0m Ω ± 50 ppm/°C Standard)



For higher/lower resistance, tighter tolerance, higher power, lower TCR and larger size, please contact us.





Performance

Test	Test Method	Standards	Typical	Max.	
High Temperature Storage	1000h@+170°C, unpowered	AEC-Q200 TEST 3 MIL-STD-202 Method 108	△R≤±0.5%	△R≤±1.0%	
Thermal Shock	-55°C, 15min~ambient temperature<20s~+155°C, 15min, 1000 cycles	AEC-Q200 TEST 16 MIL-STD-202 Method 107	^R≤±0.1%	△R≤±0.5%	
Bias Humidity	+85°C, 85%RH, powered no less than 10% rated power for 1000h	AEC-Q200 TEST 7 MIL-STD-202 Method 103	△R≤±0.2%	△R≤±0.5%	
Load Life	2000h @ +70°C, rated power, 90min on, 30min off +70°C refers to terminal temperature	AEC-Q200 TEST 8 MIL-STD-202 Method 108	△R≤±0.5%	△R≤±1.0%	
Resistance to Solvent	Immerse in solvent for 3 min and wipe 10 times. Three cycles of three solvents. Dry at ambient temperature after cleaning	AEC-Q200 TEST 12 MIL-STD-202 Method 215	Clear marking. No visible damage		
Mechanical Shock	Half Sine Wave, peak acceleration 100g's, pulse duration 6ms, 3 times in each of six directions, on three different axes	AEC-Q200 TEST 13 MIL-STD-202 Method 213	^R≤±0.05%	△R≤±0.2%	
Vibration	10-2KHz, 5g's, 20min/cycle, 12 cycles in each directions of X Y Z	AEC-Q200 TEST 14 MIL-STD-202 Method 204	^R≤±0.05%	△R≤±0.2%	
Resistance to Solder Heat	+260°C tin bath for 10s	AEC-Q200 TEST 15 MIL-STD-202 Method 210	△R≤±0.2%	△R≤±0.5%	
Solderability	+245°C tin bath for 3s	AEC-Q200 TEST 18 IEC 60115-1 4.17	No visible damag 95% minimum co		
TCR	-55°C and +170°C, +20°C Ref.	AEC-Q200 TEST 19 IEC 60115-1 4.8	Refer to tested curve, max. value ≤ ±50ppm/°C		
Substrate Bending	2mm. Duration: 60s.	AEC-Q200 TEST 21 AEC-Q200-005	△R≤±0.01%	△R≤±0.1%	
Short Time Overload	5x rated voltage, 5s	IEC 60115-1 4.13	△R≤±0.1%	△R≤±0.5%	
Low Temperature Storage	-55°C for 96h, unpowered	IEC 60068-2-1	△R≤±0.1%	△R≤±0.5%	
Moisture Resistance	Apply T=24 h/cycle, zero power, method 7a and 7b are not required	MIL-STD-202 Method 106	△R≤±0.1%	△R≤±0.5%	



ICR (ppm/°C)

5.00


0.00

38.27 30.13 30.69 30.78

-40°C -20°C 37.94 37.12 29.48 31.93 31.01 30.61 30.29 29.47 36.14 34.49

High-Precision Low-Inductance

Temperature Coefficient of Resistance Test Curve



 -20°C
 O°C
 40°C
 60°C
 80°C
 100°C
 120°C
 140°C
 170°C

 371.2
 34.6
 47.02
 40.83
 37.12
 35.88
 34.64
 33.41
 32.88

 31.93
 27.02
 39.30
 31.93
 29.40
 28.66
 28.00
 26.61
 26.67

 30.61
 26.93
 46.52
 35.50
 32.65
 31.22
 29.87
 28.97
 28.33

 29.47
 24.60
 39.30
 35.61
 31.11
 29.47
 28.00
 27.43
 26.31

 34.49
 32.03
 41.88
 35.72
 33.67
 32.65
 30.55
 29.98
 29.21

Temperature (°C)

45.00 TCR (ppm/°C) 20.00 10.00 5.00 0.00 22.69 23.85 27.68 22.57 21.85 20.73 20.89 22.14 21.57 21.41 27.17 26.28 25.64 24.07 23.12 22.92 22.15 21.82 21.58 30.26 28.96 35.23 33.43 28.53 26.06 23.85 31.87 28.42 26.01 23.53 24.41 29.63 26.19 24.06 22.69 22.99 28.10 25.07 22.66

TCR Test Curve -PEWK3920 3.0mΩ


Temperature (°C)

TCR Test Curve -PEWK3920 4.0mΩ



Temperature (°C)

TCR Test Curve -PEWK3920 5.0mΩ




Temperature (°C)




High-Precision Low-Inductance Alloy Current Sensing Resistor

Derating Curve




Reflow Soldering Profile

Resistor Surface Temperature: Pre-Heat: +150°C~+190°C,60~120sec. Reflow: Above +220°C,90~150sec. Applicable Solder Composition: Sn-Ag-Cu



Maximum Pulse Energy Curve






PEWK3920

High-Precision Low-Inductance Alloy Current Sensing Resistor

Construction



Marking

The first line (four digits) represents brand. The second line (five digits) represents tolerance and resistance.

Size	Illustration	Demonstration	
3920	F2100	RESI: Brand F: Tolerance 2L00: Resistance	

Storage Instructions

- (1) Resistors should be stored at a temperature of 5 to 35 °C, with a humidity of <60% RH. The humidity should be kept as low as possible.
- (2) Resistors should be protected from direct sunlight.
- (3) Resistors should be stored in a clean and dry environment free of harmful gases (HCI, Sulfuric acid, H₂S, etc.)
- (4) Do not move the resistor from the packaging unless use it.
- (5) Under the above storage conditions, the resistor can be stored for at least 1 year.

Usage Suggestions


- (1) Please protect the surface of the resistor during use. Prevent defects such as scratches, bumps, and oil stains on the surface.
- (2) Do not use sharp tweezers to move the resistor. Scratches on the surface can cause resistance drift and resistor failure.
- (3) When installing and using resistors, avoid the impact of mechanical stress on the resistor.
- (4) The long-term operating power of resistors should be less than the rated power to avoid resistance drift caused by long-term overload.
- (5) Please refer to the derating curve when operating under high temperature conditions or poor heat dissipation environment.
- (6) If the operating conditions exceed the pulse specified in the pulse curve, a systematic evaluation is required.
- (7) If the resistor is not used after being moved from the packaging, it should be stored under vacuum to avoid risks such as poor solderability caused by oxidation of the resistor.



Packaging

Tape Specifications






Resistance	Α	В	ϕD_0	φD1	Ko	K 1	K2	E	G	W	D	t
2.0mΩ	5.5±0.2	10.5±0.2	1.5±0.1	1.5±0.1	4.0±0.1	8.0±0.1	2.0±0.1	1.75±0.1	7.5±0.1	16.0±0.3	1.5±0.1	0.3±0.05
3.0mΩ	5.5±0.2	10.5±0.2	1.5±0.1	1.5±0.1	4.0±0.1	8.0±0.1	2.0±0.1	1.75±0.1	7.5±0.1	16.0±0.3	1.5±0.1	0.3±0.05
4.0mΩ	5.5±0.2	10.5±0.2	1.5±0.1	1.5±0.1	4.0±0.1	8.0±0.1	2.0±0.1	1.75±0.1	7.5±0.1	16.0±0.3	1.5±0.1	0.3±0.05
5.0mΩ	5.5±0.2	10.5±0.2	1.5±0.1	1.5±0.1	4.0±0.1	8.0±0.1	2.0±0.1	1.75±0.1	7.5±0.1	16.0±0.3	1.5±0.1	0.3±0.05

Reel Specifications






A	φВ	φC	φD	φΕ
1.5 Min.	13.0 +0.5/-0.2	20.2 Min.	330±2	100±2




Packaging


- (1) 2000 pcs. resistors are packed in a tape and wrapped in a reel;
- (2) Every 2 reels are packed by a cardboard. The size of the cardboard is 335mm*340mm*37mm;
- (3) Place every 3 cardboards into a box (12000 pcs. / box);
- (4) Box size: 350*370*165mm.




1. 2000 pcs. resistors are packed in a tape and wrapped in a reel.




2. Every 2 reels are packed by a cardboard. The size of the cardboard is 335mm*340mm*37mm.



3. Place every 3 cardboards into a box (12000 pcs. / box).



4. For the last box which is less than 12000 pcs., bubble wraps or EPE should be placed to prevent products from shaking or vibration.



5. Box size: 350*370*165mm



High-Precision Low-Inductance Alloy Current Sensing Resistor

Popular Part Numbers

Part Number	Size	Tolerance	Resistance	TCR	Power	Max. Operating Current
PEWK3920D2L00Q9	3920	±0.5%	2.0mΩ	±50ppm/°C	6W	54A
PEWK3920F2L00Q9	3920	±1.0%	2.0mΩ	±50ppm/°C	6W	54A
PEWK3920J2L00Q9	3920	±5.0%	2.0mΩ	±50ppm/°C	6W	54A
PEWK3920D3L00Q9	3920	±0.5%	3.0mΩ	±50ppm/°C	5W	40A
PEWK3920F3L00Q9	3920	±1.0%	3.0mΩ	±50ppm/°C	5W	40A
PEWK3920J3L00Q9	3920	±5.0%	3.0mΩ	±50ppm/°C	5W	40A
PEWK3920D4L00Q9	3920	±0.5%	4.0mΩ	±50ppm/°C	4W	30A
PEWK3920F4L00Q9	3920	±1.0%	4.0mΩ	±50ppm/°C	4W	30A
PEWK3920J4L00Q9	3920	±5.0%	4.0mΩ	±50ppm/°C	4W	30A
PEWK3920D5L00Q9	3920	±0.5%	5.0mΩ	±50ppm/°C	3W	24A
PEWK3920F5L00Q9	3920	±1.0%	5.0mΩ	±50ppm/°C	3W	24A
PEWK3920J5L00Q9	3920	±5.0%	5.0mΩ	±50ppm/°C	3W	24A

Revision

Version	Revised Content	Date	Approver
V0	Initial Issue	2022.07.28	LWW
V1	Add TCR test curve	2022.10.28	LWW
V2	Add a new resistance 4mR、5mR; Change datasheet to the new template	2023.10.31	LWW



PEWK3920

High-Precision Low-Inductance Alloy Current Sensing Resistor

Disclaimer

All products, datasheets and data can be changed without prior notice.

C&B Electronics Shenzhen CO., LTD., its affiliates, distributors, employees, and any other person acting on its behalf (collectively referred to as "C&B Electronics") shall not bear any legal responsibility for any errors, inaccuracies, or incompleteness of information related to the product disclosed under this agreement or other disclosures.

Product datasheet does not constitute an extension or revision of the purchase terms and conditions in C&B Electronics, including but not limited to the warranties under this agreement.

Unless specified in the purchase terms and conditions, C&B Electronics makes no guarantees, representations or warranties.

To the maximum extent permitted by applicable laws, C&B Electronics hereby makes the following disclaimer:

- (1) All liabilities arising from the use of the product;
- (2) Including but not limited to all liabilities arising from special, indirect or incidental damages;
- (3) All implied warranties, including warranties of suitability for special purposes, non infringement possibility, and marketability.

The information provided in the datasheet and parameter tables may vary in different applications, and the performance of the product may change over time. The recommended application instructions for the product are based on C&B Electronics' understanding and experience of typical requirements. Customers are obligated to verify whether the product is suitable for a specific application based on the parameters provided in the datasheet. Before officially installing or using the product, you should ensure that you have obtained the latest version of relevant information, which can be obtained through the website: resistor.today.

The signing of this agreement does not constitute an express, implied or other form of license related to all intellectual property rights of C&B Electronic Products.

Unless explicitly stated, the products listed in this agreement are not applicable to lifesaving or life sustaining products. In the absence of a clear indication, the customer shall bear all risks caused by unauthorized use of the above products and agree to fully compensate C&B Electronics for all losses caused by such sales or use. For written product terms for such special applications, please contact authorized personnel from C&B Electronics to obtain.

The names and markings on the listed products may be trademarks owned by others.