



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-3 @20°C	0.370 ohms max.
D.C. RESISTANCE	6-4 @20°C	0.140 ohms max.
INDUCTANCE	1-3 10kHz, 100mVAC, Ls	450.00uH min.
LEAKAGE INDUCTANCE	1-3 tie(4+5+6), 1MHz, 100mVAC, Ls	750nH typ., 1300nH max.
INTERWINDING CAPACITANCE	1-6 100kHz, 10mVAC, Cs	11.0pF typ., 18.0pF max.
DIELECTRIC	1-6 2500VAC, 1 second	2500VAC, 1 minute
URNS RATIO	(1-3):(6-4)	2.4:1

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

CURRENT RATING: 1.1A on secondary side.

VOLTAGE-TIME: 19Vus for Unipolar operation  
38Vus for Bipolar operation

Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-1281 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE <b>TRANSFORMER</b>	PART NO. <b>750320324</b>
6A	8/23	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750320324	SPECIFICATION SHEET 1 OF 1