



34-Way IDC Connector Socket for Cable Mount, 2-Row

RoHS Compliant

FEATURES

- 34 Ways
- 2 Rows
- 1.27mm Pitch



Stock No.: D1275WVI-234-P0BKG

Product Description

- □ Double Row Female IDC connector with polarization
- □ Gold finish on contact area, Tin finish on termination.
- □ For use with 0.635mm pitch, 30AWG ribbon cable.

General Specifications

Connector Type	Jack
Number of Contacts	34
Number of Rows	2
Gender	Female
Body Orientation	Straight
Contact Material	Phosphor Bronze
Housing Material	РВТ
Colour	Black
Applications	computers connecting drives, cd drives, SSD's and other components

Electrical Specifications

Current Rating	1A
Voltage Rating	AC 500V
Proof Voltage	500VDC or AC peak
Termination Method	IDC
Contact Plating	Gold over Nickel Plated
Cable	1.27mm (0.05in) pitch flat cable
Insulator Resistance	1000MOhm min. at DC 500V
Contact Resistance	20MOhm max. at DC 100mA
Dielectric Withstanding Voltage	1000VAC for 1 Minute
Connector System	Wire to Board

After every difficulty, there is always ease.





Mechanical Specifications

Pitch	1.27mm
Mounting Type	Cable Mount
Ejector Style	N/A
Length	25.79mm
Width	3.0mm


Operation Environment Specifications

Operating Temperature Range	-40°C to 105°C
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	105°C





Product Drawing



Dimensions: Millimeters (Inches)

Part Number Table

Part Number	Description
D1275WVI-234-P0BKG	34-Way IDC Connector Socket for Cable Mount, 2-Row

Important Notice: This data sheet and its contents (the "Information") belong to the members of the EASE group of companies (the "Group") or are licensed to it. No license is granted for the use of it other than for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate, but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility for less or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. EASE is the registered trademark of Ease Electronics Co., Limited 2019.