# **SUNON**

### **SPECIFICATION FOR APPROVAL**

**CUSTOMER** :

**DESCRIPTION** : AXIAL AC FAN

DIMENSIONS : 92X92X25 mm

MODEL : SF11592A

P/N : 1092HST.GN

**SUNON SPEC. NO.** : A09000370G-00

**CUSTOMER** 

APPROVAL NO.

**APPROVED BY** 

**CUSTOMER** 

(AUTHORIZED)

DRAWN	Jeff 06/03 CHECKED March Kiddy Approved Jacky		SPEC.NO	A09000370G-00			
		CHECKED		APPROVED		ISSUE DATE	04. 30. 2005
						EDITION	3
				REVISION DATE	06. 03. 2013		
						E.SPEC	EA92012

建準電機工業股份有限公司

SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD.

No. 30, LN. 296, XINYA RD., QIANZHEN DIST., TEL:886-7-8135888

KAOHSIUNG CITY 80673, TAIWAN (R.O.C)

URL:http://www.sunon.com

FAX:886-7-8230505/8230606/8231010

E-mail: sunon@email.sunon.com

2013.07.15

AXIAL AC FAN MODEL : SF11592A

P/N : 1092HST.GN

### **CHARACTERISTICS**

1. Motor Design : Reliable Shaded-Pole Motor Construction.

2. Insulation Resistance : 500 Megohms minimum at 500 VDC.

3. Dielectric Strength : 1500 VAC for one second.

4. Motor Protection : Impedance protected.

5. Noise Level : Measured in a semi-anechoic chamber

with background noise level below 15

dB(A). The fan is running in free air with the

microphone at a distance of one meter

from the fan intake.

6. Tolerance : ±15% on rated power and current.

7. Air Performance : Measured by a double chamber. The values

are recorded when the fan speed has stabilized

at rated voltage.

建準電機工業股份有限公司	SPEC.NO	A09000370G-00	REVISION DATE	06.03.2013
SUNONWEALTH ELECTRIC	ISSUE DATE	04. 30. 2005	EDITION	B D C C
MACHINE INDUSTRY CO., LTD.	P A G E	2 OF 9	F	2012 07 15

### **SPECIFICATIONS**

**MODEL: SF11592A** 

P/N : 1092HST.GN

1-1. Rated Voltage : 115 VAC 50/60 Hz

1-2. Operating Voltage Range : 85~125 VAC

1-3. Starting Voltage : 85 VAC (25 deg. C POWER ON/OFF)

1-4. Rated Speed :  $2250/2750 \text{ RPM} \pm 10\%$ 

1-5. Air Delivery : 29/36 CFM

1-6. Static Pressure : 0.12/0.18 Inch-H<sub>2</sub>O

1-7. Rated Current : 0.12/0.11 AMP

1-8. Rated Power : 13/12 WATTS

1-9. Noise Level : 36/39 dB(A)

1-10. Direction of Rotation : Counter-clockwise viewed from front of fan blade

1-11. Operating Temperature : -10 to +70 deg. C

1-12. Storage Temperature : -40 to +70 deg. C

1-13. Bearing System : Lubricated sleeve bearing system

1-14. Weight : 280 g

1-15. Safety : UL/CUR/TUV/CE Approvals

1-16. Protection : □Automatic Restart Capability

Note: In a situation where the fan is locked by an external force while the electricity is on, an increase in coil temperature will be prevented by temporarily turning off the electrical power to the motor. The fan will automatically restart when the locked rotor condition is released.

**□Polarity Protection** 


建準電機工業股份有限公司	SPEC.NO	A09000370G-00	REVISION DATE	06,03,2013
SUNONWEALTH ELECTRIC	ISSUE DATE	04. 30. 2005	EDITION /	3 DCC FI
MACHINE INDUSTRY CO., LTD.	PAGE	3 OF 9		2013 07 15

**MODEL: SF11592A** 

P/N : 1092HST.GN

### PERFORMANCE CURVES

STATIC PRESSURE



建準電機工業股份有限公司	SPEC.NO	A09000370G-00	REVISION DATI	E 06. 03. 2013
SUNONWEALTH ELECTRIC	ISSUE DATE	04. 30. 2005	EDITION	第一 <sup>集(象)</sup>
MACHINE INDUSTRY CO., LTD.	P A G E	4 OF 9	ļ.	D.C.C.


### MATERIAL

2. Material

2-1. Frame : DIE-CAST ALUMINUM

2-2. Impeller : Thermoplastic PBT of UL 94V-0

## **DIMENSIONS**



Air Flow Direction: Toward label side.

UNITS: mm

建準電機工業股份有限公司	SPEC.NO	A09000370G-00	REVISION DATE	96×03×2013
SUNONWEALTH ELECTRIC	ISSUE DATE	04. 30. 2005	EDITION	3 D.C.C. 🕏
MACHINE INDUSTRY CO., LTD.	PAGE	5 OF 9		2013.07.15

# Notes

#### I .SAFETY

- 1. DO NOT use or operate this fan in excess of the limitations set forth in this specification. SUNON is not responsible for the non-performance of this fan and/or any damages resulting from its use, if it is not used or operated in accordance with the specifications.
- 2. SUNON recommends adding a protection circuit to the product or application in which this fan is installed, such as a thermo-fuse, or current-fuse or thermo-protector. The failure to use such a device may result in smoke, fire, electric shock by insulation degradation in cases of motor lock, motor lead short circuit, overload, or over voltage, and/or other failure.
- 3. SUNON recommends installing a protection device to the product or application in which this fan is installed if there is a possibility of reverse-connection between VDC (+) and GND (-). The failure to install such a device may result in smoke, fire, and/or destruction, although these conditions may not manifest immediately.
- 4. This fan must be installed and used in compliance with all applicable safety standards and regulations.
- 5. Use proper care when handling and/or installing this fan. Improper handling or installation of this fan may cause damage that could result in unsafe conditions.
- 6. Use proper care during installation and/or wiring. Failure to use proper care may cause damage to certain components of the fan including, but not limited to, the coil and lead wires, which could result in smoke and/or fire.
- 7. DO NOT use power or ground PWM to control the fan speed. If the fan speed needs to be adjusted, please contact SUNON to customize the product design for your application.
- 8. For critical or extreme environments, including non stop operation, please contact SUNON and we will gladly provide assistance with your product selection to ensure an appropriate cooling product for your application.

建準電機工業股份有限公司	SPEC.NO	A09000370G-00	REVISION DATE	06 03 2013
SUNONWEALTH ELECTRIC	<b>ISSUE DATE</b>	04. 30. 2005	EDITION	
MACHINE INDUSTRY CO., LTD.	PAGE	6 OF 9	F	2013 07 15

## **Notes**

#### II. SPECIFICATION MODIFICATION

- 1. SUNON offers engineering assistance on fan installation and cooling system design.
- 2. All changes, modifications and/or revisions to the specifications, if any, are incorporated in the attached specifications.
- 3. No changes, modifications and/or revisions to these specifications are effective absent agreement, by both SUNON and the customer, in writing.
- 4. This fan will be shipped in accordance with the attached specification unless SUNON and the customer have agreed otherwise, in writing, as specified in Paragraph 3, above.

#### III. OTHER

- 1. When building your device, please examine thoroughly any variation of EMC, temperature rise, life data, quality, etc. of this product by shock/drop/vibration testing, etc. If there are any problems or accidents in connection with this product, it should be mutually discussed and examined.
- 2. Use proper care when handling this fan. Components such as fan holders or bearings may be damaged, if touched with fingers or other objects. Additionally, static electricity (ESD) may damage the internal circuits of the fan.
- 3. DO NOT operate this fan in proximity to hazardous materials such as organic silicon, cyanogens, formalin, phenol, or corrosive gas environments including, but not limited to, H<sub>2</sub>S, SO<sub>2</sub>, NO<sub>2</sub>, or Cl<sub>2</sub>.
- 4. SUNON recommends that you protect this fan from exposure to outside elements such as dust, condensation, humidity or insects. Exposure of this fan to outside elements such as dust, condensation, humidity or insects may affect its performance and may cause safety hazards. SUNON does not warrant against damage to the product caused by outside elements.

建準電機工業股份有限公司	SPEC.NO	A09000370G-00	REVISION DATE	06 03 2013
SUNONWEALTH ELECTRIC	ISSUE DATE	04. 30. 2005	EDITION /	
MACHINE INDUSTRY CO., LTD.	PAGE	7 OF 9		2013 07 15

## **Notes**

- 5. This fan must be installed properly and securely. Improper mounting may cause harsh resonance, vibration, and noise.
- 6. Fan guards may prevent injury during handling or installation of the fan and are available for sale with this fan.
- 7. Unless otherwise noted, all testing of this fan is conducted at 25°C ambient temperature and sixty-five percent (65%) relative humidity.
- 8. DO NOT store this fan in an environment with high humidity. This fan must be stored in accordance with the attached specifications regarding storage temperature. If this fan is stored for more than 6 months, SUNON recommends functional testing before using.
- 9. SUNON reserves the right to use components from multiple sources at its discretion. The use of components from other sources will not affect the specifications as described herein.
- 10. The "Life Expectancy" of this fan has not been evaluated for use in combination with any end application. Therefore, the Life Expectancy Test Reports (L10 and MTTF Report) that relate to this fan are only for reference.

#### VI. WARRANTY

This fan is warranted against all defects which are proved to be fault in our workmanship and material for one year from the date of our delivery. The sole responsibility under the warranty shall be limited to the repair of the fan or the replacement thereof, at SUNON's sole discretion. SUNON will not be responsible for the failures of its fans due to improper handing, misuse or the failure to follow specifications or instructions for use. In the event of warranty claim, the customer shall immediately notify SUNON for verification. SUNON will not be responsible for any consequential damage to the customer's equipment as a result of any fans proven to be defective.

建準電機工業股份有限公司	SPEC.NO	A09000370G-00	REVISION DATE	06.03.2013
SUNONWEALTH ELECTRIC	ISSUE DATE	04. 30. 2005	EDITION /	3 D.C.C 🔻
MACHINE INDUSTRY CO., LTD.	P A G E	8 OF 9		2013.07.15

### **Declaration of RoHS**

#### Control declaration of environment- related substances/ materials

1. In accordance with the Restriction of Hazardous Substances (RoHS) Directive 2011/65/EU, SUNON product have complied with law and discipline not to employ the forbidden substances, and restrict the allowable concentration of some limited substances deliberately in our components.

No **Substance** Criteria Forbidden 1 CFCs & HCFCs (ozone depleting substances) Forbidden 2 **Chlorinated Organic Solvent** Plastic (Frame, Impeller, wire harness, etc.) <100ppm <1000ppm Solder 3 Steel alloy <3500ppm Lead and its compounds <4000ppm Aluminium alloy <4wt% Copper alloy Solder <20ppm Parts composed of metals containing zinc <100ppm 4 Cadmium and its compounds (e.g. brass, zinc for die casting) <5ppm **Plastic** Forbidden **PBBs and PBDEs** 5 Forbidden **PCB** and **PCT** 6 Forbidden CP, Short-chain Chlorinated paraffins C10-13, Cl≥48 wt% Forbidden 8 Mirex Forbidden **PCN** 9 <100ppm 10 **Hexavalent Chromium compounds** Forbidden Mercury and its compounds 11 Forbidden 12 Asbestos Forbidden 13 **Organic Tin compounds** Forbidden 14 Azo compounds TBBP-A in external case plastic parts of products (PCB is exempted) <1000ppm 15 <1000ppm 16 Nickel in external case parts, which are likely to result in prolonged skin exposure <1000ppm **17** Hexabromocyclododecane (HBCDD) <1000ppm 18 Di-butyl Phthalate (DBP) 19 **Benzyl butyl Phthalate (BBP)** <1000ppm <1000ppm 20 Di-ethylhexyl Phthalate (DEHP) <1000ppm 21 Di-isobutyl Phthalate (DIBP)

建準電機工業股份有限公司	SPEC.NO	A09000370G-00	REVISION DATE	06. 03. 2013
SUNONWEALTH ELECTRIC	ISSUE DATE	04. 30. 2005	EDITION	3%激工業後
MACHINE INDUSTRY CO., LTD.	P A G E	9 OF 9	Į.	D.C.C.

2013.07.15