

MICROWAVE TEST ASSEMBLIES, 1.85mm (male), 1.85mm (male), 50 Ohm, 70 GHz, 24in, time delay matched +/- 1ps.

PMASF570S/11PC185/11PC185/24in

Properties

- Applicable up to 70 GHz
- High phase- and amplitude stability with flexure and movement
- Excellent insertion and return loss
- Absolute time delay matched +/- 1ps
- Precise and repeatable measurements
- Return loss figures are guaranteed up to 67 GHz



Product configuration	
Type of cable	SUCOFLEX_570_S
Type description connector A	SF_11_PC185-501
Series connector A	PC 1.85, straight - plug
Series connector B	PC 1.85, straight - plug
Length	610 mm
	24 inch
Length type	REF to REF

Electrical data	
Impedance	50 Ω
Max. operating frequency	70 GHz
Min. return loss	14 dB
VSWR max	1.499
Max. insertion loss	4.63 dB
Signal delay	4.3 ns/m
Propagation velocity	77 %
Min. screening effectiveness	90 dB
Max. screening frequency	18 GHz
Amplitude stability vs. flexure	+/- 0.05 dB
Phase stability vs. flexure	+/- 8 °

Mechanical data	
Cable diameter	5.8 mm
Static bending radius	25.4 mm

**MICROWAVE TEST ASSEMBLIES, 1.85mm (male), 1.85mm (male), 50 Ohm, 70 GHz, 24in,
time delay matched +/- 1ps.**

PMASF570S/11PC185/11PC185/24in

Environmental data	
Operation temperature	-55 °C ... 125°C

Ordering information	
Item number	Item description
85153051	PMASF570S/11PC185/11PC185/24in

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P10604 / Date of publication: 16.11.2023 / uncontrolled copy