

**FP BOX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The FieldPower® power distributors support error-free installation in an extremely short space of time. Branches and functions integrated in the cover can simply be plugged in. Robust with high protection degree.

**General ordering data**

Version	FieldPower® power distribution box, AC, IP65, in complete state, glass-fibre reinforced polycarbonate, Insulation displacement connection (IDC), PUSH IN
Order No.	<a href="#">1957580000</a>
Type	FP BOX
GTIN (EAN)	4032248636655
Qty.	1 pc(s).

Creation date February 1, 2024 11:21:09 AM CET

Catalogue status 27.01.2024 / We reserve the right to make technical changes.

## FP BOX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	67 mm	Depth (inches)	2.638 inch
Height	181 mm	Height (inches)	7.126 inch
Width	104 mm	Width (inches)	4.094 inch
Net weight	542.93 g		

### Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...55 °C
---------------------	----------------	-----------------------	----------------

### Clamping capacity

Connection data - contact element power bus	Wire connection method	Insulation displacement connection (IDC)
	Blade size of operating tool	0.6 x 3.5 mm
	Number of poles	5
	Conductor connection cross-section, solid, max.	6 mm <sup>2</sup>
	Conductor connection cross-section, solid, min.	1.5 mm <sup>2</sup>
	Conductor connection cross-section, stranded, max.	6 mm <sup>2</sup>
	Conductor connection cross-section, stranded, min.	2.5 mm <sup>2</sup>
	Conductor connection cross-section, finely stranded, max.	6 mm <sup>2</sup>
	Conductor connection cross-section, finely stranded, min.	2.5 mm <sup>2</sup>
	Conductor connection cross-section, finest stranded, max.	6 mm <sup>2</sup>
Conductor connection cross-section, finest stranded, min.	2.5 mm <sup>2</sup>	

## FP BOX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

Connection data - contact element  
 Branch / Feed-in

Wire connection method	PUSH IN	
Blade size of operating tool	0.6 x 3.5 mm	
Stripping length	14 mm	
Number of poles	5	
Conductor connection cross-section, solid, max.	6 mm <sup>2</sup>	
Conductor connection cross-section, solid, min.	0.5 mm <sup>2</sup>	
Conductor connection cross-section, stranded, max.	6 mm <sup>2</sup>	
Conductor connection cross-section, stranded, min.	0.5 mm <sup>2</sup>	
Conductor connection cross-section, finely stranded, max.	10 mm <sup>2</sup>	
Conductor connection cross-section, finely stranded, min.	0.5 mm <sup>2</sup>	
Conductor connection cross-section, finest stranded, max.	6 mm <sup>2</sup>	
Conductor connection cross-section, finest stranded, min.	0.5 mm <sup>2</sup>	
Conductor connection cross-section with wire end ferrule	Type of wire end ferrule	12 mm with plastic collar
	Standard	DIN 46228/1
	Cross-section, min.	0.5 mm <sup>2</sup>
	Cross-section, max.	6 mm <sup>2</sup>
	Type of wire end ferrule	12 mm with plastic collar
	Standard	DIN 46228/4
	Cross-section, min.	0.5 mm <sup>2</sup>
	Cross-section, max.	6 mm <sup>2</sup>
	Type of wire end ferrule	8 mm with plastic collar
	Standard	DIN 46228/1
	Cross-section, min.	0.5 mm <sup>2</sup>
	Cross-section, max.	6 mm <sup>2</sup>
	Type of wire end ferrule	8 mm with plastic collar
	Standard	DIN 46228/4
	Cross-section, min.	0.5 mm <sup>2</sup>
	Cross-section, max.	6 mm <sup>2</sup>
Type of wire end ferrule	Twin wire-end ferrules	
Cross-section, min.	0.5 mm <sup>2</sup>	
Cross-section, max.	6 mm <sup>2</sup>	

## General data

Material	Polycarbonate, glass fibre reinforced	Insulating material	Polycarbonate
Enclosure material	glass-fibre reinforced polycarbonate	Silicone	No
Colour	black	Protection degree	IP65, in complete state
UL 94 flammability rating	5VA	Torque for lid screws	2 Nm
Lid attachment	TX20 screws	Type of mounting	Screw mounting, Fixing lugs
Installation advice	Lid screws included	Can be coded	Yes, Coded on PE
Voltage type	AC	Number of poles	5
Number of connections / pole	1	Wire connection method	Insulation displacement connection (IDC), PUSH IN

## FP BOX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Rated data acc. to IEC

Rated data acc. to IEC for contact element	Voltage type	AC
	Number of phases	3
	Standard	IEC 60947-7-1, IEC 60947-7-2
	Rated voltage	800 V
	Rated impulse withstand voltage	8 kV
	Rated current (3 loaded poles)	41 A
	Rated current (4 loaded poles)	25 A

## Rated data acc. to UL

Rated data acc. to UL for contact element	Standard	UL 1059
	Note	for use with UL-listed TC-ER cables
	Conductor connection cross-section, AWG, max.	AWG 10
	Conductor connection cross-section, AWG, min.	AWG 14
	Rated voltage	600 V
	Rated current	30 A
Standards	UL 2237	


## Classifications

ETIM 6.0	EC000214	ETIM 7.0	EC000214
ETIM 8.0	EC000214	ETIM 9.0	EC000214
ECLASS 9.0	27-14-24-09	ECLASS 9.1	27-14-24-09
ECLASS 10.0	27-14-24-09	ECLASS 11.0	27-14-24-09
ECLASS 12.0	27-14-24-09	ECLASS 13.0	27142409

## Environmental Product Compliance

REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	5f19cd84-8946-4797-9386-3ac323b95c10

## Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UL)	E310075

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">UL Certificate FieldPower® Box and accessories</a> <a href="#">Manufacturer's Declaration FieldPower® BOX, BOX FUSE and Terminal variants</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Product Change Notification	<a href="#">Product Change Notification FieldPower® box base</a> <a href="#">Produktänderungsmitteilung FieldPower® Box Unterschale</a> <a href="#">Produktänderungsmitteilung FieldPower® Box Schrauben</a> <a href="#">Product Change Notification FieldPower® box screws</a> <a href="#">Technical change to FieldPower® (GHDE)</a>
User Documentation	<a href="#">Manual FieldPower® Box</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

Creation date February 1, 2024 11:21:09 AM CET

Catalogue status 27.01.2024 / We reserve the right to make technical changes.

**FP BOX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Drilling template**

